Product datasheet





pendant station XAC-A pistol grip -2 push buttons 1 Emergency stop

XACA2033

! Discontinued on: 9 Feb 2023

EAN Code: 3389110558791

① Discontinued

Main

Range Of Product	Harmony XAC
Product Or Component Type	Pendant control station
Device Short Name	XACA pistol grip

Complementary

Control Station Type	Double insulated
Enclosure Material	Polypropylene
Control Type	Intuitive
Electrical Circuit Type	Control circuit
Enclosure Type	Complete ready for use
Control Station Application	Control of single speed hoist motor
Control Station Composition	2 push-buttons + 1 emergency stop
Control Button Type	Stop push-button Ø 30 mm 1 NC latching First push-button 2 NO raise, slow Second push-button 2 NO lower, slow
Product Compatibility	ZB2BE101 for each direction ZB2BE102 for emergency stop
Mechanical Interlocking	With mechanical interlocking
Control Station Colour	Yellow
Connections - Terminals	Screw clamp terminals, $1 \times 2.5 \text{ mm}^2$ with or without cable end Screw clamp terminals, $2 \times 1.5 \text{ mm}^2$ with or without cable end
Standards	· · · · · · · · · · · · · · · · · · ·
_	UL 508 EN/IEC 60947-5-1 CSA C22.2 No 14
Standards	UL 508 EN/IEC 60947-5-1 CSA C22.2 No 14 EN/IEC 60204-32
Standards Product Certifications	UL 508 EN/IEC 60947-5-1 CSA C22.2 No 14 EN/IEC 60204-32 CSA UL
Product Certifications Protective Treatment Ambient Air Temperature For	UL 508 EN/IEC 60947-5-1 CSA C22.2 No 14 EN/IEC 60204-32 CSA UL TH
Product Certifications Protective Treatment Ambient Air Temperature For Operation Ambient Air Temperature For	UL 508 EN/IEC 60947-5-1 CSA C22.2 No 14 EN/IEC 60204-32 CSA UL TH -2570 °C
Product Certifications Protective Treatment Ambient Air Temperature For Operation Ambient Air Temperature For Storage	Screw clamp terminals, 2 x 1.5 mm² with or without cable end UL 508 EN/IEC 60947-5-1 CSA C22.2 No 14 EN/IEC 60204-32 CSA UL TH -2570 °C
Product Certifications Protective Treatment Ambient Air Temperature For Operation Ambient Air Temperature For Storage Vibration Resistance	UL 508 EN/IEC 60947-5-1 CSA C22.2 No 14 EN/IEC 60204-32 CSA UL TH -2570 °C -4070 °C 15 gn (f= 10500 Hz) conforming to IEC 60068-2-6

Life Is On Schneider 23 Apr 2024

Ik Degree Of Protection	IK08 conforming to EN 50102	
Mechanical Durability	1000000 cycles	
Cable Entry	Rubber sleeve with stepped entry 715 mm	
Contact Code Designation	A600 AC-15, Ue = 240 V, Ie = 3 A conforming to IEC 60947-5-1 appendix A A600 AC-15, Ue = 600 V, Ie = 1.2 A conforming to IEC 60947-5-1 appendix A Q600 DC-13, Ue = 250 V, Ie = 0.27 A conforming to IEC 60947-5-1 appendix A Q600 DC-13, Ue = 600 V, Ie = 0.1 A conforming to IEC 60947-5-1 appendix A	
[Ithe] Conventional Enclosed Thermal Current	10 A	
[Ui] Rated Insulation Voltage	600 V (pollution degree 3) conforming to IEC 60947-1	
[Uimp] Rated Impulse Withstand Voltage	6 kV conforming to IEC 60947-1	
Contact Operation	Slow-break	
Maximum Resistance Across Terminals	25 MOhm	
Operating Force	1315 N	
Short-Circuit Protection	10 A fuse protection by cartridge fuse type gG	
Rated Operational Power In W 40 W DC-13 for 1000000 cycles, operating rate <60 cyc/mn at 120 V, load for 0.5 (inductive load) conforming to IEC 60947-5-1 appendix C 48 W DC-13 for 1000000 cycles, operating rate <60 cyc/mn at 48 V, load far (inductive load) conforming to IEC 60947-5-1 appendix C 65 W DC-13 for 1000000 cycles, operating rate <60 cyc/mn at 24 V, load far (inductive load) conforming to IEC 60947-5-1 appendix C		
Terminal Identifier	(11-12)NC (13-14)NO	

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	8.2 cm
Package 1 Width	11.9 cm
Package 1 Length	34.4 cm
Package 1 Weight	360.0 g
Unit Type Of Package 2	S03
Number Of Units In Package 2	15
Package 2 Height	30.0 cm
Package 2 Width	30.0 cm
Package 2 Length	40.0 cm
Package 2 Weight	5.924 kg

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

Ø	Reach Free Of Svhc	
⊘	Toxic Heavy Metal Free	
⊘	Mercury Free	
⊘	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	No need of specific recycling operations