

# Product data sheet

Specifications

SQUARE D



NEMA starter, Type DPS, reversing, horizontal, Size 4, 135A, 100 HP at 575VAC, 10kA SCCR, 3 phase, 3 pole, melting alloy overload, 120VAC coil, open

8911DPSO32V02

⚠ Discontinued

⚠ Discontinued on: Dec 18, 2023

Product availability: Stock - Normally stocked in distribution facility

## Main

Product	Definite Purpose Starter
Ampere Rating	30 A
Horsepower Rating	2 hp 115 V AC, 1 phase 5 hp 230 V AC, 1 phase
Maximum Voltage Rating	600 V AC
Control Circuit Voltage	110 V AC 50 Hz 120 V AC 60 Hz
Phase	1 phase

## Complementary

Enclosure Rating	Not rated (open device)
Locked Rotor Amperes	180 A 230 V AC 150 A 460 V AC 120 A 575 V AC
Number Of Poles	2P
Range	DPS
Overload Type	Melting alloy
Number Of Thermal Units	1

## Ordering and shipping details

Category	US10CP121381
Discount Schedule	0CP1
Gtin	785901342809
Returnability	Yes
Country Of Origin	MX

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	5.00 in (12.7 cm)

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Width	5.00 in (12.7 cm)
Package 1 Length	8.00 in (20.32 cm)
Package 1 Weight	35.20 oz (997.913 g)

## Contractual warranty

Warranty	18 months
----------	-----------

# Sustainability



**Green Premium™ label** is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)

## Well-being performance

 Mercury Free	
 Rohs Exemption Information	<a href="#">Yes</a>
Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	<a href="#">China RoHS declaration</a> Product out of China RoHS scope. Substance declaration for your information.