Product datasheet

Specifications





empty control station-severe environments-black-3 cut-outs-3 vertical openings

XALG03

EAN Code: 3389119019347

Main

Range Of Product	Harmony XALG	
Product Or Component Type	Empty control station	
Device Short Name	XALG	
Product Destination	For XB5 Ø 22 mm control and signalling units	
Environmental Characteristic	Severe ambiance	
Colour Of Base Of Enclosure	Black (RAL 9005)	
Colour Of Cover	Black (RAL 9005)	
Material	Mineral reinforced polyamide	
Cable Entry	2 knock-outs for ISO M20 cable entry	
Ip Degree Of Protection	IP66 conforming to IEC 60529 IP67 conforming to IEC 60529 IP69 IP69K	

Complementary

-		
Assembly Style	For customer assembly	
Number Of Cut-Out	3 cut-outs 30 mm	
Cad Overall Width	180 mm	
Cad Overall Height	72 mm	
Cad Overall Depth	65 mm	
Net Weight	0.333 kg	
Resistance To High Pressure Washer	10 mPa at 80 °C, distance : 0.2 m	

Environment

Protective Treatment	TH
	TC
Ambient Air Temperature For Storage	-4070 °C
Ambient Air Temperature For Operation	-2570 °C
Electrical Shock Protection Class	Class II conforming to EN/IEC 61140
Ik Degree Of Protection	IK05 conforming to EN 50102

23 Apr 2024 Life Is On Schneider

Resistance To Chemical Agents Good resistance to lactic acid at 10 °C Good resistant to detergent at 60 °C Not resistant to formic acid (10 %) at 50 °C Not resistant to lactic acid at 90 °C Good resistance to ammonia Good resistance to benzene Good resistance to butter Good resistance to citric acid (10 %) Good resistance to cutting compounds Good resistance to ethane Good resistance to ethanol Good resistance to ethylene Good resistance to fatty acids Good resistance to fatty alcohols Good resistance to milk Good resistance to motor oils and greases Good resistance to oils (vegetable, mineral) Good resistance to petroleum Good resistant to acetone Good resistant to uric acid (20 %) Limited resistance to acetic acid (10 %) Limited resistance to boric acid Not resistant to hydrogen peroxide (30 %) Not resistant to nitric acid (2 %) Standards EN/IEC 60947-1

EN/IEC 60947-5-1

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	8.0 cm
Package 1 Width	10.0 cm
Package 1 Length	18.7 cm
Package 1 Weight	321.0 g
Unit Type Of Package 2	S03
Number Of Units In Package 2	16
Package 2 Height	30.0 cm
Package 2 Width	30.0 cm
Package 2 Length	40.0 cm
Package 2 Weight	5.64 kg

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance


Ø	Reach Free Of Svhc	
⊘	Toxic Heavy Metal Free	
Ø	Mercury Free	
⊘	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information

Dimensions Drawings

Dimensions



(1) 2 ISO 20 cable entries.