



# Pilot light 3 phases voltage, indicator with 3 LED, white, 400 V AC

XB5EV57L4

EAN Code: 3606481194190

#### Main

Range Of Product	Harmony XB5
Product Or Component Type	Monolithic pilot light
Device Short Name	XB5
Bezel Material	Plastic
Fixing Collar Material	Plastic
Mounting Diameter	30 mm
Sale Per Indivisible Quantity	1
Shape Of Signaling Unit Head	Round
Cap/Operator Or Lens Colour	Clear
Light Source	Protected LED
Bulb Base	Integral LED
Light Source Colour	White
Network Number Of Phases	3 phases
Device Presentation	Monolithic product

### Complementary

Height	65.5 mm			
Width	36 mm			
Depth	77 mm			
Net Weight	0.065 kg			
Connections - Terminals	Faston terminals, connection size: 6.3 mm conforming to IEC 60947-1			
[Uimp] Rated Impulse Withstand Voltage	1 kV conforming to IEC 61000-4-5			
Compatibility Code	XB5			
Supply Voltage Limits	450 V AC			
Current Consumption	2.6 mA			
Service Life	100000 h at rated voltage and 25 °C			
Surge Withstand	1 kV conforming to IEC 61000-4-5			

#### **Environment**

Ambient Air Temperature For Storage	-4070 °C
Ambient Air Temperature For Operation	-3070 °C

Ip Degree Of Protection	IP67 (front face) IP20 (back face)				
Ik Degree Of Protection	IK10 conforming to IEC 50102				
Standards	IEC 60947-5-1 IEC 60947-5-4 IEC 60947-1				
Resistance To Fast Transients	2 kV conforming to IEC 61000-4-4				
Resistance To Electromagnetic Fields	10 V/m conforming to IEC 61000-4-3				
Electromagnetic Compatibility	Electrostatic discharge - test level: 8 kV (in free air (in insulating parts)) conforming to IEC 61000-4-2 Electrostatic discharge - test level: 4 kV (on contact (on metal parts)) conforming to IEC 61000-4-2				

## **Packing Units**

•	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4.000 cm
Package 1 Width	4.500 cm
Package 1 Length	9.000 cm
Package 1 Weight	64.000 g
Unit Type Of Package 2	S01
Number Of Units In Package 2	50
Package 2 Height	15.000 cm
Package 2 Width	15.000 cm
Package 2 Length	40.000 cm
Package 2 Weight	3.448 kg

## **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

#### Well-being performance



Mercury Free



Rohs Exemption Information


Yes

#### **Certifications & Standards**

Reach Regulation	REACh Declaration				
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)				
China Rohs Regulation	China RoHS declaration				
Environmental Disclosure	Product Environmental Profile				
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins				
Circularity Profile	End of Life Information				

#### **Dimensions Drawings**

#### **Dimensions**




(e) clamp thickness max. 6mm / 0.24 in.

#### Mounting and Clearance

#### Panel Cut-out for Pilot Light(Finished Holes, Ready for Installation)


#### **Connection by Faston Connectors**



(1) Diameter on finished panel or support (2) Ø30 mm recommended / Ø1.2 in. recommended

Connections	a in mm	a in in.	b in mm	b in in.
By Faston Connectors	40	1.57	40	1.57


#### **Panel Cut-out**



- (1) Diameter on finished panel or support
- (2) Ø30 mm recommended / Ø1.2 in. recommended

#### Connections and Schema

#### Wiring Diagram



- (1) Phase 1 (2) Phase 2 (3) Phase 3

- (N) Neutral