# **Product datasheet**





# Pilot light, Harmony XB5, antimicrobial, grey plastic, blue flush mounted, 30mm, universal LED, plain lens, 110...120V AC

Local distributor code: 407813955

Important message: A change in appearance may be noted on the product but does not affect its use in terms of function and safety. This makes it compatible with our Universal LED blocks EAN Code: 3606481360946

#### Main

Range Of Product	Harmony XB5
Product Or Component Type	Pilot light
Device Short Name	XB5F
Bezel Material	Dark grey plastic
Fixing Collar Material	Plastic
Head Type	Built-in-flush
Mounting Diameter	30.5 mm
Sale Per Indivisible Quantity	1
Shape Of Signaling Unit Head	Round
Cap/Operator Or Lens Colour	Blue
Operator Additional Information	With plain lens
Light Source	Universal LED
Bulb Base	Integral LED
Light Source Colour	Blue
[Us] Rated Supply Voltage	110120 V AC at 50/60 Hz
Device Presentation	Complete product

### Complementary

Height	42 mm
Width	36.6 mm
Depth	55 mm
Terminals Description Iso N°1	(X1-X2)PL
Net Weight	0.038 kg
Resistance To High Pressure Washer	7000000 Pa at 55 °C, distance : 0.1 m
Connections - Terminals	Screw clamp terminals, <= 2 x 1.5 mm² with cable end conforming to IEC 60947-1 Screw clamp terminals, 1 x 0.222 x 2.5 mm² without cable end conforming to IEC 60947-1
[Ui] Rated Insulation Voltage	250 V (pollution degree 3) conforming to IEC 60947-1
[Uimp] Rated Impulse Withstand Voltage	4 kV conforming to IEC 60947-1
Signalling Type	Steady

Life Is On Schneider 23 Apr 2024



Gcr Bridge	XB5FVCUST01
Compatibility Code	XB5
Supply Voltage Limits	100132 V AC
Current Consumption	14 mA
Service Life	100000 h at rated voltage and 25 °C
Surge Withstand	1 kV conforming to IEC 61000-4-5

### **Environment**

Liviloilileit			
Protective Treatment	тн		
Ambient Air Temperature For Storage	-4070 °C		
Ambient Air Temperature For Operation	-4070 °C		
Overvoltage Category	Class II conforming to IEC 60536		
Ip Degree Of Protection	IP66 conforming to IEC 60529 IP67 conforming to IEC 60529 IP69 conforming to IEC 60529 IP69K conforming to ISO 20653		
Nema Degree Of Protection	NEMA 13 NEMA 4X		
Ik Degree Of Protection	IK03 conforming to IEC 50102		
Standards	JIS C8201-5-1 CSA C22.2 No 14 UL 508 IEC 60947-1 IEC 60947-5-4 IEC 60947-5-1 JIS C8201-1 ISO 21702 ISO 22196:2011		
Product Certifications	UL listed CSA		
Vibration Resistance	5 gn (f= 12500 Hz) conforming to IEC 60068-2-6		
Shock Resistance	50 gn (duration = 18 ms) for half sine wave acceleration conforming to IEC 60068-2-27 30 gn (duration = 11 ms) for half sine wave acceleration conforming to IEC 60068-2-27		
Resistance To Fast Transients	2 kV conforming to IEC 61000-4-4		
Resistance To Electromagnetic Fields	10 V/m conforming to IEC 61000-4-3		
Electromagnetic Compatibility	Electrostatic discharge - test level: 6 kV (on contact (on metal parts)) conforming to IEC 61000-4-2 Electrostatic discharge - test level: 8 kV (in free air (in insulating parts)) conforming to IEC 61000-4-2 Electromagnetic emission class B conforming to IEC 55011		
Resistance To Electrostatic Discharge	6 kV on contact (on metal parts) conforming to IEC 61000-4-2 8 kV in free air (in insulating parts) conforming to IEC 61000-4-2		
Electromagnetic Emission	Class B conforming to IEC 55011		

# **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4.3 cm
Package 1 Width	5.3 cm

Package 1 Length	8.6 cm	
Package 1 Weight	42.0 g	

### **Contractual warranty**

Warranty 18 months

# Sustainability Green Premium\*

**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

#### Well-being performance



Mercury Free



Rohs Exemption Information


Yes

#### **Certifications & Standards**

Reach Regulation	REACh Declaration		
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)		
China Rohs Regulation	China RoHS declaration		
Environmental Disclosure	Product Environmental Profile		
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins		
Circularity Profile	End of Life Information		

#### **Dimensions Drawings**

#### **Dimensions**




e: Clamping thickness: 1 to 6 mm / 0.04 to 0.24 in.

#### XB5FVG6

#### Mounting and Clearance

Panel Cut-out for Pushbuttons, Switches and Pilot Lights (Finished Holes, Ready for Installation)

#### Connection by Screw Clamp Terminals or Plug-in Connectors



(1) Diameter on finished panel or support

(2) Ø30.75 mm recommended (Ø30.5  $_0^{+0.5}$ ) / Ø1.21 in. recommended (Ø1.20 in.  $_0^{+0.0196}$ )

· ·				•
Connections	a in mm	a in in.	b in mm	b in in.
By screw clamp terminals or plug-in connector	40	1.57	40	1.57
By Faston connectors	45	1.77	40	1.57

### **Product datasheet**

#### XB5FVG6

**Technical Description** 

Electrical Composition Corresponding to Codes P1, P3, PF1, PR1 and PF2

Light block



#### **Electrical Composition Corresponding to Code P4**




#### Legend

Single contact



Double contact



Light block



Possible location

