# **Product datasheet**

Specifications





Wireless push button and nonconfigurable receiver with 10 colored caps, plastic, Ø22, 24 V DC

Local distributor code:

398126696 XB5RFB01

EAN Code: 3606480334443

#### Main

Range Of Product	Harmony XB5R
Product Or Component Type	Wireless and batteryless package
Device Short Name	XB5R
Head Material	Plastic
Frequency	2405 MHz for transmitter 2405 MHz for receiver
Emission Class	5M00G7W
Antenna Type	Omnidirectional

# Complementary

•	
Control Type	Wireless and batteryless push-button Ø 22 mm assembled on fixing collar
Type Of Receiver	Non-programmable receiver (1 relay)
[Us] Rated Supply Voltage	24 V DC
Kit Composition	1 transmitter
	1 set of caps
	1 receiver
	1 fixing collars
	1 diameter: 22 mm
	1 push-button head diameter: 22 mm
Communication Port Protocol	Zigbee conforming to IEEE 802.15.4
Max Power Consumption In W	1 mW
Number Of Channels	1
Modulation Technique	O-QPSK
Bandwidth	5 MHz
Antenna Gain	0 dBi
Customizable	No
Compatibility Code	XB5R
[Us] Rated Supply Voltage	24 V

#### **Environment**

Product Certifications	UL C-Tick GOST
	CSA
	CCC
Marking	CE

Standards	IEC 60947-5-1 CSA C22.2 No 14 IEC 60947-1 UL 508	
Radio Agreement	SRRC	
	ICASA	
	RSS	
	ANATEL	
	FCC	
	ARIB T66	

# **Packing Units**

•	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	9.300 cm
Package 1 Width	10.500 cm
Package 1 Length	10.800 cm
Package 1 Weight	195.000 g
Unit Type Of Package 2	S03
Number Of Units In Package 2	16
Package 2 Height	30.000 cm
Package 2 Width	30.000 cm
Package 2 Length	40.000 cm
Package 2 Weight	3.666 kg

# **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

### Well-being performance



Mercury Free



Rohs Exemption Information

Yes


#### **Certifications & Standards**


Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information

# XB5RFB01

### **Dimensions Drawings**


### Non-Programmable Receiver






### Wireless and Batteryless Pushbutton - Transmitter

#### With Plastic Pushbutton without Cap






e: panel thickness 1 to 6 mm / 0.039 to 0.24 in.

# XB5RFB01


# Mounting and Clearance

### Receiver Clearance



- (1) Drive
- (2) Power Supply or PLC

#### **Receiver Mounting**




# XB5RFB01

#### Connections and Schema

### Non-Programmable Receiver

#### Wiring Diagram



- (1) 125 mA fast-blow fuse
- (2) Imax = 3 A