

Product datasheet

Specifications



totalising counter - mechanical 6 digit display - 115 V AC

XBKT60000U11M

⚠ Discontinued on: 1 Oct 2021

EAN Code: 3389110893618

⚠ Discontinued

Main

Range Of Product	Zelio Count
Product Or Component Type	Totalising counter
Display Type	Mechanical
Size	50 x 60 mm
Display Digits	6 digit(s)
Counting Frequency	10 Hz
Reset	Manual
Counting Capacity	0...999999
Technology Type	Electromechanical

Complementary

[Us] Rated Supply Voltage	115 V AC 50/60 Hz Us +/- 10 %
Power Consumption In Va	2.75 VA
Backup Time	Permanent
Counting Mode	Adding
Input Function	Counting
Input Type	Contact
Mechanical Durability	10000000 cycles
Mounting Mode	Flush-mounted
Mounting Support	Panel mounting
Connections - Terminals	AMP lugs (connection box)
Height	50 mm
Net Weight	0.03 kg
Width	60 mm
Product Destination	Cable
Character Size	4 mm

Environment

Standards	EN 50082-2 EN 50081-2
Product Certifications	cUR

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Ip Degree Of Protection	IP40 conforming to EN/IEC 60529
Ambient Air Temperature For Operation	-10...50 °C
Ambient Air Temperature For Storage	-20...60 °C
Vibration Resistance	5 gn (f= 10...150 Hz) conforming to EN/IEC 60068-2-6
Shock Resistance	30 gn for 6 ms conforming to EN/IEC 60068-2-27
Electrical Shock Protection Class	Class II conforming to IEC 60536

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	8 cm
Package 1 Width	12.1 cm
Package 1 Length	15.6 cm
Package 1 Weight	191 g

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability



Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Well-being performance





 Mercury Free	
 Rohs Exemption Information	Yes
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Dimensions Drawings

Electromechanical and Electronic Totalizing Counters

Dimensions, Flush-Mounting

Counters Dimensions	Flush-Mounting
XBKT50000U•M, XBKT70000U•M	
<p>Technical drawing showing the dimensions of the XBKT50000U•M and XBKT70000U•M counters. The drawing includes a side view and a front view. The side view shows a width of 64.2 mm (2.53 in) and a height of 75 mm (2.95 in). The front view shows a width of 41.5 mm (1.63 in) and a height of 31 mm (1.22 in). The mounting hole diameter is 6 mm (0.24 in).</p>	<p>Technical drawing showing the dimensions of the XBKT50000U•M and XBKT70000U•M counters. The drawing includes a side view and a front view. The side view shows a width of 38.5 mm (1.52 in) and a height of 27 mm (1.06 in). The front view shows a width of 38.5 mm (1.52 in) and a height of 27 mm (1.06 in).</p>
XBKT60000U00M	
<p>Technical drawing showing the dimensions of the XBKT60000U00M counter. The drawing includes a side view and a front view. The side view shows a width of 33.7 mm (1.33 in) and a height of 42.3 mm (1.67 in). The front view shows a width of 30 mm (1.18 in) and a height of 20 mm (0.79 in). The mounting hole diameter is 6 mm (0.24 in).</p>	<p>Technical drawing showing the dimensions of the XBKT60000U00M counter. The drawing includes a side view and a front view. The side view shows a width of 27 mm (1.06 in) and a height of 14.2 mm (0.56 in). The front view shows a width of 27 mm (1.06 in) and a height of 14.2 mm (0.56 in).</p>
XBKT60000U1•M	
<p>Technical drawing showing the dimensions of the XBKT60000U1•M counter. The drawing includes a side view and a front view. The side view shows a width of 68 mm (2.68 in) and a height of 101.5 mm (3.99 in). The front view shows a width of 60 mm (2.36 in) and a height of 50 mm (1.97 in). The mounting hole diameter is 6 mm (0.24 in).</p>	<p>Technical drawing showing the dimensions of the XBKT60000U1•M counter. The drawing includes a side view and a front view. The side view shows a width of 55 mm (2.17 in) and a height of 28.5 mm (1.13 in). The front view shows a width of 55 mm (2.17 in) and a height of 28.5 mm (1.13 in). The mounting hole diameter is 6 mm (0.24 in).</p>
XBKT80000U00M	


Counters Dimensions	Flush-Mounting
 <p>Technical drawing of the XBKT60000U11M component showing side and front views. Dimensions are provided in mm and in.</p> <p>Side View Dimensions:</p> <ul style="list-style-type: none">Top: 88 mm (3.47 in.)Bottom: 94 mm (3.7 in.)Width: 3.7 in. <p>Front View Dimensions:</p> <ul style="list-style-type: none">Top: 38 mm (1.5 in.)Bottom: 50 mm (1.97 in.)Width: 60 mm (2.36 in.)	 <p>Technical drawing of the XBKT60000U11M component showing flush-mounting dimensions. Dimensions are provided in mm and in.</p> <p>Flush-Mounting Dimensions:</p> <ul style="list-style-type: none">Top: 2x24.3 mm (2x0.957 in.)Bottom: 29.5 mm (1.16 in.)Width: 55 mm (2.17 in.)
XBKT81030U33E	
 <p>Technical drawing of the XBKT81030U33E component showing side and front views. Dimensions are provided in mm and in.</p> <p>Side View Dimensions:</p> <ul style="list-style-type: none">Top: 32 mm (1.26 in.)Bottom: 40 mm (1.58 in.)Width: 1.58 in. <p>Front View Dimensions:</p> <ul style="list-style-type: none">Top: 24 mm (0.95 in.)Bottom: 48 mm (1.89 in.)	 <p>Technical drawing of the XBKT81030U33E component showing flush-mounting dimensions. Dimensions are provided in mm and in.</p> <p>Flush-Mounting Dimensions:</p> <ul style="list-style-type: none">Top: 22^{+0.3}_{-0.2} mm (0.87^{+0.012}_{-0.008} in.)Bottom: 45^{+0.3}_{-0.2} mm (1.77^{+0.012}_{-0.008} in.)
e: panel thickness, 1 mm < e < 2.5 mm / 0.039 in. < e < 0.098	

Connections and Schema


Wiring Diagrams of Electromechanical and Electronic Totalizing Counters

Counters with Mechanical Display

XBKT50000U••M, XBKT70000U00M




XBKT60000U1•M, XBKT80000U00M



Counters with LCD Display, Lithium Battery Supply

XBKT181030U33E

PNP Transistor, NPN Transistor




- 1: Keylock
- 2: 0 V
- 3: Count
- 4: Reset

Reset Key Locking Facility



- 1: Keylock
- 2: 0 V
- 3: Count
- 4: Reset

Volt-free Contact



- 1: Keylock
- 2: 0 V
- 3: Count
- 4: Reset

