



# module XPSAK - Emergency stop - 120 V AC

Local distributor code: 407168985

XPSAK351144

! Discontinued on: 3 Jul 2021

EAN Code: 3389110291698

## ① Discontinued

## Main

Range Of Product	Preventa Safety automation
Product Or Component Type	Preventa safety module
Safety Module Name	XPSAK
Safety Module Application	For emergency stop, switch, sensing mat/edges or safety light curtain monitoring
Function Of Module	Monitoring of a movable guard associated with 2 switches and automatic start Sensing mat and edges monitoring Proximity sensor monitoring Monitoring of electro-sensitive protection equipment (ESPE) Multiple emergency stop monitoring 2-channel wiring Monitoring of a movable guard Emergency stop with 2 NC contacts monitoring 2-channel wiring Emergency stop monitoring 1-channel wiring
Safety Level	Can reach PL e/category 4 conforming to EN/ISO 13849-1 Can reach SILCL 3 conforming to EN/IEC 62061
Safety Reliability Data	DC > 99 % conforming to EN/ISO 13849-1 MTTFd = 154.5 years conforming to EN/ISO 13849-1 PFHd = 7.39E-9 1/h conforming to EN/IEC 62061
Type Of Start	Configurable
Connections - Terminals	Captive screw clamp terminals, 1 x 0.141 x 2.5 mm² flexible with cable end, with double bezel Captive screw clamp terminals, 1 x 0.141 x 2.5 mm² solid with cable end, with double bezel Captive screw clamp terminals, 1 x 0.251 x 1.5 mm² flexible with cable end, with double bezel Captive screw clamp terminals, 1 x 0.251 x 2.5 mm² flexible with cable end, with double bezel Captive screw clamp terminals, 2 x 0.142 x 0.75 mm² flexible with cable end, with double bezel Captive screw clamp terminals, 2 x 0.142 x 0.75 mm² solid with cable end, with double bezel Captive screw clamp terminals, 2 x 0.252 x 1 mm² flexible with cable end, with double bezel Captive screw clamp terminals, 2 x 0.252 x 1 mm² flexible with cable end, with double bezel Captive screw clamp terminals, 2 x 0.52 x 1.5 mm² flexible with cable end, with double bezel
Output Type	Relay instantaneous opening, 3 NO circuit(s), volt-free
Number Of Additional Circuits	1 NC + 4 solid state outputs
[Us] Rated Supply Voltage	120 V AC - 1510 % 24 V DC - 1510 %

# Complementary

Synchronisation Time Between Inputs	2 or 4 s depending of wiring (automatic start) Unlimited (manual start)
Supply Frequency	50/60 Hz

Maximum Power Consumption In	6 VA AC	
Va		
Input Protection Type	Internal, electronic	
[Uc] Control Circuit Voltage	24 V DC	
Maximum Line Resistance	28 Ohm	
Breaking Capacity	180 VA holding AC-15 C300 relay output 1800 VA inrush AC-15 C300 relay output	
Breaking Capacity	1.5 A at 24 V (DC-13) time constant: 50 ms for relay output	
Output Thermal Current 6 A per relay for relay output		
[Ith] Conventional Free Air Thermal Current	18 A	
Associated Fuse Rating	4 A gG or gL for relay output conforming to EN/IEC 60947-5-1, DIN VDE 0660 part 200 6 A fast blow for relay output conforming to EN/IEC 60947-5-1, DIN VDE 0660 part 200	
Minimum Output Current	10 mA for relay output	
Minimum Output Voltage	17 V for relay output	
Maximum Response Time On Input Open	40 ms	
[Ui] Rated Insulation Voltage	300 V (pollution degree 2) conforming to IEC 60947-5-1 300 V (pollution degree 2) conforming to DIN VDE 0110 part 1	
[Uimp] Rated Impulse Withstand Voltage	4 kV overvoltage category III conforming to IEC 60947-5-1 4 kV overvoltage category III conforming to DIN VDE 0110 part 1	
Local Signalling	4 LEDs	
Current Consumption	30 mA at 24 V AC on power supply	
Mounting Support	35 mm symmetrical DIN rail	
Net Weight	0.4 kg	
Environment		
Standards	EN/ISO 13850	
	ENUE 0 00004 4	

Standards	EN/ISO 13850 EN/IEC 60204-1 EN 1088/ISO 14119 EN/IEC 60947-5-1
Product Certifications	UL TÜV CSA
Ip Degree Of Protection	IP20 (terminals) conforming to EN/IEC 60529 IP40 (enclosure) conforming to EN/IEC 60529
Ambient Air Temperature For Operation	-1055 °C
Ambient Air Temperature For Storage	-2585 °C

# **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	6.5 cm
Package 1 Width	12.5 cm
Package 1 Length	10.5 cm
Package 1 Weight	465.0 g
Unit Type Of Package 2	S02

Number Of Units In Package 2	12
Package 2 Height	15.0 cm
Package 2 Width	30.0 cm
Package 2 Length	40.0 cm
Package 2 Weight	6.09 kg

# **Contractual warranty**

Warranty 18 months



**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

## Well-being performance

<b>②</b>	Mercury Free	
	Rohs Exemption Information	Yes
	Pvc Free	

## **Certifications & Standards**

Circularity Profile	End of Life Information
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
<b>Environmental Disclosure</b>	Product Environmental Profile
China Rohs Regulation	China RoHS declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
Reach Regulation	REACh Declaration

# **Product datasheet**

## XPSAK351144

## **Dimensions Drawings**

## **Dimensions**

