Product data sheet

Specifications





Push-to-test pilot light, Harmony 9001SK, plastic, polycarbonate, fresnel lens, red, 30mm, LED red, 24...28V

9001SKT35LRR31

Product availability: Stock - Normally stocked in distribution facility

Price*: 197.00 USD

Main

Range Of Product	Harmony 9001SK
Product Or Component Type	Push-to-test pilot light
Device Short Name	9001SK
Type Of Operator	spring return
Operator Profile	Red projecting, unmarked

Complementary

e emprementar y	
Bezel Material	Plastic
Mounting Diameter	1.18 in (30 mm)
Shape Of Signaling Unit Head	Octagonal
Light Source	LED
Light Source	LED
Bulb Base	BA 9s
Light Block Supply	Direct
[Us] Rated Supply Voltage	24 V AC/DC
[Us] Rated Supply Voltage	2428 V AC/DC
Contacts Type And Composition	1 C/O
Connections - Terminals	Screw clamp terminals 1 x 0.222 x 1.5 mm ² EN/IEC 60947-1
Tightening Torque	7.08 lbf.in (0.8 N.m) EN/IEC 60947-1
Shape Of Screw Head	Cross slotted
Mechanical Durability	5000000 cycles
Operating Position	Any position
[Ui] Rated Insulation Voltage	250 V 3)EN/IEC 60947-1
[Uimp] Rated Impulse Withstand Voltage	2.5 kV EN/IEC 60947-1
Contacts Material	Silver alloy contacts
Positive Opening	Without
Short-Circuit Protection	10 A cartridge fuse EN/IEC 60947-5-1
[Ith] Conventional Free Air Thermal Current	10 A

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

[Icm] Rated Short-Circuit Making	12 kA 600 V AC-15, 7200 VA
Capacity	15 kA 480 V AC-15, 7200 VA
	30 kA 240 V AC-15, 7200 VA
	60 kA 120 V AC-15, 7200 VA
Rated Breaking Capacity	1.2 kA 600 V AC-15, 720 VA
	1.5 kA 480 V AC-15, 720 VA
	3 kA 240 V AC-15, 720 VA
	6 kA 120 V AC-15, 720 VA
	0.1 kA 600 V DC-13
	0.27 kA 250 V DC-13
	0.55 kA 125 V DC-13
Net Weight	0.43 lb(US) (0.195 kg)
Device Presentation	Complete product
Cap/Operator Or Lens Colour	Red
Lens Type	Fresnel
[Us] Rated Supply Voltage	2428 V
Light Source Colour	Red
Lens Material	Polycarbonate
Size	30 mm

Environment

Standards	JIS C 852 UL 508 JIS C8201-5-1 EN/IEC 60947-1 EN/IEC 60947-5-4 EN/IEC 60947-5-1 CSA C22.2 No 14 JIS C8201-1
Product Certifications	NEMA UL 508
Protective Treatment	TC
Ambient Air Temperature For Storage	-40158 °F (-4070 °C)
Ambient Air Temperature For Operation	-13158 °F (-2570 °C)
Vibration Resistance	7 gn 2500 Hz)IEC 60068-2-6
Shock Resistance	50 gn IEC 60068-2-27
Electrical Shock Protection Class	Class II IEC 61140
Ip Degree Of Protection	IP66 IEC 60529
Nema Degree Of Protection	NEMA 1 NEMA 12 NEMA 13 NEMA 2 NEMA 3 NEMA 3R NEMA 4 NEMA 4X

Ordering and shipping details

Category	US10CS121429
Discount Schedule	0CS1
Gtin	785901159803
Returnability	Yes
Country Of Origin	US

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2.40 in (6.096 cm)
Package 1 Width	4.50 in (11.43 cm)
Package 1 Length	2.00 in (5.08 cm)
Package 1 Weight	4.48 oz (127.006 g)

Contractual warranty

Warranty

18 months

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Reach Free Of Svhc
Toxic Heavy Metal Free
Mercury Free
Rohs Exemption Information Yes


Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Circularity Profile	End of Life Information
California Proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

Product data sheet

Dimensions Drawings

Dimensions




e panel thickness: 1 to 6 mm / 0.04 to 0.24 in.

Mounting and Clearance

Contact Block Mounting Position

Top and Rear views



(1) It is possible to mount up to 3 levels of contacts blocks (maximum of 6 contacts blocks)

- (2) Operator
- (3) Locating notch

(4) Side 1

(5) Side 2