

Product data sheet

Specifications



Circuit protector, Linergy, thermal magnetic overcurrent, track mount, 15.0A, 125VAC, 65VDC

9080GCB150

Product availability: Stock - Normally stocked in distribution facility

Price*: 72.00 USD

Main

| | |
|---------------------------|-------------------|
| Range Of Product | 9080GCB |
| Product Or Component Type | Circuit Protector |
| Trip Unit Type | Thermal-magnetic |
| Electrical Connection | Box lugs |

Complementary

| | |
|----------------------------|---|
| Protection Type | Overcurrent |
| Contact Operation | Trip-free |
| Device Application | Industrial Application |
| Line Rated Current | 15 A |
| Number Of Poles | 1P |
| Votlage Rating | 65 V DC 125 V AC |
| Wire Size | AWG 16...AWG 10 copper |
| Wire Stripping Length | 0.5 in (12.70 mm) |
| Terminal Tightening Torque | Control circuit 7 lbf.in (0.79 N.m) cage type connector |
| Terminal Rating | Factory wiring only |
| Operating Temperature | -22...140 °F (-30...60 °C) |
| Calibration Temperature | 70 °F (21 °C) |
| Mounting Support | 9080GH track 35 mm DIN rail |
| Height | 3.45 in (87.63 mm) |
| Width | 3.15 in (80.01 mm) |
| Depth | 0.5 in (12.70 mm) |

Environment

| | |
|------------------------|--|
| Product Certifications | CE CSA file 025490 class 3211 07 UL recognized E233026 CCN QVNU2 |
| Standards | CSA C22.2 No 235 UL 1077 DIN 57470 |

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Ordering and shipping details

| | |
|-------------------|--------------|
| Category | US10CP521703 |
| Discount Schedule | 0CP5 |
| Gtin | 785901481003 |
| Returnability | Yes |
| Country Of Origin | US |

Packing Units

| | |
|------------------------------|----------------------------|
| Unit Type Of Package 1 | PCE |
| Number Of Units In Package 1 | 1 |
| Package 1 Height | 1.00 in (2.54 cm) |
| Package 1 Width | 3.20 in (8.128 cm) |
| Package 1 Length | 3.70 in (9.398 cm) |
| Package 1 Weight | 2.56 oz (72.575 g) |
| Unit Type Of Package 2 | PAL |
| Number Of Units In Package 2 | 2000 |
| Package 2 Height | 40.00 in (101.6 cm) |
| Package 2 Width | 40.00 in (101.6 cm) |
| Package 2 Length | 48.00 in (121.92 cm) |
| Package 2 Weight | 338.00 lb(US) (153.314 kg) |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Well-being performance

| | | |
|---------------------------|----------------------------|---|
| ✓ | Reach Free Of Svhc | |
| ✓ | Mercury Free | |
| ✓ | Rohs Exemption Information | Yes |
| | | |
| Reach Regulation | | REACH Declaration |
| | | |
| Eu Rohs Directive | | Compliant with Exemptions |
| | | |
| China Rohs Regulation | | China RoHS declaration Product out of China RoHS scope. Substance declaration for your information. |
| | | |
| California Proposition 65 | | WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov |