

Product data sheet

Specifications



iEM3465 energy meter - BACnet - 1 DI - 1 DO - multi-tariff - LVCT

A9MEM3465

Product availability: Stock - Normally stocked in distribution facility

Price*: 832.57 USD

Main

Range	Acti9
Range Of Product	Acti9 iEM3000
Device Short Name	iEM3465
Product Or Component Type	Energy meter

Complementary

Poles Description	3P 1P + N 3P + N
Type Of Measurement	Active and reactive energy Active and reactive power Current Voltage
Metering Type	Active, reactive, apparent energy (signed, four quadrant)
Device Application	Sub billing Multi-tariff Partial meter
Accuracy Class	Class 0.5S active energy IEC 62053-22 Class 0.5S active energy ANSI C12.20
Input Type	Split core current transducer 0.333 V or 1 V
Rated Voltage	100...277 V +/- 20 % 173...480 V +/- 20 %
Network Frequency	60 Hz 50 Hz
Technology Type	Electronic
Display Type	LCD display
Sampling Rate	32 samples/cycle
Measurement Current	1...32767000 mA
Maximum Value Measured	99999999.9 kWh 99999999 MWh
Tariff Input	Tariff 4)
Communication Port Protocol	BACnet 9.6, 19.2, 38.4, 57.6, 76.8 kbauds
Communication Port Support	Screw terminal block RS485
Local Signalling	Green indicator light power ON Yellow flashing LED accuracy checking alarm overload
Number Of Inputs	1 digital 0...5 V/11...40 V 24 V DC

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Number Of Outputs	1 digital (static)
Output Voltage	5...40 V DC@50 mA
Mounting Mode	Clip-on
Mounting Support	DIN rail
Connections - Terminals	Current circuit screw terminals 0.01 in² (6 mm²) Voltage circuit screw terminals 0.00 in² (2.5 mm²) Input/output circuit screw terminals 0.00 in² (1.5 mm²) Communication screw terminals 0.00 in² (2.5 mm²)
Tightening Torque	Input/output circuit 4.43 lbf.in (0.5 N.m) Philips Voltage circuit 4.43 lbf.in (0.5 N.m) Philips Current circuit 7.08 lbf.in (0.8 N.m) pozidriv Communication 4.43 lbf.in (0.5 N.m) Philips
Wire Stripping Length	Input/output circuit: 0.24 in (6 mm) Voltage circuit: 0.31 in (8 mm) Current circuit: 0.31 in (8 mm) Communication: 0.28 in (7 mm)
Standards	BS EN 61326-1 IEC 61326-1 EN 61326-1 BS EN 61010-1:2010 EN 61010-1:2010 IEC 61010-1:2010 UL 61010-1:2010 BS EN 61010-2-30 IEC 61010-2-30 EN 61010-2-30 UL 61010-2-30 ANSI C12.20
Product Certifications	CE IEC 61010-1 safety) CE EN 61557-12 power monitor) CE EN/IEC 61326-1 EMC) UKCA BS EN 61010-1 safety) UKCA BS EN 61557-12 power monitor) UKCA BS EN 61326-1 EMC) CULus UL 61010-1 safety) CULus EN 61010-1 safety) KZ RCM

Environment

Ip Degree Of Protection	IP40 front panel: conforming to IEC 60529 IP20 body: conforming to IEC 60529
Ik Degree Of Protection	IK08
Pollution Degree	2
Relative Humidity	5...95 % 97 °F (36 °C)
Ambient Air Temperature For Operation	-13...158 °F (-25...70 °C) - IEC
Ambient Air Temperature For Storage	-40...185 °F (-40...85 °C)
Operating Altitude	< 9842.52 ft (3000 m)
Color	White
9 Mm Pitches	10
Width	3.54 in (90 mm)
Height	3.43 in (87 mm)
Depth	2.72 in (69 mm)

Ordering and shipping details

Category	US10PL109786
----------	--------------

Discount Schedule	0PL1
Gtin	3606480845239
Returnability	Yes
Country Of Origin	US

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.46 in (8.8 cm)
Package 1 Width	3.86 in (9.8 cm)
Package 1 Length	4.13 in (10.5 cm)
Package 1 Weight	12.66 oz (359 g)
Unit Type Of Package 2	S03
Number Of Units In Package 2	30
Package 2 Height	11.81 in (30 cm)
Package 2 Width	11.81 in (30 cm)
Package 2 Length	15.75 in (40 cm)
Package 2 Weight	25.32 lb(US) (11.483 kg)
Unit Type Of Package 3	P06
Number Of Units In Package 3	240
Package 3 Height	19.69 in (50 cm)
Package 3 Width	31.50 in (80 cm)
Package 3 Length	23.62 in (60 cm)
Package 3 Weight	221.26 lb(US) (100.364 kg)

Sustainability

Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency RoHS/REACH

Well-being performance

 Mercury Free

 RoHS Exemption Information [Yes](#)

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Circularity Profile	End of Life Information
California Proposition 65	WARNING: Cancer and Reproductive Harm - www.P65Warnings.ca.gov