Specifications





variable speed drive, Altivar 212, 55kW, 75hp, 480V, 3 phases, with EMC, IP21

ATV212HD55N4

Product availability: Stock - Normally stocked in distribution facility

Price*: 5,646.00 USD

Main

Device Short Name	ATV212		
Product Destination	Asynchronous motors		
Phase	3 phase		
Motor Power Kw	55 kW		
Maximum Horse Power Rating	75 hp		
Supply Voltage Limits	323528 V		
Supply Frequency	5060 Hz - 55 %		
Line Current	102.7 A 380 V 89 A 480 V		
Range Of Product	Altivar 212		
Product Or Component Type	Variable speed drive		
Product Specific Application	Pumps and fans in HVAC		
Communication Port Protocol	METASYS N2 BACnet LonWorks APOGEE FLN Modbus		
[Us] Rated Supply Voltage	380480 V - 1510 %		
Emc Filter	Class C2 EMC filter integrated		
Ip Degree Of Protection	IP21		

Complementary

·		
Apparent Power	76.3 kVA 380 V	
Continuous Output Current	116 A 380 V 116 A 460 V	
Maximum Transient Current	127.6 A 60 s	
Speed Drive Output Frequency	0.5200 Hz	
Speed Range	110	
Speed Accuracy	+/- 10 % of nominal slip 0.2 Tn to Tn	
Local Signalling	for DC bus energized 1 LED (red)	
Output Voltage	<= power supply voltage	
Isolation	Electrical between power and control	

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Type Of Cable	Without mounting kit 1 IEC cable 113 °F (45 °C), copper 90 °C / XLPE/EPR Without mounting kit 1 IEC cable 113 °F (45 °C), copper 70 °C / PVC With UL Type 1 kit 3 UL 508 cable 104 °F (40 °C), copper 75 °C / PVC		
Electrical Connection	VIA, VIB, FM, FLA, FLB, FLC, RY, RC, F, R, RES terminal 0.00 in ² (2.5 mm ²) / AWG 14		
	L1/R, L2/S, L3/T terminal 0.23 in ² (150 mm ²) 300 kcmil)		
Tightening Torque	5.31 lbf.in (0.6 N.m) VIA, VIB, FM, FLA, FLB, FLC, RY, RC, F, R, RES) 362.88 lbf.in (41 N.m), 360 lb.in L1/R, L2/S, L3/T)		
Supply	Internal supply for reference potentiometer (1 to 10 kOhm) 10.5 V DC +/- 5 %, <10 A overload and short-circuit protection Internal supply 24 V DC 2127 V), <200 A overload and short-circuit protection		
Sampling Duration	2 ms +/- 0.5 ms F discrete 2 ms +/- 0.5 ms R discrete 2 ms +/- 0.5 ms RES discrete 3.5 ms +/- 0.5 ms VIA analog 22 ms +/- 0.5 ms VIB analog		
Response Time	FM 2 ms +/- 0.5 ms analog FLA, FLC 7 ms +/- 0.5 ms discrete FLB, FLC 7 ms +/- 0.5 ms discrete RY, RC 7 ms +/- 0.5 ms discrete		
Accuracy	+/- 0.6 % VIA) for a temperature variation 60 °C +/- 0.6 % VIB) for a temperature variation 60 °C +/- 1 % FM) for a temperature variation 60 °C		
Linearity Error	VIA +/- 0.15 % of maximum value input VIB +/- 0.15 % of maximum value input FM +/- 0.2 % output		
Analogue Output Type	FM switch-configurable voltage 010 V DC 7620 Ohm 10 bits FM switch-configurable current 020 mA 970 Ohm 10 bits		
Discrete Output Type	Configurable relay logic FLA, FLC) NO - 100000 cycles Configurable relay logic FLB, FLC) NC - 100000 cycles Configurable relay logic RY, RC) NO - 100000 cycles		
Minimum Switching Current	3 mA 24 V DC configurable relay logic		
Maximum Switching Current	5 A 250 V AC resistive cos phi = 1 L/R = 0 ms FL, R) 5 A 30 V DC resistive cos phi = 1 L/R = 0 ms FL, R) 2 A 250 V AC inductive cos phi = $0.4 L/R = 7$ ms FL, R) 2 A 30 V DC inductive cos phi = $0.4 L/R = 7$ ms FL, R)		
Discrete Input Type	F programmable 24 V DC level 1 PLC 4700 Ohm R programmable 24 V DC level 1 PLC 4700 Ohm RES programmable 24 V DC level 1 PLC 4700 Ohm		
Discrete Input Logic	Positive logic (source) F, R, RES), <= 5 V, >= 11 V Negative logic (sink) F, R, RES), >= 16 V, <= 10 V		
Dielectric Strength	3535 V DC between earth and power terminals 5092 V DC between control and power terminals		
Insulation Resistance	>= 1 mOhm 500 V DC for 1 minute		
Frequency Resolution	Display unit 0.1 Hz Analog input 0.024/50 Hz		
Communication Service	Time out setting from 0.1 to 100 s Write multiple registers (16) 2 words maximum Write single register (06) Read holding registers (03) 2 words maximum Read device identification (43) Monitoring inhibitable		
Option Card	Communication card LonWorks		
Power Dissipation In W	1455 W		
Air Flow	131560.04 Gal/hr(US) (498 m3/h)		
Functionality	Mid		
Specific Application	HVAC		

Variable Speed Drive Application Selection	Building - HVAC compressor for scroll Building - HVAC fan Building - HVAC pump		
Motor Power Range Ac-3	55100 kW 380440 V 3 phase 55100 kW 480500 V 3 phase		
Motor Starter Type	Variable speed drive		
Discrete Output Number	2		
Analogue Input Number	2		
Analogue Input Type	VIA switch-configurable voltage 010 V DC 24 V max 30000 Ohm 10 bits VIB configurable voltage 010 V DC 24 V max 30000 Ohm 10 bits VIB configurable PTC probe 06 probes 1500 Ohm VIA switch-configurable current 020 mA 250 Ohm 10 bits		
Analogue Output Number	1		
Physical Interface	2-wire RS 485		
Connector Type	1 open style 1 RJ45		
Transmission Rate	9600 bps or 19200 bps		
Transmission Frame	RTU		
Number Of Addresses	1247		
Data Format	8 bits, 1 stop, odd even or no configurable parity		
Type Of Polarization	No impedance		
Asynchronous Motor Control Profile	Voltage/frequency ratio, automatic IR compensation (U/f + automatic Uo) Flux vector control without sensor, standard Voltage/frequency ratio, 5 points Voltage/frequency ratio - Energy Saving, quadratic U/f Voltage/frequency ratio, 2 points		
Torque Accuracy	+/- 15 %		
Transient Overtorque	120 % of nominal motor torque +/- 10 % 60 s		
Acceleration And Deceleration Ramps	Automatic based on the load Linear adjustable separately from 0.01 to 3200 s		
Motor Slip Compensation	Adjustable Automatic whatever the load Not available in voltage/frequency ratio motor control		
Switching Frequency	616 kHz adjustable 816 kHz with derating factor		
Nominal Switching Frequency	8 kHz		
Braking To Standstill	By DC injection		
Network Frequency	47.563 Hz		
Prospective Line Isc	22 kA		
Protection Type	Overheating protection drive Thermal power stage drive Short-circuit between motor phases drive Input phase breaks drive Overcurrent between output phases and earth drive Overvoltages on the DC bus drive Break on the control circuit drive Against exceeding limit speed drive Line supply overvoltage and undervoltage drive Line supply undervoltage drive Against input phase loss drive Thermal protection motor Motor phase break motor With PTC probes motor		
Width	12.60 in (320 mm)		

Height	24.80 in (630 mm)
Depth	11.42 in (290 mm)

Environment

3 IEC 61800-5-1			
IP20 on upper part without blanking plate on cover IEC 61800-5-1 IP20 on upper part without blanking plate on cover IEC 60529 IP21 IEC 61800-5-1			
IP21 IEC 60529 IP41 on upper part IEC 61800-5-1 IP41 on upper part IEC 60520			
IP41 on upper part IEC 60529			
1.5 mm 313 Hz)IEC 60068-2-6 1 gn 13200 Hz)EN/IEC 60068-2-8			
15 gn 11 ms IEC 60068-2-27			
Classes 3C1 IEC 60721-3-3 Classes 3S2 IEC 60721-3-3			
63.7 dB 86/188/EEC			
3280.849842.52 ft (10003000 m) limited to 2000 m for the Corner Grounded distribution network with current derating 1 % per 100 m <= 3280.84 ft (1000 m) without derating			
595 % without condensation IEC 60068-2-3 595 % without dripping water IEC 60068-2-3			
14104 °F (-1040 °C) without derating) 104122 °F (4050 °C) with derating factor)			
Vertical +/- 10 degree			
C-tick UL CSA			
NOM 117			
CE			
IEC 61800-3 environments 1 category C1 IEC 61800-3 environments 1 category C3 IEC 61800-5-1			
IEC 61800-3 IEC 61800-3 environments 2 category C1			
IEC 61800-3 IEC 61800-3 environments 1 category C2			
EN 55011 class A group 1			
IEC 61800-3 environments 1 category C1			
IEC 61800-3 environments 2 category C3 IEC 61800-3 environments 1 category C2			
IEC 61800-3 environments 2 category C3			
IEC 61800-3 environments 2 category C2			
UL Type 1 IEC 61800-3 category C2			
IEC 61800-3 category C3			
IEC 61800-5-1			
EN 61800-3 category C3 IEC 61800-3 environments 2 category C2			
IEC 61800-3 environments 1 category C3			
IEC 61800-3 category C2 IEC 61800-3 environments 2 category C1			
With heat sink			
Electrostatic discharge immunity test level 3 IEC 61000-4-2			
Radiated radio-frequency electromagnetic field immunity test level 3 IEC 61000-4-3 Electrical fast transient/burst immunity test level 4 IEC 61000-4-4			
1.2/50 μs - 8/20 μs surge immunity test level 3 IEC 61000-4-5			
Conducted radio-frequency immunity test level 3 IEC 61000-4-6 Voltage dips and interruptions immunity test IEC 61000-4-11			
Adjustable PI regulator			

Ambient Air Temperature For -13...158 °F (-25...70 °C) Storage

Ordering and shipping details

Category	US1CP4D22158	
Discount Schedule	CP4D	
Gtin	3606480322587	
Returnability	Yes	
Country Of Origin	CN	

Packing Units

0	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	18.50 in (47 cm)
Package 1 Width	19.69 in (50 cm)
Package 1 Length	30.31 in (77 cm)
Package 1 Weight	93.70 lb(US) (42.5 kg)

Contractual warranty

Warranty

18 months

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Yes

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance




Rohs Exemption Information

Certifications & Standards


Reach Regulation	REACh Declaration			
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)			
China Rohs Regulation	China RoHS declaration			
Environmental Disclosure	Product Environmental Profile			
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.			
Weee Circularity Profile				

Dimensions Drawings

Dimensions



EMC mounting plate (supplied with drive)



ATV212HD55N4

Mounting and Clearance


Mounting Recommendations

Clearance


Depending on the conditions in which the drive is to be used, its installation will require certain precautions and the use of appropriate accessories.

Install the unit vertically:

- Do not place it close to heating elements.
- Leave sufficient free space to ensure that the air required for cooling purposes can circulate from bottom to the top of the unit.



Mounting Types




By removing the protective blanking cover from the top of the drive, the degree of protection for the drive becomes IP21. The protective blanking cover may vary according to the drive model, see opposite.

ATV212HD55N4

Specific Recommendations for Mounting in an Enclosure

To help ensure proper air circulation in the drive:

- Fit ventilation grilles.
- Check that there is sufficient ventilation. If there is not, install a forced ventilation unit with a filter. The openings and/or fans must provide a flow rate at least equal to that of the drive fans (refer to the product



characteristics).

- Use special filters with UL Type 12/IP54 protection. •
- Remove the blanking cover from the top of the drive. .


Sealed Metal Enclosure (IP54 Degree of Protection)

The drive must be mounted in a dust and damp proof enclosure in certain environmental conditions, such as dust, corrosive gases, high humidity with risk of condensation and dripping water, splashing liquid, etc. This enables the drive to be used in an enclosure where the maximum internal temperature reaches 50°C.

Connections and Schema

Recommended Wiring Diagram

3-Phase Power Supply



- A1: ATV 212 drive
- KM1: Contactor
- Q1: Circuit breaker
- Q2: GV2 L rated at twice the nominal primary current of T1
- Q3: GB2CB05
- S1, S2: XB4 B or XB5 A pushbuttons
- T1: 100 VA transformer 220 V secondary
- (1) Fault relay contacts for remote signalling of the drive status
- (2) Connection of the common for the logic inputs depends on the positioning of the switch (Source, PLC, Sink)
- (3) Reference potentiometer SZ1RV1202

NOTE: All terminals are located at the bottom of the drive. Install interference suppressors on all inductive circuits near the drive or connected on the same circuit, such as relays, contactors, solenoid valves, fluorescent lighting, etc.


Switches (Factory Settings)

Voltage/current selection for analog I/O (VIA and VIB)

VIA U		1
VIB U		PTC


Voltage/current selection for analog I/O (FM)







Other Possible Wiring Diagrams


Logic Inputs According to the Position of the Logic Type Switch







2-wire control




F: Forward

R: Preset speed

(2) ATV 212 control terminals

3-wire control



F: Forward


R: Stop

RES: Reverse

(2) ATV 212 control terminals

PTC probe


ATV212HD55N4




- (2) ATV 212 control terminals
- (3) Motor

Analog Inputs

Voltage analog inputs



Analog input configured for current: 0-20 mA, 4-20 mA, X-Y mA




- (2) ATV 212 control terminals
- (5) Source 0-20 mA, 4-20 mA, X-Y mA

Analog input VIA configured as positive logic input ("Source" position)



(2) ATV 212 control terminals

Analog input VIA configured as negative logic input ("Sink" position)



(2) ATV 212 control terminals


ATV212HD55N4

Performance Curves

Derating Curves

The derating curves for the drive nominal current (In) depend on the temperature, the switching frequency and the mounting type (A, B or C).

For intermediate temperatures (45°C for example), interpolate between 2 curves.



X Switching frequency