Product data sheet

Specifications

Green Premium"



analog output module Modicon Quantum - 4 O

140AVO02000

Discontinued on: Dec 31, 2022
To be end-of-service on: Dec 31, 2030

(!) Discontinued - Service only

Product availability: Non-Stock - Not normally stocked in distribution facility

Main

Range Of Product	Modicon Quantum automation platform
Product Or Component Type	Analogue output module

Complementary

Analogue Output Number	4
Addressing Requirement	4 output words
Analogue Output Range	+/- 10 V >= 1000 Ohm bipolar voltage +/- 5 V >= 500 Ohm bipolar voltage 010 V >= 1000 Ohm unipolar voltage
	05 V >= 500 Ohm unipolar voltage
Analogue Output Resolution	12 bits
Analogue Output Current	-1010 mA
Source Resistance	0.1 Ohm
Maximum Cable Distance Between Devices	1312.34 ft (400 m)
Absolute Accuracy Error	+/- 0.15 % of full scale 77 °F (25 °C)
Linearity	+/- 1 LSB
Accuracy Drift According To Temperature	0.003 % of full scale/°C unipolar 0.004 % of full scale/°C bipolar 0.005 % of full scale/°C maximum unipolar 0.007 % of full scale/°C maximum bipolar
Isolation Between Channels	500 V for 1 minute 4763 Hz AC
Isolation Between Channels And Bus	780 V for 1 minute AC
Update Time	3 ms
Setting Time	700 μs to +/- 0.1 % of the final value maximum
Bus Current Requirement	700 mA
Maximum Power Dissipation In W	4.5 W
Associated Fuse Rating	0.063 mA 3 AG fast blow 250 V
Marking	CE
Local Signalling	for bus communication is present (Active) 1 LED (green) for external fault 1 LED (red) for channel is turned on 4 LEDs (green) for channel fault 4 LEDs (red)
Module Format	Standard

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Net Weight

0.66 lb(US) (0.3 kg)

Environment

Product Certifications	FM Class 1 Division 2 cUL
Standards	UL 508 CSA C22.2 No 142
Resistance To Electromagnetic Fields	9.14 V/m (10 V/m) 802000 MHz IEC 801-3
Ambient Air Temperature For Operation	32140 °F (060 °C)
Ambient Air Temperature For Storage	-40185 °F (-4085 °C)
Relative Humidity	95 % without condensation
Operating Altitude	<= 16404.2 ft (5000 m)

Ordering and shipping details

Category	US1PC2118155
Discount Schedule	PC21
Gtin	3595861126626
Returnability	No
Country Of Origin	FR

Packing Units

-	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	1.97 in (5.0 cm)
Package 1 Width	6.50 in (16.5 cm)
Package 1 Length	12.40 in (31.5 cm)
Package 1 Weight	16.47 oz (467.0 g)
Unit Type Of Package 2	S03
Number Of Units In Package 2	7
Package 2 Height	11.81 in (30.0 cm)
Package 2 Width	11.81 in (30.0 cm)
Package 2 Length	15.75 in (40.0 cm)
Package 2 Weight	7.31 lb(US) (3.318 kg)

Contractual warranty

Warranty

18 months

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



RoHS/REACh

Well-being performance

Reach Free Of Svhc

Mercury Free

Rohs Exemption Information Yes

Certifications & Standards


Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Circularity Profile	End of Life Information
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

Product data sheet

Dimensions Drawings

Racks for Modules Mounting

Dimensions of Modules and Racks




- (1) 2 slots
- (2) 3 slots
- (3) 4 slots
- (4) 6 slots
- (5) 10 slots
- (6) 16 slots

Connections and Schema

Analog Output 4-Channel Voltage Module

Wiring Diagram



N/C Not Connected

External Wiring Recommendation

- 1. Master override is an input connected via an internal relay contact to the output when the module is not active. If connected to an external source, the master override input must be fused by a 1/16 A fuse.
- 2. If the master override is not connected to an external source, then it must be connected to common of that channel.The master override relay transition time is typically 2 ms.
- 3. The master override inputs must be from an external supply with a source impedance of <200 Ω or tied to system common. These inputs for channels that are in use should not be allowed to float and may be unique for each.