Product data sheet

Specification





Circuit breaker, PowerPacT B, 35A, 1 pole, 600Y/347VAC, 14kA, terminal nut, thermal magnetic, 80%

BDF16035

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 343.00 USD

Main

Range	PowerPact
Product Name	PowerPact B
Device Short Name	BD 035
Product Or Component Type	Circuit breaker
Device Application	Distribution

Complementary

Line Rated Current	35 A
Number Of Poles	1P
Protected Poles Description	1t
Control Type	Toggle
Breaking Capacity Code	D
Breaking Capacity	25 kA 208Y/120 V AC 50/60 Hz UL 489 25 kA 240 V AC 50/60 Hz UL 489 18 kA 480Y/277 V AC 50/60 Hz UL 489 10 kA 125 V DC 50/60 Hz UL 489 14 kA 600/347 V AC 50/60 Hz UL 489
[Ue] Rated Operational Voltage	240 V AC 50/60 Hz UL 489
Network Frequency	50/60 Hz
[Ics] Rated Service Breaking Capacity	25 kA 220240 V AC 50/60 Hz IEC 60947-2
[Uimp] Rated Impulse Withstand Voltage	8 kV IEC 60947-2
Trip Unit Technology	Thermal-magneticTM-D,
Continuous Current Rating	80 %
[Ui] Rated Insulation Voltage	800 V IEC 60947-2
Trip Unit Name	TM-D
Suitability For Isolation	Yes IEC 60947-2
Utilisation Category	Category A
Mechanical Durability	15000 cycles IEC 947-1 Annex F ed 5.2
Electrical Durability	10000 cycles IEC 947-1 Annex K ed 5.2 In
Connection Pitch	1.06 in (27 mm)

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Awg Gauge	AWG 14AWG 8 aluminium/copper AWG 6AWG 3/0 aluminium/copper	
Mounting Mode	Clip-on 35 mm symmetrical DIN rail) By screws plate)	
Electrical Connection	Terminal nut, ON and OFF end	
Tightening Torque	44.25 lbf.in (5 N.m) 0.000.02 in² (2.516 mm²) (AWG 14AWG 4) 79.66 lbf.in (9 N.m) 0.040.15 in² (2595 mm²) (AWG 3AWG 3/0)	
Power Wire Stripping Length	0.79 in (20 mm)	
Color	Gray RAL 7016)	
9 Mm Pitches	3	
	5.39 in (137 mm)	
Width	1.06 in (27 mm)	
Depth	3.15 in (80 mm)	
Net Weight	1.01 lb(US) (0.46 kg)	
Quantity Per Set	Set of 1	
Circuit Breaker Application	HACR rated	

Environment

Quality Labels	CE
Standards	EN/IEC 60947-2 UL 489 GB 14048.2 EN/IEC 60947-5-1 NEMA AB1 NMX J-266 CSA C22.2 No 5
Product Certifications	UL IEC CCC EAC CSA NOM
Ip Degree Of Protection	Front cover IP40 IEC 60529
Ik Degree Of Protection	IK07 conforming to IEC 62262
Pollution Degree	3 IEC 60947-1
Ambient Air Temperature For Operation	-13158 °F (-2570 °C)
Ambient Air Temperature For Storage	-58185 °F (-5085 °C)
Operating Altitude	6561.68 ft (2000 m) without derating 5000 m with derating

Ordering and shipping details

Category	US10DE201130
Discount Schedule	0DE2
Gtin	3606481148643
Returnability	Yes
Country Of Origin	MX

Packing Units

Unit Type Of Package 1	PCE		

Number Of Units In Package 1	1
Package 1 Height	1.40 in (3.556 cm)
Package 1 Width	4.70 in (11.938 cm)
Package 1 Length	7.50 in (19.05 cm)
Package 1 Weight	16.00 oz (453.6 g)

Sustainability Green Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

Ø	Mercury Free	
Ø	Rohs Exemption Information	Yes
⊘	Pvc Free	
Ø	Halogen Free Product	

Certifications & Standards

Reach Regulation	REACh Declaration	
Eu Rohs Directive	Compliant with Exemptions	
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.	
Environmental Disclosure	Product Environmental Profile	
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.	
Circularity Profile	No need of specific recycling operations	
California Proposition 65	WARNING: This product can expose you to chemicals including: DINP, which is known to the State of California to cause cancer, and DIDP, which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov	