# **Product data sheet**

Specifications





## Circuit breaker, PowerPacT B, 50A, 1 pole, 600Y/347VAC, 14kA, terminal nut, thermal magnetic, 80%

BDF16050

Product availability: Non-Stock - Not normally stocked in distribution facility

#### Main

Range	PowerPact
Product Name	PowerPact B
Device Short Name	BD 050
Product Or Component Type	Circuit breaker
Device Application	Distribution

### alamantary

Complementary	
Line Rated Current	50 A
Number Of Poles	1P
Protected Poles Description	1t
Control Type	Toggle
Breaking Capacity Code	D
Breaking Capacity	25 kA 208Y/120 V AC 50/60 Hz UL 489 25 kA 240 V AC 50/60 Hz UL 489 18 kA 480Y/277 V AC 50/60 Hz UL 489 10 kA 125 V DC 50/60 Hz UL 489 14 kA 600/347 V AC 50/60 Hz UL 489
[Ue] Rated Operational Voltage	240 V AC 50/60 Hz UL 489
Network Frequency	50/60 Hz
[Ics] Rated Service Breaking Capacity	25 kA 220240 V AC 50/60 Hz IEC 60947-2
[Uimp] Rated Impulse Withstand Voltage	8 kV IEC 60947-2
Trip Unit Technology	Thermal-magneticTM-D,
Continuous Current Rating	80 %
[Ui] Rated Insulation Voltage	800 V IEC 60947-2
Trip Unit Name	TM-D
Suitability For Isolation	Yes IEC 60947-2
Utilisation Category	Category A
Mechanical Durability	15000 cycles IEC 947-1 Annex F ed 5.2
Electrical Durability	10000 cycles IEC 947-1 Annex K ed 5.2 In
Connection Pitch	1.06 in (27 mm)
Awg Gauge	AWG 14AWG 8 aluminium/copper AWG 6AWG 3/0 aluminium/copper

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Mounting Mode	Clip-on 35 mm symmetrical DIN rail) By screws plate)
Electrical Connection	Terminal nut, ON and OFF end
Tightening Torque	44.25 lbf.in (5 N.m) 0.000.02 in² (2.516 mm²) (AWG 14AWG 4) 79.66 lbf.in (9 N.m) 0.040.15 in² (2595 mm²) (AWG 3AWG 3/0)
Power Wire Stripping Length	0.79 in (20 mm)
Color	Gray RAL 7016)
9 Mm Pitches	3
Height	5.39 in (137 mm)
Width	1.06 in (27 mm)
Depth	3.15 in (80 mm)
Net Weight	1.01 lb(US) (0.46 kg)
Quantity Per Set	Set of 1
Circuit Breaker Application	HACR rated

#### Environment

Quality Labels	CE
Standards	EN/IEC 60947-2
	GB 14048.2
	UL 489
	NMX J-266
	CSA C22.2 No 5
	NEMA AB1
	EN/IEC 60947-5-1
Product Certifications	UL
	IEC
	CCC
	EAC
	CSA
	NOM
Ip Degree Of Protection	Front cover IP40 IEC 60529
Ik Degree Of Protection	IK07 conforming to IEC 62262
Pollution Degree	3 IEC 60947-1
Ambient Air Temperature For Operation	-13158 °F (-2570 °C)
Ambient Air Temperature For Storage	-58185 °F (-5085 °C)
Operating Altitude	6561.68 ft (2000 m) without derating 5000 m with derating

## Ordering and shipping details

Category	01130 - BD UNIT MOUNT BREAKER/SWITCH
Discount Schedule	DE2
Gtin	3606481148674
Returnability	No
Country Of Origin	MX

# **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1

Package 1 Height	1.40 in (3.556 cm)
Package 1 Width	4.70 in (11.938 cm)
Package 1 Length	7.50 in (19.05 cm)
Package 1 Weight	16.00 oz (453.592 g)

### Sustainability Screen

**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

#### Well-being performance

Mercury Free	
Rohs Exemption Information	Yes
Pvc Free	
Halogen Free Product	

#### **Certifications & Standards**

REACh Declaration
Compliant with Exemptions
China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
Product Environmental Profile
The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
No need of specific recycling operations
WARNING: This product can expose you to chemicals including: DINP, which is known to the State of California to cause cancer, and DIDP, which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov