Product data sheet

Specifications





(!) Discontinued - Service only

RIO drop adaptor module Modicon Quantum - 2 connectors with redundant cable

140CRA93200

! Discontinued on: Jan 15, 2023

! To be end-of-service on: Dec 31, 2030

Product availability: Non-Stock - Not normally stocked in distribution facility

Main

Range Of Product	Modicon Quantum automation platform	
Product Or Component Type	RIO drop adaptor module	

Complementary

Product Compatibility	Quantum	
Maximum Number Of I/O Expansion Module	27	
Type Of Cable	75 Ohm coaxial	
Transmission Rate	1544 Mbit/s	
Dynamic Range	35 dB	
Isolation Voltage	500 V DC coaxial center and ground	
Electrical Connection	2 female connectors F, elbowed with redundant cable	
Diagnostics Startup	Power up and runtime RAM address/data Executive checksum	
Power Dissipation In W	3.8 W 2 channels	
Bus Current Requirement	750 mA 2 channels	
Module Format	Standard	

Environment

Standards	UL 508 CUL CSA C22.2 No 142
Resistance To Electrostatic Discharge	4 kV contact IEC 801-2 8 kV on air IEC 801-2
Resistance To Electromagnetic Fields	9.14 V/m (10 V/m) 801000 MHz IEC 801-3
Ambient Air Temperature For Operation	32140 °F (060 °C)
Ambient Air Temperature For Storage	-40185 °F (-4085 °C)
Relative Humidity	95 % without condensation
Operating Altitude	<= 16404.2 ft (5000 m)

Ordering and shipping details

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Category	US1PC2118155	
Discount Schedule	PC21	
Gtin	3595861133785	
Returnability	No	
Country Of Origin	FR	

Packing Units

•	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	1.97 in (5.000 cm)
Package 1 Width	6.50 in (16.500 cm)
Package 1 Length	12.40 in (31.500 cm)
Package 1 Weight	19.22 oz (545.000 g)
Unit Type Of Package 2	S03
Number Of Units In Package 2	7
Package 2 Height	11.81 in (30.000 cm)
Package 2 Width	11.81 in (30.000 cm)
Package 2 Length	15.75 in (40.000 cm)
Package 2 Weight	9.48 lb(US) (4.299 kg)

Contractual warranty

Warranty 18 months



Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



RoHS/REACh

Well-being performance

⊘	Reach Free Of Svhc	
②	Mercury Free	
②	Rohs Exemption Information	Yes


Certifications & Standards

Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
	EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Circularity Profile	End of Life Information
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

Dimensions Drawings

Racks for Modules Mounting

Dimensions of Modules and Racks



- (1) 2 slots
- (2) 3 slots
- (3) 4 slots
- (4) 6 slots
- (5) 10 slots
- (6) 16 slots