Product data sheet

Specifications

Circuit breaker, PowerPacT B, 60A, 1 pole, 600Y/347VAC, 14kA, terminal nut, thermal magnetic, 80%

BDF16060

Product availability: Non-Stock - Not normally stocked in distribution facility

Main

Range	PowerPact
Product Name	PowerPact B
Device Short Name	BD 060
Product Or Component Type	Circuit breaker
Device Application	Distribution

Complementary

Line Rated Current	60 A
Number Of Poles	1P
Protected Poles Description	1t
Control Type	Toggle
Breaking Capacity Code	D
Breaking Capacity	25 kA 208Y/120 V AC 50/60 Hz UL 489 25 kA 240 V AC 50/60 Hz UL 489 18 kA 480Y/277 V AC 50/60 Hz UL 489 10 kA 125 V DC 50/60 Hz UL 489 14 kA 600/347 V AC 50/60 Hz UL 489
[Ue] Rated Operational Voltage	240 V AC 50/60 Hz UL 489
Network Frequency	50/60 Hz
[Ics] Rated Service Breaking Capacity	25 kA 220...240 V AC 50/60 Hz IEC 60947-2
[Uimp] Rated Impulse Withstand Voltage	8 kV IEC 60947-2
Trip Unit Technology	Thermal-magneticTM-D,
Continuous Current Rating	80 %
[Ui] Rated Insulation Voltage	800 V IEC 60947-2
Trip Unit Name	TM-D
Suitability For Isolation	Yes IEC 60947-2
Utilisation Category	Category A
Mechanical Durability	15000 cycles IEC 947-1 Annex F ed 5.2
Electrical Durability	10000 cycles IEC 947-1 Annex K ed 5.2 In
Connection Pitch	1.06 in (27 mm)
Awg Gauge	AWG 14...AWG 8 aluminium/copper AWG 6...AWG 3/0 aluminium/copper

Price is “List Price” and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Mounting Mode	Clip-on 35 mm symmetrical DIN rail) By screws plate)
Electrical Connection	Terminal nut, ON and OFF end
Tightening Torque	44.25 lbf.in (5 N.m) 0.00…0.02 in² (2.5…16 mm²) (AWG 14...AWG 4) 79.66 lbf.in (9 N.m) 0.04…0.15 in² (25…95 mm²) (AWG 3...AWG 3/0)
Power Wire Stripping Length	0.79 in (20 mm)
Color	Gray RAL 7016)
9 Mm Pitches	3
Height	5.39 in (137 mm)
Width	1.06 in (27 mm)
Depth	3.15 in (80 mm)
Net Weight	1.01 lb(US) (0.46 kg)
Quantity Per Set	Set of 1
Circuit Breaker Application	HACR rated

Environment

Quality Labels	CE
Standards	NMX J-266 NEMA AB1 EN/IEC 60947-2 GB 14048.2 CSA C22.2 No 5 EN/IEC 60947-5-1 UL 489
Product Certifications	UL IEC CCC EAC CSA NOM
Ip Degree Of Protection	Front cover IP40 IEC 60529
Ik Degree Of Protection	IK07 conforming to IEC 62262
Pollution Degree	3 IEC 60947-1
Ambient Air Temperature For Operation	-13…158 °F (-25…70 °C)
Ambient Air Temperature For Storage	-58…185 °F (-50…85 °C)
Operating Altitude	6561.68 ft (2000 m) without derating 5000 m with derating

Ordering and shipping details

Category	01130 - BD UNIT MOUNT BREAKER/SWITCH
Discount Schedule	DE2
Gtin	3606481148681
Returnability	No
Country Of Origin	MX

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1

Package 1 Height	1.40 in (3.556 cm)
Package 1 Width	4.70 in (11.938 cm)
Package 1 Length	7.50 in (19.05 cm)
Package 1 Weight	16.00 oz (453.592 g)

Sustainability

Green Premium^{TM} label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO_2 products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >

Transparency

RoHS/REACh

Well-being performance

Mercury Free	
Rohs Exemption Information	Yes
Pvc Free	
Halogen Free Product	

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: DINP, which is known to the State of California to cause cancer, and DIDP, which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov