

# Product data sheet

Specifications



## Enercept power monitoring - unit basic 400 A medium

3020B043S

! Discontinued

### Main

Range	PowerLogic
Product Name	PowerLogic Enercept
Device Short Name	Enercept
Product Or Component Type	Power meter
Device Application	Power monitoring Sub billing
Variant	Basic
Power Monitoring	Basic instrumentation
Type Of Measurement	Active energy Active power
[Us] Rated Supply Voltage	208...480 V AC 50/60 Hz
Network Frequency	60 Hz 50 Hz

### Complementary

Current Transformer Type	Split core balance
Current Transformer Input	Split core CT 0...400 A
Measurement Voltage	208...480 V
Measurement Accuracy	+/- 1 % 10...100 %
Communication Port Protocol	Modbus RTU
Communication Port Support	RS485
Communication Network Type	Modbus RTU
Mounting Mode	Direct

### Environment

Ambient Air Temperature For Operation	32...140 °F (0...60 °C)
Relative Humidity	95 %
Product Certifications	CUL UL
Width	Internal 2.44 in (62 mm) External 5.94 in (151 mm)
Depth	1.18 in (30 mm)

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Height	Internal 2.87 in (73 mm)
	External 5.20 in (132 mm)
Net Weight	3.31 lb(US) (1.5 kg)

## Ordering and shipping details

Category	09791-POWERLOGIC ENERCEPT POWER METER
Discount Schedule	PL1
Gtin	00785901985853
Returnability	No
Country Of Origin	US

## Contractual warranty

Warranty	18 months
----------	-----------

# Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Eu Rohs Directive	Not compliant
-------------------	---------------

---