Product data sheet

Specifications





servo motor BMH, Lexium 32, 1.4Nm, 8000rpm, keyed shaft, with brake, IP54, 128 multiturn encoder

BMH0701T12F2A

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 2,287.50 USD

Main

Product Or Component Type	Comic modes							
	Servo motor							
Device Short Name	ВМН							
Maximum Mechanical Speed	8000 rpm							
Continuous Stall Torque	12.39 lbf.in (1.4 N.m) LXM32.U90M2 3 A, 230 V, single phase 12.39 lbf.in (1.4 N.m) LXM32.D18M2 6 A, 115 V, single phase							
Peak Stall Torque	35.40 lbf.in (4 N.m) LXM32.U90M2 3 A, 230 V, single phase 37.17 lbf.in (4.2 N.m) LXM32.D18M2 6 A, 115 V, single phase							
Nominal Output Power	450 W LXM32.U90M2 3 A, 230 V, single phase 350 W LXM32.D18M2 6 A, 115 V, single phase							
Nominal Torque	9.74 lbf.in (1.1 N.m) LXM32.U90M2 3 A, 230 V, single phase 11.95 lbf.in (1.35 N.m) LXM32.D18M2 6 A, 115 V, single phase							
Nominal Speed	4000 rpm LXM32.U90M2 3 A, 230 V, single phase 2500 rpm LXM32.D18M2 6 A, 115 V, single phase							
Product Compatibility	LXM32.D18M2 115 V single phase LXM32.U90M2 230 V single phase							
Shaft End	Keyed							
Ip Degree Of Protection	IP54 standard							
Speed Feedback Resolution	131072 points/turn x 4096 turns							
Holding Brake	With							
Mounting Support	International standard flange							
Electrical Connection	Rotatable right-angled connectors							

Complementary

Range Compatibility	Lexium 32
[Us] Rated Supply Voltage	240 V
Phase	Three phase
Continuous Stall Current	2.85 A
Continuous Power	1.05 W
Maximum Current Irms	9.6 A LXM32.D18M2 9.6 A LXM32.U90M2
Maximum Permanent Current	9.56 A
Second Shaft	Without second shaft end
Shaft Diameter	0.43 in (11 mm)

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Shaft Length	0.91 in (23 mm)						
Key Width	0.71 in (18 mm)						
Feedback Type	Multiturn SinCos Hiperface						
Holding Torque	26.55 lbf.in (3 N.m) holding brake						
Motor Flange Size	2.76 in (70 mm)						
Number Of Motor Stacks	1						
Torque Constant	0.49 N.m/A 248 °F (120 °C)						
Back Emf Constant	31.17 V/krpm 248 °F (120 °C)						
Number Of Motor Poles	10						
Rotor Inertia	0.7 kg.cm²						
Stator Resistance	3.2 Ohm 68 °F (20 °C)						
Stator Inductance	9.1 mH 68 °F (20 °C)						
Stator Electrical Time Constant	2.8 ms 68 °F (20 °C)						
Maximum Radial Force Fr	660 N 1000 rpm 520 N 2000 rpm 460 N 3000 rpm 410 N 4000 rpm 380 N 5000 rpm 360 N 6000 rpm						
Maximum Axial Force Fa	0.2 x Fr						
Brake Pull-In Power	7 W						
Type Of Cooling	Natural convection						
Length	6.34 in (161 mm)						
Centring Collar Diameter	2.36 in (60 mm)						
Centring Collar Depth	0.10 in (2.5 mm)						
Number Of Mounting Holes	4						
Mounting Holes Diameter	0.22 in (5.5 mm)						
Circle Diameter Of The Mounting Holes	3.23 in (82 mm)						
Net Weight	5.73 lb(US) (2.6 kg)						

Ordering and shipping details

Category	US1PC5318282
Discount Schedule	PC53
Gtin	3606485194127
Returnability	No
Country Of Origin	DF

Packing Units

Unit Type Of Package 1	PCE					
Number Of Units In Package 1	1					
Package 1 Height	4.53 in (11.500 cm)					
Package 1 Width	7.68 in (19.500 cm)					
Package 1 Length	15.55 in (39.500 cm)					

Package 1 Weight	5.94 lb(US) (2.693 kg)					
Unit Type Of Package 2	P06					
Number Of Units In Package 2	4					
Package 2 Height	29.53 in (75.000 cm)					
Package 2 Width	31.50 in (80.000 cm)					
Package 2 Length	23.62 in (60.000 cm)					
Package 2 Weight	47.12 lb(US) (21.372 kg)					

Contractual warranty

Warranty 18 months

Sustainability Screen Premium*

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

Ø	Mercury Free	
	Rohs Exemption Information	Yes
②	Pvc Free	

Certifications & Standards


Reach Regulation	REACh Declaration						
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)						
China Rohs Regulation	China RoHS declaration						
Environmental Disclosure	Product Environmental Profile						
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.						
Circularity Profile	No need of specific recycling operations						
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov						

BMH0701T12F2A

Dimensions Drawings

Servo Motors Dimensions

Example with Straight Connectors



- a: Power supply for servo motor brake
- b: Power supply for servo motor encoder
- (1) Shaft end, keyed slot (optional)

Dimensions in mm

Straight Rotatable angled connectors		c (without c (with		c1 c2	c2	c2 c3	h	h1	Ø	Ø1 for		
b1	b2	b1	b2	brake)	brake)							screws
39.5	25.5	39.5	39.5	122	161	23	18	2.5	4 h9	12.5 ⁺⁰ _	11 k6	M4 x 14

Dimensions in in.

_	Straight connectors		ble ctors	c (without	c (with brake)	c1	c2	сЗ	h	h1	Ø	Ø1 for screws
b1	b2	b1	b2	brake)								
1.55	1	1.55	1.55	4.80	6.33	0.90	0.70	0.09	0.16 h9	0.49 ⁺⁰ _ 0.0051	0.43 k6	M4 x 0.55

Product data sheet


BMH0701T12F2A

Performance Curves

115 V Single-Phase Supply Voltage

Torque/Speed Curves

Servo motor with LXM32•D18M2 servo drive




- X Speed in rpm
- Y Torque in Nm
- 1 Peak torque
- 2 Continuous torque

230 V Single-Phase Supply Voltage

Torque/Speed Curves

Servo motor with LXM32•U90M2 servo drive



- X Speed in rpm
- Y Torque in Nm
- 1 Peak torque
- 2 Continuous torque