# Product data sheet

Specifications





# servo motor BMH, Lexium 32, 3.4Nm, 8000rpm, keyed shaft, without brake, IP65, IP67, 16bit encoder, 3 phases

BMH0703P36A2A

Product availability: Non-Stock - Not normally stocked in distribution facility

# Price\*: 960.00 USD

# Main

Product Or Component Type	Servo motor							
Device Short Name	ВМН							
Maximum Mechanical Speed	8000 rpm							
Continuous Stall Torque	30.09 lbf.in (3.4 N.m) LXM32.D18N4 6 A, 400 V, three phase 30.09 lbf.in (3.4 N.m) LXM32.D18N4 6 A, 480 V, three phase							
Peak Stall Torque	90.28 lbf.in (10.2 N.m) LXM32.D18N4 6 A, 400 V, three phase 90.28 lbf.in (10.2 N.m) LXM32.D18N4 6 A, 480 V, three phase							
Nominal Output Power	1300 W LXM32.D18N4 6 A, 400 V, three phase 1300 W LXM32.D18N4 6 A, 480 V, three phase							
Nominal Torque	21.24 lbf.in (2.4 N.m) LXM32.D18N4 6 A, 400 V, three phase 21.24 lbf.in (2.4 N.m) LXM32.D18N4 6 A, 480 V, three phase							
Nominal Speed	5000 rpm LXM32.D18N4 6 A, 400 V, three phase 5000 rpm LXM32.D18N4 6 A, 480 V, three phase							
Product Compatibility	LXM32.D18N4 400480 V three phase							
Shaft End	Keyed							
Ip Degree Of Protection	IP65 standard IP67 with IP67 kit							
Speed Feedback Resolution	32768 points/turn							
Holding Brake	Without							
Mounting Support	International standard flange							
Electrical Connection	Rotatable right-angled connectors							

# Complementary

•	
Range Compatibility	Lexium 32
[Us] Rated Supply Voltage	480 V
Phase	Three phase
Continuous Stall Current	3.91 A
Continuous Power	1.68 W
Maximum Current Irms	12.6 A LXM32.D18N4
Maximum Permanent Current	12.57 A
Second Shaft	Without second shaft end
Shaft Diameter	0.55 in (14 mm)

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Shaft Length	1.18 in (30 mm)
Key Width	0.79 in (20 mm)
Feedback Type	Single turn SinCos Hiperface
Motor Flange Size	2.76 in (70 mm)
Number Of Motor Stacks	3
Torque Constant	0.87 N.m/A 248 °F (120 °C)
Back Emf Constant	55.8 V/krpm 248 °F (120 °C)
Number Of Motor Poles	10
Rotor Inertia	1.67 kg.cm <sup>2</sup>
Stator Resistance	2.65 Ohm 68 °F (20 °C)
Stator Inductance	8.6 mH 68 °F (20 °C)
Stator Electrical Time Constant	3.2 ms 68 °F (20 °C)
Maximum Radial Force Fr	730 N 1000 rpm 580 N 2000 rpm 510 N 3000 rpm 460 N 4000 rpm 430 N 5000 rpm 400 N 6000 rpm
Maximum Axial Force Fa	0.2 x Fr
Type Of Cooling	Natural convection
Length	7.32 in (186 mm)
Centring Collar Diameter	2.36 in (60 mm)
Centring Collar Depth	0.10 in (2.5 mm)
Number Of Mounting Holes	4
Mounting Holes Diameter	0.22 in (5.5 mm)
Circle Diameter Of The Mounting Holes	3.23 in (82 mm)
Net Weight	6.61 lb(US) (3 kg)

# Ordering and shipping details

Category	US1PC5318282
Discount Schedule	PC53
Gtin	3606485199467
Returnability	No
Country Of Origin	DE

# **Packing Units**

V	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4.33 in (11.0 cm)
Package 1 Width	7.87 in (20.0 cm)
Package 1 Length	15.75 in (40.0 cm)
Package 1 Weight	4.85 lb(US) (2.2 kg)

# Contractual warranty

Warranty

18 months

# Sustainability Screen Premium

**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

## Well-being performance

Mercury Free
Rohs Exemption Information Yes
Pvc Free


## **Certifications & Standards**

Reach Regulation	REACh Declaration							
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)							
China Rohs Regulation	China RoHS declaration							
Environmental Disclosure	Product Environmental Profile							
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.							
Circularity Profile	No need of specific recycling operations							
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov							

## **Dimensions Drawings**

#### **Servo Motors Dimensions**

### **Example with Straight Connectors**



a: Power supply for servo motor brake

b: Power supply for servo motor encoder

(1) Shaft end, keyed slot (optional)

Dimensions in mm

Straight Rotatable angled connectors connectors		c (without c (with		c1 (	c2 c3	c3	c3 h	h1	Ø	Ø1 for		
b1	b2	b1	b2	brake)	brake)							screws
39.5	25.5	39.5	39.5	186	225	30	20	5	5 h9	16 <sup>+0</sup> _ 0.13	14 k6	M5 x 17

#### Dimensions in in.


Straigh conneo	angled		c (without brake)	c (with brake)	c1	c2	c3	h	h1	Ø	Ø1 for screws	
b1	b2	b1	b2	brake)								
1.55	1	1.55	1.55	7.32	8.85	1.18	0.78	0.19	0.20 h9	0.63 <sup>+0</sup> _ 0.0051	0.55 k6	M5 x 0.67

### Performance Curves

## 400 V 3-Phase Supply Voltage

#### **Torque/Speed Curves**


Servo motor with LXM32•D18N4 servo drive



- X Speed in rpm
- Y Torque in Nm
- 1 Peak torque
- 2 Continuous torque

#### 480 V 3-Phase Supply Voltage

#### **Torque/Speed Curves**



- X Speed in rpm
- Y Torque in Nm
- 1 Peak torque
- 2 Continuous torque