Product data sheet





servo motor BMH, Lexium 32, 3.4Nm, 6000rpm, untapped shaft, with brake, IP65, IP67, 128 multiturn encoder

BMH1001T22F2A

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 4,106.25 USD

Main

Product Or Component Type	Servo motor		
Device Short Name	вмн		
Maximum Mechanical Speed	6000 rpm		
Continuous Stall Torque	30.09 lbf.in (3.4 N.m) LXM32.D30M2 10 A, 115 V, single phase 30.09 lbf.in (3.4 N.m) LXM32.D18M2 6 A, 230 V, single phase		
Peak Stall Torque	78.77 lbf.in (8.9 N.m) LXM32.D30M2 10 A, 115 V, single phase 90.28 lbf.in (10.2 N.m) LXM32.D18M2 6 A, 230 V, single phase		
Nominal Output Power	700 W LXM32.D30M2 10 A, 115 V, single phase 900 W LXM32.D18M2 6 A, 230 V, single phase		
Nominal Torque	29.21 lbf.in (3.3 N.m) LXM32.D30M2 10 A, 115 V, single phase 24.78 lbf.in (2.8 N.m) LXM32.D18M2 6 A, 230 V, single phase		
Nominal Speed	2000 rpm LXM32.D30M2 10 A, 115 V, single phase 3000 rpm LXM32.D18M2 6 A, 230 V, single phase		
Product Compatibility	LXM32.D30M2 115 V single phase LXM32.D18M2 230 V single phase		
Shaft End	Smooth shaft		
Ip Degree Of Protection	IP65 standard IP67 with IP67 kit		
Speed Feedback Resolution	131072 points/turn x 4096 turns		
Holding Brake	With		
Mounting Support	International standard flange		
Electrical Connection	Rotatable right-angled connectors		

Complementary

•	
Range Compatibility	Lexium 32
[Us] Rated Supply Voltage	240 V
Phase	Three phase
Continuous Stall Current	5.11 A
Continuous Power	1.74 W
Maximum Current Irms	15 A LXM32.D30M2 19.4 A LXM32.D18M2
Maximum Permanent Current	19.38 A
Second Shaft	Without second shaft end

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

0.75 in (19 mm)		
1.57 in (40 mm)		
Multiturn SinCos Hiperface		
48.68 lbf.in (5.5 N.m) holding brake		
3.94 in (100 mm)		
1		
0.67 N.m/A 248 °F (120 °C)		
43.3 V/krpm 248 °F (120 °C)		
10		
3.68 kg.cm ²		
1.19 Ohm 68 °F (20 °C)		
5.3 mH 68 °F (20 °C)		
4.5 ms 68 °F (20 °C)		
900 N 1000 rpm 720 N 2000 rpm 630 N 3000 rpm 570 N 4000 rpm 530 N 5000 rpm		
0.2 x Fr		
12 W		
12 VV		
Natural convection		
Natural convection		
Natural convection 6.70 in (170.3 mm)		
Natural convection 6.70 in (170.3 mm) 3.74 in (95 mm)		
Natural convection 6.70 in (170.3 mm) 3.74 in (95 mm) 0.14 in (3.5 mm)		
Natural convection 6.70 in (170.3 mm) 3.74 in (95 mm) 0.14 in (3.5 mm) 4		

Ordering and shipping details

Category	US1PC5318282
Discount Schedule	PC53
Gtin	3606485196961
Returnability	No
Country Of Origin	DE

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	8.66 in (22.0 cm)
Package 1 Width	7.87 in (20.0 cm)
Package 1 Length	15.75 in (40.0 cm)
Package 1 Weight	11.24 lb(US) (5.1 kg)

Contractual warranty

Warranty

Apr 25, 2024

18 months

Sustainability Screen Premium*

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

Ø	Mercury Free	
	Rohs Exemption Information	Yes
②	Pvc Free	

Certifications & Standards


Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

BMH1001T22F2A

Dimensions Drawings

Servo Motors Dimensions

Example with Straight Connectors



- a: Power supply for servo motor brake
- b: Power supply for servo motor encoder
- (1) Shaft end, keyed slot (optional)
- (2) For screw M6 x 21 mm/M6 x 0.83 in.

Dimensions in mm

Straight connectors		Rotatable angled connectors		c (without brake)	(مامسط طفندر)
b1	b2	b1	b2	c (without brake)	c (with brake)
39.5	25.5	39.5	39.5	128	170

Dimensions in in

Straight connectors		Rotatable angled connectors		c (without brake)	(معامعها طلندر)
b1	b2	b1	b2	c (without brake)	c (with brake)
1.55	1.00	1.55	1.55	5.03	6.69


BMH1001T22F2A

Performance Curves

115 V Single-Phase Supply Voltage

Torque/Speed Curves

Servo motor with LXM32•D30M2 servo drive




- X Speed in rpm
- Y Torque in Nm
- 1 Peak torque
- 2 Continuous torque

230 V Single-Phase Supply Voltage

Torque/Speed Curves

Servo motor with LXM32•D18M2 servo drive



- X Speed in rpm
- Y Torque in Nm
- 1 Peak torque
- 2 Continuous torque