Product data sheet

Specification





servo motor BMH, Lexium 32, 6.2Nm, 6000rpm, keyed shaft, without brake, IP54, 16bit encoder, straight

BMH1002P16A1A

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 1,150.00 USD

Main

Product Or Component Type	Servo motor		
Device Short Name	вмн		
Maximum Mechanical Speed	6000 rpm		
Continuous Stall Torque	54.87 lbf.in (6.2 N.m) LXM32.D18N4 6 A, 400 V, three phase 54.87 lbf.in (6.2 N.m) LXM32.D18N4 6 A, 480 V, three phase		
Peak Stall Torque	162.85 lbf.in (18.4 N.m) LXM32.D18N4 6 A, 400 V, three phase 162.85 lbf.in (18.4 N.m) LXM32.D18N4 6 A, 480 V, three phase		
Nominal Output Power	1600 W LXM32.D18N4 6 A, 400 V, three phase 1600 W LXM32.D18N4 6 A, 480 V, three phase		
Nominal Torque	34.52 lbf.in (3.9 N.m) LXM32.D18N4 6 A, 400 V, three phase 34.52 lbf.in (3.9 N.m) LXM32.D18N4 6 A, 480 V, three phase		
Nominal Speed	4000 rpm LXM32.D18N4 6 A, 400 V, three phase 4000 rpm LXM32.D18N4 6 A, 480 V, three phase		
Product Compatibility	LXM32.D18N4 400480 V three phase		
Shaft End	Keyed		
Ip Degree Of Protection	IP54 standard		
Speed Feedback Resolution	32768 points/turn		
Holding Brake	Without		
Mounting Support	International standard flange		
Electrical Connection	Straight connectors		

Complementary

,		
Range Compatibility	Lexium 32	
[Us] Rated Supply Voltage	480 V	
Phase	Three phase	
Continuous Stall Current	5.04 A	
Continuous Power	2.36 W	
Maximum Current Irms	18 A LXM32.D18N4	
Maximum Permanent Current	18.23 A	
Second Shaft	Without second shaft end	
Shaft Diameter	t Diameter 0.75 in (19 mm)	

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Shaft Length	1.57 in (40 mm)		
Key Width	1.18 in (30 mm)		
Feedback Type	Single turn SinCos Hiperface		
Motor Flange Size	3.94 in (100 mm)		
Number Of Motor Stacks	2		
Torque Constant	1.2 N.m/A 248 °F (120 °C)		
Back Emf Constant	77 V/krpm 248 °F (120 °C)		
Number Of Motor Poles	10		
Rotor Inertia	6.28 kg.cm ²		
Stator Resistance	1.51 Ohm 68 °F (20 °C)		
Stator Inductance	7.5 mH 68 °F (20 °C)		
Stator Electrical Time Constant	5 ms 68 °F (20 °C)		
Maximum Radial Force Fr	990 N 1000 rpm 790 N 2000 rpm 690 N 3000 rpm 620 N 4000 rpm 580 N 5000 rpm		
Maximum Axial Force Fa	0.2 x Fr		
Type Of Cooling	Natural convection		
Length	6.32 in (160.6 mm)		
Centring Collar Diameter	3.74 in (95 mm)		
Centring Collar Depth	0.14 in (3.5 mm)		
Number Of Mounting Holes	4		
Mounting Holes Diameter	0.35 in (9 mm)		
Circle Diameter Of The Mounting Holes	4.53 in (115 mm)		
Net Weight	10.85 lb(US) (4.92 kg)		

Ordering and shipping details

Category	US1PC5318282		
Discount Schedule	PC53		
Gtin	3606485196046		
Returnability	No		
Country Of Origin	DE		

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	7.87 in (20.0 cm)
Package 1 Width	8.66 in (22.0 cm)
Package 1 Length	15.75 in (40.0 cm)
Package 1 Weight	13.01 lb(US) (5.901 kg)
Unit Type Of Package 2	P06
Number Of Units In Package 2	12

Package 2 Height	30.31 in (77.0 cm)
Package 2 Width	31.50 in (80.0 cm)
Package 2 Length	23.62 in (60.0 cm)
Package 2 Weight	174.85 lb(US) (79.312 kg)

Contractual warranty

Warranty 18 months

Sustainability Screen Premium*

Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Certifications & Standards


Reach Regulation	REACh Declaration		
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)		
China Rohs Regulation	China RoHS declaration		
Environmental Disclosure	Product Environmental Profile		
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.		
Circularity Profile	No need of specific recycling operations		
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov		

BMH1002P16A1A

Dimensions Drawings

Servo Motors Dimensions

Example with Straight Connectors



- a: Power supply for servo motor brake
- b: Power supply for servo motor encoder
- (1) Shaft end, keyed slot (optional)
- (2) For screw M6 x 21 mm/M6 x 0.83 in.

Dimensions in mm

Straight connectors Rotatable angl		led connectors	a (without broke)	a (with harden)	
b1	b2	b1	b2	c (without brake)	c (with brake)
39.5	25.5	39.5	39.5	160	202

Dimensions in in.

Straight connectors		Rotatable angled connectors		c (without brake)	(د ا د ا د ا د ا د ا	
b1	b2	b1	b2	c (without brake)	c (with brake)	
1.55	1.00	1.55	1.55	6.29	7.95	

Product data sheet


BMH1002P16A1A

Performance Curves

400 V 3-Phase Supply Voltage

Torque/Speed Curves

Servo motor with LXM32•D18N4 servo drive




- X Speed in rpm
- Y Torque in Nm
- 1 Peak torque
- 2 Continuous torque

480 V 3-Phase Supply Voltage

Torque/Speed Curves

Servo motor with LXM32•D18N4 servo drive



- X Speed in rpm
- Y Torque in Nm
- 1 Peak torque
- 2 Continuous torque