Product data sheet

Specifications





servo motor BMH, Lexium 32, 34.4Nm, 3800rpm, untapped shaft, without brake, IP54, 16 multiturn encoder

BMH2051P07A2A

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 4,480.00 USD

Main

Product Or Component Type	Servo motor
Device Short Name	вмн
Maximum Mechanical Speed	3800 rpm
Continuous Stall Torque	304.47 lbf.in (34.4 N.m) LXM32.D72N4 24 A, 400 V, three phase 304.47 lbf.in (34.4 N.m) LXM32.D72N4 24 A, 480 V, three phase
Peak Stall Torque	915.17 lbf.in (103.4 N.m) LXM32.D72N4 24 A, 400 V, three phase 915.17 lbf.in (103.4 N.m) LXM32.D72N4 24 A, 480 V, three phase
Nominal Output Power	5400 W LXM32.D72N4 24 A, 400 V, three phase 5400 W LXM32.D72N4 24 A, 480 V, three phase
Nominal Torque	228.35 lbf.in (25.8 N.m) LXM32.D72N4 24 A, 400 V, three phase 228.35 lbf.in (25.8 N.m) LXM32.D72N4 24 A, 480 V, three phase
Nominal Speed	2000 rpm LXM32.D72N4 24 A, 400 V, three phase 2000 rpm LXM32.D72N4 24 A, 480 V, three phase
Product Compatibility	LXM32.D72N4 400480 V three phase
Shaft End	Smooth shaft
Ip Degree Of Protection	IP54 standard
Speed Feedback Resolution	32768 points/turn x 4096 turns
Holding Brake	Without
Mounting Support	International standard flange
Electrical Connection	Rotatable right-angled connectors

Complementary

•	
Range Compatibility	Lexium 32
[Us] Rated Supply Voltage	480 V
Phase	Three phase
Continuous Stall Current	21.5 A
Continuous Power	6.8 W
Maximum Current Irms	72 A LXM32.D72N4
Maximum Permanent Current	78.1 A
Second Shaft	Without second shaft end
Shaft Diameter	1.50 in (38 mm)

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Shaft Length	3.15 in (80 mm)	
Feedback Type	Multiturn SinCos Hiperface	
Motor Flange Size	8.07 in (205 mm)	
Number Of Motor Stacks	1	
Back Emf Constant	104 V/krpm 248 °F (120 °C)	
Number Of Motor Poles	10	
Rotor Inertia	71.4 kg.cm²	
Stator Resistance	0.3 Ohm 68 °F (20 °C)	
Stator Inductance	5.9 mH 68 °F (20 °C)	
Stator Electrical Time Constant	19.7 ms 68 °F (20 °C)	
Maximum Radial Force Fr	3730 N 1000 rpm 2960 N 2000 rpm 2580 N 3000 rpm	
Maximum Axial Force Fa	0.2 x Fr	
Type Of Cooling	Natural convection	
Length	12.64 in (321 mm)	
Centring Collar Diameter	7.09 in (180 mm)	
Centring Collar Depth	0.16 in (4 mm)	
Number Of Mounting Holes	4	
Mounting Holes Diameter	0.55 in (14 mm)	
Circle Diameter Of The Mounting Holes	8.46 in (215 mm)	
Net Weight	72.75 lb(US) (33 kg)	

Ordering and shipping details

Category	US1PC5318282
Discount Schedule	PC53
Gtin	3606485202969
Returnability	No
Country Of Origin	DE

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	14.17 in (36.0 cm)
Package 1 Width	12.20 in (31.0 cm)
Package 1 Length	22.83 in (58.0 cm)
Package 1 Weight	85.98 lb(US) (39.0 kg)

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov