Specifications





servo motor BMI 3-phase - keyed IP65 single turn - 32768 p/t

BMI0703P36A

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 2,346.51 USD

Main

Range Compatibility	Lexium 32i
Product Or Component Type	Servo motor with power stage
Device Short Name	BMI

Complementary

Compromontary		
Maximum Mechanical Speed	8000 rpm	
[Us] Rated Supply Voltage	208480 V - 1510 %	
Supply Voltage Limits	208480 V	
Phase	Three phase	
Supply Frequency	50/60 Hz - 55 %	
Network Frequency Limits	47.563 Hz	
Emc Filter	Integrated	
Continuous Output Current	2 A 8 kHz	
Output Current 3S Peak	6 A 400 V 3 s	
Continuous Stall Current	2 A	
Continuous Stall Torque	30.09 lbf.in (3.4 N.m) 208480 V three phase	
Peak Stall Torque	76.12 lbf.in (8.6 N.m) 208 V three phase 76.12 lbf.in (8.6 N.m) 400 V three phase 76.12 lbf.in (8.6 N.m) 480 V three phase	
Nominal Output Power	900 W 400 V three phase 900 W 480 V three phase 450 W 208 V three phase	
Nominal Torque	25.67 lbf.in (2.9 N.m) 208 V three phase 23.90 lbf.in (2.7 N.m) 400 V three phase 20.36 lbf.in (2.3 N.m) 480 V three phase	
Nominal Speed	3300 rpm 400 V three phase 1600 rpm 208 V three phase 3900 rpm 480 V three phase	
Maximum Current Irms	12.5 A 400 V, three phase 12.5 A 480 V, three phase 12.5 A 208 V, three phase	
Product Compatibility	Drive control unit LXM32i CANopen Drive control unit LXM32i EtherCAT	
Shaft End	Keyed	
Second Shaft	Without second shaft end	
Shaft Diameter	0.55 in (14 mm)	

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Shaft Length	1.18 in (30 mm)
Key Width	0.20 in (5 mm)
Feedback Type	Absolute single turn SinCos Hiperface
Speed Feedback Resolution	32768 points/turn
Holding Brake	Without
Mounting Support	International standard flange
Motor Flange Size	2.76 in (70 mm)
Electrical Connection	Printed circuit board connector
Torque Constant	1.41 N.m/A 68 °F (20 °C)
Back Emf Constant	95.39 V/krpm 68 °F (20 °C)
Number Of Motor Poles	10
Rotor Inertia	1.67 kg.cm ²
Stator Resistance	7.99 Ohm 68 °F (20 °C)
Stator Inductance	25.6 mH 68 °F (20 °C)
Stator Electrical Time Constant	3.2 ms 68 °F (20 °C)
Maximum Radial Force Fr	730 N 1000 rpm 580 N 2000 rpm 510 N 3000 rpm 460 N 4000 rpm 430 N 5000 rpm 400 N 6000 rpm
Maximum Axial Force Fa	0.2 x Fr
Type Of Cooling	Natural convection
Length	11.81 in (300 mm)
Number Of Motor Stacks	3
Centring Collar Diameter	2.36 in (60 mm)
Centring Collar Depth	0.10 in (2.5 mm)
Number Of Mounting Holes	4
Mounting Holes Diameter	0.22 in (5.5 mm)
Circle Diameter Of The Mounting Holes	2.953.23 in (7582 mm)
Distance Shaft Shoulder-Flange	0.10 in (2.5 mm)

Environment

Ip Degree Of Protection

IP65

PCE

Ordering and shipping details

Category	US1PC5618287
Discount Schedule	PC56
Gtin	3606485376561
Returnability	No
Country Of Origin	DE

Packing Units

Unit Type Of Package 1

Number Of Units In Package 1	1
Package 1 Height	9.84 in (25.0 cm)
Package 1 Width	7.32 in (18.6 cm)
Package 1 Length	21.65 in (55.0 cm)
Package 1 Weight	14.33 lb(US) (6.5 kg)

Contractual warranty

Warranty

18 months

Sustainability Screen

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance




Certifications & Standards

Reach Regulation	REACh Declaration	
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)	
China Rohs Regulation	China RoHS declaration	
Environmental Disclosure	Product Environmental Profile	
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.	
Circularity Profile	End of Life Information	
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth	

Dimensions Drawings

External Dimensions

With Standard Braking Resistor



- (1) Module for supply voltage
- (2) I/O module
- (3) Standard braking resistor


Dimensions in mm

W	Н	L
99	187	321

Dimensions in in.

W	Н	L
3,90	7,36	12,64

Mounting type B




(2) I/O module

(3) Standard braking resistor

Dimensions in mm		
W	Н	L
99	138,5	370

Dimensions in in.			
W H L			
3,90	5,45	14,57	

With External Braking Resistor



(1) Module for supply voltage

- (2) I/O module
- (4) External braking resistor


Dimensions in mm

W	Н	L
99	187	333

Dimensions in in.

W	Н	L
3,90	7,36	13,11

Mounting type D



- (1) Module for supply voltage
- (2) I/O module
- (4) External braking resistor


Dimen	sions	in	mm

W	Н	L
99	160	370

Dimensions in in.

W	Н	L
3,90	6,3	14,57

Mounting type E




- (1) Module for supply voltage
- (2) I/O module
- (4) External braking resistor

Dimensions in mm

W	Н	L
99	187	360

Dimensions in in.					
W H L					
3,90	7,36	14,17			

Mounting type F



- (1) Module for supply voltage
- (2) I/O module
- (4) External braking resistor

Dimensions in mm

W	Н	L	
99	180	370	

Dimensions in in.

W	Н	L
3,90	7,09	14,57

BMI0703P36A

Performance Curves

Performance Curves

(Y) 10.0 9.0 8.0 7.0 6.0 - (1) 5.0 (2) 4.0 (3) 3.0 (4) (5) 4 2.0 1.0 0 -1000 2000 3000 4000 5000 6000 7000 8000 9000 0 (X)


Torque/Speed Curves with 208 V Three Phases Supply Voltage

- (X) Speed (rpm)
- (Y) Torque (N.m)
- (1) Motor peak
- (2) Drive peak
- (3) Drive cont
- (4) Motor cont
- (5) Operating point

		Power	At Speed	With Torque
max. Peak Power		1138 W	1360 rpm	7.99 N.m
max Cont. Power (Drive)	•	564 W	1840 rpm	2.93 N.m

Performance Curves

Torque/Speed Curves with 400 V Three Phases Supply Voltage




- (X) Speed (rpm)
- (Y) Torque (N.m)
- (1) Motor peak
- (2) Drive peak
- (3) Drive cont
- (4) Motor cont
- (5) Operating point

		Power	At Speed	With Torque
max. Peak Power		2390 W	2960 rpm	7.71 N.m
max Cont. Power (Drive)	•	895 W	3760 rpm	2.27 N.m

Performance Curves

Torque/Speed Curves with 480 V Three Phases Supply Voltage



- (X) Speed (rpm)
- (Y) Torque (N.m)
- (1) Motor peak
- (2) Drive peak
- (3) Drive cont
- (4) Motor cont
- (5) Operating point

		Power	At Speed	With Torque
max. Peak Power		2915 W	3600 rpm	7.73 N.m
max Cont. Power (Drive)	•	945 W	4560 rpm	1.98 N.m