

Product data sheet

Specifications



Power Relay, SPST, 1NO and 0NC, 20 A resistive at 110 VDC, 24 VAC coil

8501CO21V14

Discontinued on: Oct 11, 2019

Discontinued

Main

Product Range	Power Relay 8501C
Product Type	Power relay
Short Name	type C
[In] Rated Line Current	20 A
Device Application	Suited for controlling small single phase motors and other light loads
Switch Function	SPST
Contact Composition	1 NO
[Uc] Control Circuit Voltage	24 V AC 50/60 Hz
Maximum Switching Voltage	500 V DC

Complementary

Class Number	8501
Phase	1 phase
Terminal Connects	Screw clamp terminal
Wire Range	AWG 10 copper
Terminal Tightening Torque	11...15 lbf.in (1.24...1.69 N.m)
Coil Burden	10 VA
Mounting	Panel mounting

Environment

Ambient Temperature Range - Operational	-22...122 °F (-30...50 °C)
Product Certifications	UL listed file E78351 CCN NLDX CSA CE
Height	2.43 in (61.72 mm)
Width	2.5 in (63.50 mm)
Depth	2.18 in (55.37 mm)

Ordering and shipping details

Category	21131-8501 C
Discount Schedule	CP2
Returnability	No

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Country Of Origin	CN
-------------------	----

Contractual warranty

Warranty	18 months
----------	-----------