## **Product data sheet**

Specifications



# Plug in relay, Type KU, blade, 0.5 HP at 240 VAC, 10A resistive at 120 VAC, 8 blade, DPDT, 2 NO, 2

(!) End-of-service on: Dec 31, 2020

#### Main

Product Range	8501K	
Product Type	Relay	
Relay Type	General purpose	
Mounting Type	Socket	
Contact Composition	DPDT	
[Uc] Control Circuit Voltage	240 V AC	
Pilot Light	Indicator light relay energised LED	

### Complementary

Horsepower Rating	1 hp 277 V AC 0.33 hp 120 V AC	
Breaking Capacity	3 A 120 V AC inductive control circuit UL 508 1.5 A 240 V AC inductive control circuit UL 508 10 A 277 V AC resistive control circuit UL 508 10 A 30 V DC resistive control circuit UL 508	
Maximum Switching Voltage	300 V AC 30 V DC	
Contact Material	Silver alloy (AgNi)	
Operating Time	20 ms - pick-up 20 ms - drop-out	
Shape Of Pins	Spade	
For Use With	8501NR82	

#### **Environment**

Ambient Temperature Range - Operational	-40131 °F (-4055 °C)
Product Certifications	UL Listed UL Recognized CSA CE
Height	2.25 in (57.15 mm)
Width	1.37 in (34.80 mm)
Depth	1.4 in (35.56 mm)

## Ordering and shipping details

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Category	21144-8501 KU
Discount Schedule	CP2
Gtin	00785901982319
Returnability	No
Country Of Origin	CN

## **Packing Units**

<u> </u>			
Unit Type Of Package 1	PCE		

Number Of Units In Package 1 1

## Sustainability Screen Premium

**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

#### Well-being performance

Reach Free Of Svhc

Rohs Exemption Information Yes

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov