





## NEMA Control Relay, Type X, machine tool, 10A resistive at 600 VAC, 2 normally open contacts, 24 VDC coil

8501XDO20V53

Product availability: Non-Stock - Not normally stocked in distribution facility

Price\*: 264.00 USD

#### Main

Range	8501X	
Relay Type	Control	
Product	Relay	
Current Rating	10 A AC	
	5 A DC	

### Complementary

Coil Voltage	24 V DC
Control Circuit Voltage Limits	Operational 0.81.1 Uc DC
Rated Breaking Capacity	6 A 120 V AC inductive control circuit UL 508 3 A 240 V AC inductive control circuit UL 508 1.5 A 480 V AC inductive control circuit UL 508 1.2 A 600 V AC inductive control circuit UL 508 10 A <= 600 V AC resistive control circuit UL 508 1.1 A 125 V DC inductive control circuit UL 508 0.55 A 250 V DC inductive control circuit UL 508 0.2 A 301600 V DC inductive control circuit UL 508 4 A 125 V DC resistive control circuit UL 508 0.8 A 250 V DC resistive control circuit UL 508
[Icm] Rated Short-Circuit Making Capacity	60 A 120 V AC inductive control circuit UL 508 30 A 240 V AC inductive control circuit UL 508 15 A 480 V AC inductive control circuit UL 508 12 A 600 V AC inductive control circuit UL 508 10 A <= 600 V AC resistive control circuit UL 508 1.1 A 125 V DC inductive control circuit UL 508 0.55 A 250 V DC inductive control circuit UL 508 0.2 A 301600 V DC inductive control circuit UL 508 4 A 125 V DC inductive control circuit UL 508 0.8 A 250 V DC resistive control circuit UL 508
Inrush Power In W	18 W
Hold-In Power Consumption In W	18 W
Operating Time	37 ms - pick-up 21 ms - drop-out
Contact Configuration	2 NO 2 standard contact cartridges
Electrical Connection	Screw clamp terminals
Awg Gauge	AWG 18AWG 12 copper
Tightening Torque	Control circuit 9.0312.04 lbf.in (1.021.36 N.m) screw terminals
Mounting Type	Panel
Height	3.56 in (90.42 mm)

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Width	2.23 in (56.64 mm)
Depth	5.17 in (131.32 mm)

### **Environment**

Operating Temperature	-40160 °F (-4071 °C)
Certifications	UL listed file E78403 CCN NKCR
	CSA LR60905 class 3211 03

# Ordering and shipping details

Category	US10CP221157	
Discount Schedule	0CP2	
Gtin	785901537441	
Returnability	No	
Country Of Origin	US	

### **Packing Units**

Unit Type Of Package 1	PCE	
Number Of Units In Package 1	1	
Package 1 Height	8.89 in (22.581 cm)	
Package 1 Width	3.50 in (8.89 cm)	
Package 1 Length	22.58 in (57.355 cm)	
Package 1 Weight	3.32 lb(US) (1.506 kg)	

## **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

#### Well-being performance



Mercury Free



Rohs Exemption Information

Yes

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov