Product data sheet

Specifications





AC servo motor BSH, Lexium 05, 5.5N.m, 4000rpm, keyed shaft, without brake, IP50

BSH1002T12A1A

! Discontinued on: Jun 30, 2023

① Discontinued

Product availability: Non-Stock - Not normally stocked in distribution facility

Main

| Product Or Component Type | Servo motor |
|---------------------------|---|
| Device Short Name | BSH |
| Maximum Mechanical Speed | 6000 rpm |
| Continuous Stall Torque | 51.33 lbf.in (5.8 N.m) LXM32.D30M2 10 A, 230 V, single phase 48.68 lbf.in (5.5 N.m) LXM15LD28M3, 230 V, three phase 48.68 lbf.in (5.5 N.m) LXM05AD42M3X, 200240 V, three phase 48.68 lbf.in (5.5 N.m) LXM05BD42M3X, 200240 V, three phase 48.68 lbf.in (5.5 N.m) LXM05CD42M3X, 200240 V, three phase |
| Peak Stall Torque | 145.15 lbf.in (16.4 N.m) LXM32.D30M2 10 A, 230 V, single phase 102.58 lbf.in (11.59 N.m) LXM15LD28M3, 230 V, three phase 141.61 lbf.in (16 N.m) LXM05AD42M3X, 200240 V, three phase 141.61 lbf.in (16 N.m) LXM05BD42M3X, 200240 V, three phase 141.61 lbf.in (16 N.m) LXM05CD42M3X, 200240 V, three phase |
| Nominal Output Power | 1500 W LXM32.D30M2 10 A, 230 V, single phase 1400 W LXM05AD42M3X, 200240 V, three phase 1400 W LXM05BD42M3X, 200240 V, three phase 1400 W LXM05CD42M3X, 200240 V, three phase 1700 W LXM15LD28M3, 230 V, three phase |
| Nominal Torque | 32.75 lbf.in (3.7 N.m) LXM32.D30M2 10 A, 230 V, single phase 35.40 lbf.in (4 N.m) LXM15LD28M3, 230 V, three phase 38.94 lbf.in (4.4 N.m) LXM05AD42M3X, 200240 V, three phase 38.94 lbf.in (4.4 N.m) LXM05BD42M3X, 200240 V, three phase 38.94 lbf.in (4.4 N.m) LXM05CD42M3X, 200240 V, three phase |
| Nominal Speed | 4000 rpm LXM32.D30M2 10 A, 230 V, single phase 3000 rpm LXM05AD42M3X, 200240 V, three phase 3000 rpm LXM05BD42M3X, 200240 V, three phase 3000 rpm LXM05CD42M3X, 200240 V, three phase 4000 rpm LXM15LD28M3, 230 V, three phase |
| Product Compatibility | LXM32.D30M2 230 V single phase LXM05AD42M3X 200240 V three phase LXM05BD42M3X 200240 V three phase LXM05CD42M3X 200240 V three phase LXM15LD28M3 230 V three phase |
| Shaft End | Keyed |
| Ip Degree Of Protection | IP50 standard |
| Speed Feedback Resolution | 131072 points/turn x 4096 turns |
| Holding Brake | Without |
| Mounting Support | International standard flange |
| Electrical Connection | Straight connectors |

Complementary

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.



| Range Compatibility | Lexium 15 Lexium 05 | | | | | |
|---------------------------------|--|--|--|--|--|--|
| | Lexium 05 Lexium 32 | | | | | |
| Supply Voltage Max | 480 V | | | | | |
| Phase | Three phase | | | | | |
| Continuous Stall Current | 9.9 A | | | | | |
| Maximum Continuous Power | 2.51 W | | | | | |
| Maximum Current Irms | 31.2 A LXM15LD28M3 35.4 A LXM05AD42M3X | | | | | |
| | 35.4 A LXM05BD42M3X 35.4 A LXM05CD42M3X | | | | | |
| | 30 A LXM32.D30M2 | | | | | |
| Maximum Permanent Current | 35.4 A | | | | | |
| Switching Frequency | 8 kHz | | | | | |
| Second Shaft | Without second shaft end | | | | | |
| Shaft Diameter | 0.75 in (19 mm) | | | | | |
| Shaft Length | 1.57 in (40 mm) | | | | | |
| Key Width | 1.18 in (30 mm) | | | | | |
| Feedback Type | Multiturn SinCos Hiperface | | | | | |
| Motor Flange Size | 3.94 in (100 mm) | | | | | |
| Number Of Motor Stacks | 2 | | | | | |
| Torque Constant | 0.59 N.m/A 248 °F (120 °C) | | | | | |
| Back Emf Constant | 37 V/krpm 248 °F (120 °C) | | | | | |
| Number Of Motor Poles | 8 | | | | | |
| Rotor Inertia | 2.31 kg.cm ² | | | | | |
| Stator Resistance | 0.56 Ohm 68 °F (20 °C) | | | | | |
| Stator Inductance | 3 mH 68 °F (20 °C) | | | | | |
| Stator Electrical Time Constant | 5.36 ms 68 °F (20 °C) | | | | | |
| Maximum Radial Force Fr | 620 N 4000 rpm 690 N 3000 rpm | | | | | |
| | 790 N 2000 rpm | | | | | |
| Maximum Axial Force Fa | 990 N 1000 rpm 0.2 x Fr | | | | | |
| Type Of Cooling | Natural convection | | | | | |
| Length | 8.05 in (204.5 mm) | | | | | |
| Centring Collar Diameter | 3.74 in (95 mm) | | | | | |
| Centring Collar Depth | 0.14 in (3.5 mm) | | | | | |
| Number Of Mounting Holes | 4 | | | | | |
| Mounting Holes Diameter | 0.35 in (9 mm) | | | | | |
| Circle Diameter Of The Mounting | 4.53 in (115 mm) | | | | | |
| Holes Net Weight | 13.01 lb(US) (5.9 kg) | | | | | |
| = | . , . •, | | | | | |

Ordering and shipping details

| Category | US1PC5318282 | | | | |
|-------------------|--------------|--|--|--|--|
| Discount Schedule | PC53 | | | | |

| Gtin | 3389118139398 | | | | |
|-------------------|---------------|--|--|--|--|
| Returnability | No | | | | |
| Country Of Origin | DF | | | | |

Packing Units

| Unit Type Of Package 1 | PCE |
|------------------------------|-----------------------|
| Number Of Units In Package 1 | 1 |
| Package 1 Height | 6.06 in (15.4 cm) |
| Package 1 Width | 6.42 in (16.3 cm) |
| Package 1 Length | 16.02 in (40.7 cm) |
| Package 1 Weight | 12.79 lb(US) (5.8 kg) |

Contractual warranty

Warranty 18 months

Sustainability Screen Premium*

Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Mercury Free



Rohs Exemption Information

Yes

Certifications & Standards

| Reach Regulation | REACh Declaration | | | | | |
|---------------------------------|---|--|--|--|--|--|
| Eu Rohs Directive | Pro-active compliance (Product out of EU RoHS legal scope) | | | | | |
| China Rohs Regulation | China RoHS declaration | | | | | |
| Environmental Disclosure | Product Environmental Profile | | | | | |
| Weee | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins. | | | | | |
| Circularity Profile | No need of specific recycling operations | | | | | |
| California Proposition 65 | WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov | | | | | |


Apr 25, 2024

BSH1002T12A1A

Dimensions Drawings

Servo Motors Dimensions

Example with Straight Connectors



- a: Power supply for servo motor brake
- **b**: Power supply for servo motor encoder
- (1) M4 screw
- (2) Shaft end, keyed slot (optional)

Dimensions in mm

| Straight connectors | | Rotatable angled connectors | | c (without | c (with | c1 | c2 | h | h1 | Ø | Ø1 for |
|---------------------|------|-----------------------------|------|------------|---------|----|----|---------|----------------------------------|----------|---------|
| b1 | b2 | b1 | b2 | brake) | brake) | | | | | | screws |
| 39.5 | 25.5 | 39.5 | 39.5 | 205 | 236 | 40 | 30 | 6 N9 | 3.5 ^{+0.1} ₀ | 19 k6 | M6 x 16 |

Dimensions in in.

| Straight connectors | | Rotatable angled connectors | | c (without | c (with | c1 | c2 | h | h1 | Ø | Ø1 for |
|---------------------|------|-----------------------------|------|------------|---------|------|------|------------|------------------------|------------|--------------|
| b1 | b2 | b1 | b2 | brake) | brake) | | | | | | screws |
| 1.55 | 1.00 | 1.55 | 1.55 | 8.07 | 9.29 | 1.57 | 1.18 | 0.24 N9 | 0.14 ^{+0.1} 0 | 0.75 k6 | M6 x 0.63 |

Product data sheet


BSH1002T12A1A

Performance Curves

230 V Single-Phase Supply Voltage

Torque/Speed Curves

Servo motor with LXM32•D30M2 servo drive



- X Speed in rpm
- Y Torque in Nm
- 1 Peak torque
- 2 Continuous torque