# **Product data sheet**

Specifications





AC servo motor BSH, Lexium 05, 9.31N.m, 1500rpm, untapped shaft, without brake, IP65

BSH1004P22A2A

Product availability: Non-Stock - Not normally stocked in distribution facility

Price\*: 3,502.50 USD

#### Main

wain						
Product Or Component Type	Servo motor					
Device Short Name	BSH					
Maximum Mechanical Speed	70.81 lbf.in (8 N.m) LXM32.D30N4 10 A, 400 V, three phase 70.81 lbf.in (8 N.m) LXM32.D30N4 10 A, 480 V, three phase 82.40 lbf.in (9.31 N.m) LXM15MD40N4, 400 V, three phase 82.40 lbf.in (9.31 N.m) LXM15MD40N4, 480 V, three phase 82.40 lbf.in (9.31 N.m) LXM15MD28M3, 230 V, three phase 82.40 lbf.in (9.31 N.m) LXM15MD28N4, 230 V, three phase 82.40 lbf.in (9.31 N.m) LXM15MD28N4, 400 V, three phase 82.40 lbf.in (9.31 N.m) LXM15MD28N4, 400 V, three phase 82.40 lbf.in (9.31 N.m) LXM15MD28N4, 480 V, three phase 82.40 lbf.in (9.31 N.m) LXM15MD40N4, 230 V, three phase 82.40 lbf.in (9.31 N.m) LXM05AD34N4, 380480 V, three phase 82.40 lbf.in (9.31 N.m) LXM05AD57N4, 380480 V, three phase 82.40 lbf.in (9.31 N.m) LXM05BD34N4, 380480 V, three phase 82.40 lbf.in (9.31 N.m) LXM05BD42M3X, 200240 V, three phase 82.40 lbf.in (9.31 N.m) LXM05BD42M3X, 200240 V, three phase 82.40 lbf.in (9.31 N.m) LXM05BD42M3X, 200240 V, three phase 82.40 lbf.in (9.31 N.m) LXM05BD57N4, 380480 V, three phase					
Continuous Stall Torque						
	82.40 lbf.in (9.31 N.m) LXM05CD42M3X, 200240 V, three phase 82.40 lbf.in (9.31 N.m) LXM05CD57N4, 380480 V, three phase					
Peak Stall Torque	335.44 lbf.in (37.9 N.m) LXM32.D30N4 10 A, 400 V, three phase 335.44 lbf.in (37.9 N.m) LXM32.D30N4 10 A, 480 V, three phase 227.46 lbf.in (25.7 N.m) LXM15MD28M3, 230 V, three phase 227.46 lbf.in (25.7 N.m) LXM15MD28N4, 230 V, three phase 227.46 lbf.in (25.7 N.m) LXM15MD28N4, 400 V, three phase 227.46 lbf.in (25.7 N.m) LXM15MD28N4, 480 V, three phase 229.42 lbf.in (33.83 N.m) LXM15MD40N4, 230 V, three phase 299.42 lbf.in (33.83 N.m) LXM15MD40N4, 230 V, three phase 299.42 lbf.in (33.83 N.m) LXM15MD40N4, 400 V, three phase 299.42 lbf.in (33.83 N.m) LXM15MD40N4, 480 V, three phase 207.73 lbf.in (23.47 N.m) LXM05AD34N4, 380480 V, three phase 315.97 lbf.in (35.7 N.m) LXM05AD34N4, 380480 V, three phase 207.73 lbf.in (23.47 N.m) LXM05AD34N4, 380480 V, three phase 315.97 lbf.in (35.7 N.m) LXM05BD34N4, 380480 V, three phase 315.97 lbf.in (35.7 N.m) LXM05BD57N4, 380480 V, three phase 315.97 lbf.in (35.7 N.m) LXM05BD57N4, 380480 V, three phase 315.97 lbf.in (35.7 N.m) LXM05BD57N4, 380480 V, three phase 315.97 lbf.in (35.7 N.m) LXM05BD57N4, 380480 V, three phase 315.97 lbf.in (35.7 N.m) LXM05CD34N4, 380480 V, three phase 315.97 lbf.in (35.7 N.m) LXM05CD34N4, 380480 V, three phase 315.97 lbf.in (35.7 N.m) LXM05CD34N4, 380480 V, three phase 315.97 lbf.in (35.7 N.m) LXM05CD34N4, 380480 V, three phase 315.97 lbf.in (35.7 N.m) LXM05CD34N4, 380480 V, three phase 315.97 lbf.in (35.7 N.m) LXM05CD34N4, 380480 V, three phase 315.97 lbf.in (35.7 N.m) LXM05CD34N4, 380480 V, three phase 315.97 lbf.in (35.7 N.m) LXM05CD34N4, 380480 V, three phase 315.97 lbf.in (35.7 N.m) LXM05CD35N4, 380480 V, three phase 315.97 lbf.in (35.7 N.m) LXM05CD35N4, 380480 V, three phase 315.97 lbf.in (35.7 N.m) LXM05CD35N4, 380480 V, three phase 315.97 lbf.in (35.7 N.m) LXM05CD35N4, 380480 V, three phase 315.97 lbf.in (35.7 N.m) LXM05CD35N4, 380480 V, three phase 315.97 lbf.in (35.7 N.m) LXM05CD35N4, 380480 V, three phase 315.97 lbf.in (35.7 N.m) LXM05CD35N4, 380480 V, three phase 315.97 lbf.					

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Nominal Output Power	2600 W LXM32.D30N4 10 A, 480 V, three phase							
	2100 W LXM32.D30N4 10 A, 400 V, three phase							
	1300 W LXM05AD42M3X, 200240 V, three phase							
	1300 W LXM05BD42M3X, 200240 V, three phase							
	1300 W LXM05CD42M3X, 200240 V, three phase							
	1300 W LXM15MD28M3, 230 V, three phase 1300 W LXM15MD28N4, 230 V, three phase							
	1300 W LXM15MD2014, 230 V, three phase 1300 W LXM15MD40N4, 230 V, three phase 2200 W LXM05AD34N4, 380480 V, three phase							
	2200 W LXM05AD57N4, 380480 V, three phase							
	2200 W LXM05BD34N4, 380480 V, three phase							
	2200 W LXM05BD57N4, 380480 V, three phase							
	2200 W LXM05CD34N4, 380480 V, three phase							
	2200 W LXM05CD57N4, 380480 V, three phase 2200 W LXM15MD28N4, 400 V, three phase							
	2300 W LXM15MD40N4, 400 V, three phase							
	2400 W LXM15MD40N4, 480 V, three phase							
	2700 W LXM15MD28N4, 480 V, three phase							
Nominal Torque	73.46 lbf.in (8.3 N.m) LXM32.D30N4 10 A, 400 V, three phase							
	73.46 lbf.in (8.3 N.m) LXM32.D30N4 10 A, 480 V, three phase							
	57.53 lbf.in (6.5 N.m) LXM15MD28N4, 480 V, three phase							
	59.21 lbf.in (6.69 N.m) LXM15MD40N4, 480 V, three phase							
	61.96 lbf.in (7 N.m) LXM15MD28N4, 400 V, three phase							
	62.84 lbf.in (7.1 N.m) LXM05AD34N4, 380480 V, three phase							
	62.84 lbf.in (7.1 N.m) LXM05AD57N4, 380480 V, three phase							
	62.84 lbf.in (7.1 N.m) LXM05BD34N4, 380480 V, three phase							
	62.84 lbf.in (7.1 N.m) LXM05BD57N4, 380480 V, three phase 62.84 lbf.in (7.1 N.m) LXM05CD34N4, 380480 V, three phase							
	62.84 lbf.in (7.1 N.m) LXM05CD57N4, 380480 V, three phase							
	63.46 lbf.in (7.17 N.m) LXM15MD40N4, 400 V, three phase							
	72.40 lbf.in (8.18 N.m) LXM15MD40N4, 230 V, three phase							
	72.75 lbf.in (8.22 N.m) LXM05AD42M3X, 200240 V, three phase							
	72.75 lbf.in (8.22 N.m) LXM05BD42M3X, 200240 V, three phase							
	72.75 lbf.in (8.22 N.m) LXM05CD42M3X, 200240 V, three phase							
	72.75 lbf.in (8.22 N.m) LXM15LD28M3, 230 V, three phase							
	72.75 lbf.in (8.22 N.m) LXM15MD28N4, 230 V, three phase							
Nominal Speed	2500 rpm LXM32.D30N4 10 A, 400 V, three phase							
	3000 rpm LXM32.D30N4 10 A, 480 V, three phase							
	1500 rpm LXM05AD42M3X, 200240 V, three phase							
	1500 rpm LXM05BD42M3X, 200240 V, three phase							
	1500 rpm LXM05CD42M3X, 200240 V, three phase 3000 rpm LXM05AD34N4, 380480 V, three phase							
	3000 rpm LXM05BD34N4, 380480 V, three phase							
	3000 rpm LXM05CD34N4, 380480 V, three phase							
	1500 rpm LXM15MD28M3, 230 V, three phase							
	1500 rpm LXM15MD28N4, 230 V, three phase							
	1500 rpm LXM15MD40N4, 230 V, three phase							
	3000 rpm LXM05AD57N4, 380480 V, three phase							
	3000 rpm LXM05BD57N4, 380480 V, three phase							
	3000 rpm LXM05CD57N4, 380480 V, three phase							
	3000 rpm LXM15MD28N4, 400 V, three phase 3000 rpm LXM15MD40N4, 400 V, three phase							
	3500 rpm LXM15MD40N4, 400 V, three phase							
	4000 rpm LXM15MD28N4, 480 V, three phase							
Product Compatibility	LVM05AD42M2V 200 - 240 V three phase							
	LXM05AD42M3X 200240 V three phase LXM05BD42M3X 200240 V three phase							
	LXM05CD42M3X 200240 V three phase							
	LXM05AD34N4 380480 V three phase							
	LXM05BD34N4 380480 V three phase							
	LXM05CD34N4 380480 V three phase							
	LXM15MD28N4 400 V three phase							
	LXM15MD28N4 480 V three phase							
	LXM15MD40N4 400 V three phase							
	LXM15MD40N4 480 V three phase LXM32.D30N4 400 V three phase							
	LXM32.D30N4 480 V three phase							
	LXM05AD57N4 380480 V three phase							
	LXM05BD57N4 380480 V three phase							
	LXM05CD57N4 380480 V three phase							
	LXM15MD28M3 230 V three phase							
	LXM15MD28N4 230 V three phase							
	LXM15MD40N4 230 V three phase							

Untapped

Shaft End

Ip Degree Of Protection	IP65 standard IP67 with IP67 kit						
Speed Feedback Resolution	131072 points/turn x 4096 turns						
Holding Brake	Without						
Mounting Support	International standard flange						
Electrical Connection	Rotatable right-angled connectors						
Complementen							
Complementary							
Range Compatibility	Lexium 05 Lexium 32 Lexium 15						
Supply Voltage Max	480 V						
Phase	Three phase						
Continuous Stall Current	6.2 A						
Maximum Continuous Power	3.64 W						
Maximum Current Irms	34.8 A LXM15LD28M3 34.8 A LXM15MD28N4 34.8 A LXM15MD40N4 32.3 A LXM05AD42M3X 32.3 A LXM05AD57N4 32.3 A LXM05AD57N4 32.3 A LXM05BD42M3X 32.3 A LXM05BD34N4 32.3 A LXM05BD57N4 32.3 A LXM05CD42M3X 32.3 A LXM05CD42M3X 32.3 A LXM05CD42M3X 32.3 A LXM05CD42M3X 32.3 A LXM05CD34N4 32.3 A LXM05CD34N4						
Maximum Permanent Current	32.3 A						
Switching Frequency	8 kHz						
Second Shaft	Without second shaft end						
Shaft Diameter	0.94 in (24 mm)						
Shaft Length	1.97 in (50 mm)						
Feedback Type	Multiturn SinCos Hiperface						
Motor Flange Size	3.94 in (100 mm)						
Number Of Motor Stacks	4						
Torque Constant	1.62 N.m/A 248 °F (120 °C)						
Back Emf Constant	103 V/krpm 248 °F (120 °C)						
Number Of Motor Poles	8						
Rotor Inertia	4.22 kg.cm²						
Stator Resistance	1.81 Ohm 68 °F (20 °C)						
Stator Inductance	11.8 mH 68 °F (20 °C)						
Stator Electrical Time Constant	6.52 ms 68 °F (20 °C)						
Maximum Radial Force Fr	1070 N 1000 rpm 740 N 3000 rpm 850 N 2000 rpm						
Maximum Axial Force Fa	0.2 x Fr						
Type Of Cooling	Natural convection						
Length	10.89 in (276.5 mm)						

Centring Collar Diameter	3.74 in (95 mm)
Centring Collar Depth	0.14 in (3.5 mm)
Number Of Mounting Holes	4
Mounting Holes Diameter	0.35 in (9 mm)
Circle Diameter Of The Mounting Holes	4.53 in (115 mm)
Net Weight	20.94 lb(US) (9.5 kg)

# Ordering and shipping details

Category	US1PC5318282
Discount Schedule	PC53
Gtin	3389118140486
Returnability	No
Country Of Origin	DE

## **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	7.20 in (18.3 cm)
Package 1 Width	6.42 in (16.3 cm)
Package 1 Length	19.37 in (49.2 cm)
Package 1 Weight	16.53 lb(US) (7.5 kg)

## **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

#### Well-being performance



#### **Certifications & Standards**


Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

## BSH1004P22A2A

#### **Dimensions Drawings**

#### **Servo Motors Dimensions**

#### **Example with Straight Connectors**



- a: Power supply for servo motor brake
- **b**: Power supply for servo motor encoder
- (1) M4 screw
- (2) Shaft end, keyed slot (optional)

Dimensions in mm

Straight connectors		Rotatable angled connectors		c (without	c (with	c1	c2	h	h1	Ø	Ø1 for
b1	b2	b1	b2	brake)	brake)						screws
39.5	25.5	39.5	39.5	277	308	50	40	8 N9	4 <sup>+0.1</sup> 0	24 k6	M8 x 19

Dimensions in in.

Straight Rotatable angled connectors connectors		·	c (without c (with	c1	c2	h	h1	Ø	Ø1 for		
b1	b2	b1	b2	brake)	brake)						screws
1.55	1.00	1.55	1.55	10.90	12.12	1.96	1.57	0.31 N9	0.16 <sup>+0.1</sup> <sub>0</sub>	0.94 k6	M8 x 0.75

### **Product data sheet**


## BSH1004P22A2A

#### Performance Curves

### 400 V 3-Phase Supply Voltage

#### **Torque/Speed Curves**

Servo motor with LXM32•D30N4 servo drive




- **X** Speed in rpm
- Y Torque in Nm
- 1 Peak torque
- 2 Continuous torque

#### 480 V 3-Phase Supply Voltage

#### **Torque/Speed Curves**

Servo motor with LXM32•D30N4 servo drive



- X Speed in rpm
- ${\bf Y}$  Torque in Nm
- 1 Peak torque
- 2 Continuous torque