# Product data sheet

Specifications





## servo motor BSH, Lexium 32, 32.1N.m, 3000rpm, 140mm, untapped shaft, Sincos single turn, with brake, IP65

BSH1404P21F2P

Product availability: Non-Stock - Not normally stocked in distribution facility

### Price\*: 3,455.00 USD

### Main

Mann					
Product Or Component Type	Servo motor				
Device Short Name	BSH				
Maximum Mechanical Speed	4000 rpm				
Continuous Stall Torque	295.61 lbf.in (33.4 N.m) LXM32.D72N4 24 A, 400 V, three phase 295.61 lbf.in (33.4 N.m) LXM32.D72N4 24 A, 480 V, three phase 284.11 lbf.in (32.1 N.m) LXM05AD57N4, 380480 V, three phase 284.11 lbf.in (32.1 N.m) LXM05BD57N4, 380480 V, three phase 284.11 lbf.in (32.1 N.m) LXM05CD57N4, 380480 V, three phase				
Peak Stall Torque	916.94 lbf.in (103.6 N.m) LXM32.D72N4 24 A, 400 V, three phase 916.94 lbf.in (103.6 N.m) LXM32.D72N4 24 A, 480 V, three phase 558.39 lbf.in (63.09 N.m) LXM05AD57N4, 380480 V, three phase 558.39 lbf.in (63.09 N.m) LXM05BD57N4, 380480 V, three phase 558.39 lbf.in (63.09 N.m) LXM05CD57N4, 380480 V, three phase				
Nominal Output Power	5000 W LXM32.D72N4 24 A, 400 V, three phase 5000 W LXM32.D72N4 24 A, 480 V, three phase 3400 W LXM05AD57N4, 380480 V, three phase 3400 W LXM05BD57N4, 380480 V, three phase 3400 W LXM05CD57N4, 380480 V, three phase				
Nominal Torque	168.16 lbf.in (19 N.m) LXM32.D72N4 24 A, 400 V, three phase 168.16 lbf.in (19 N.m) LXM32.D72N4 24 A, 480 V, three phase 95.59 lbf.in (10.8 N.m) LXM05AD57N4, 380480 V, three phase 95.59 lbf.in (10.8 N.m) LXM05BD57N4, 380480 V, three phase 95.59 lbf.in (10.8 N.m) LXM05CD57N4, 380480 V, three phase				
Nominal Speed	2500 rpm LXM32.D72N4 24 A, 400 V, three phase 2500 rpm LXM32.D72N4 24 A, 480 V, three phase 3000 rpm LXM05AD57N4, 380480 V, three phase 3000 rpm LXM05BD57N4, 380480 V, three phase 3000 rpm LXM05CD57N4, 380480 V, three phase				
Product Compatibility	LXM05AD57N4 380480 V three phase LXM05BD57N4 380480 V three phase LXM05CD57N4 380480 V three phase LXM32.D72N4 400 V three phase LXM32.D72N4 480 V three phase				
Shaft End	Untapped				
Ip Degree Of Protection	IP65 standard IP67 with IP67 kit				
Speed Feedback Resolution	131072 points/turn				
Holding Brake	With				
Mounting Support	International standard flange				
Electrical Connection	Rotatable right-angled connectors				

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

## Complementary

eemplementary				
Range Compatibility	Lexium 32 Lexium 05			
Supply Voltage Max	480 V			
Phase	Three phase			
Continuous Stall Current	21.3 A			
Maximum Continuous Power	4.33 W			
Maximum Current Irms	72 A LXM32.D72N4 95.6 A LXM05AD57N4 95.6 A LXM05BD57N4 95.6 A LXM05CD57N4			
Maximum Permanent Current	95.6 A			
Switching Frequency	8 kHz			
Second Shaft	Without second shaft end			
Shaft Diameter	0.94 in (24 mm)			
Shaft Length	1.97 in (50 mm)			
Feedback Type	Single turn SinCos Hiperface			
Holding Torque	318.63 lbf.in (36 N.m) holding brake			
Motor Flange Size	5.51 in (140 mm)			
Number Of Motor Stacks	4			
Torque Constant	1.57 N.m/A 248 °F (120 °C)			
Back Emf Constant	104 V/krpm 248 °F (120 °C)			
Number Of Motor Poles	10			
Rotor Inertia	29.2 kg.cm <sup>2</sup>			
Stator Resistance	0.28 Ohm 68 °F (20 °C)			
Stator Inductance	3.9 mH 68 °F (20 °C)			
Stator Electrical Time Constant	13.93 ms 68 °F (20 °C)			
Maximum Radial Force Fr	1840 N 3000 rpm 2110 N 2000 rpm 2660 N 1000 rpm			
Maximum Axial Force Fa	0.2 x Fr			
Brake Pull-In Power	26 W			
Type Of Cooling	Natural convection			
Length	16.56 in (420.5 mm)			
Centring Collar Diameter	5.12 in (130 mm)			
Centring Collar Depth	0.14 in (3.5 mm)			
Number Of Mounting Holes	4			
Mounting Holes Diameter	0.43 in (11 mm)			
Circle Diameter Of The Mounting Holes	6.50 in (165 mm)			
Net Weight	61.29 lb(US) (27.8 kg)			

## Ordering and shipping details

Category	US1PC5318282			
Discount Schedule	PC53			

Gtin	3389118361584 No		
Returnability			
Country Of Origin	DE		

## **Packing Units**

-			
Unit Type Of Package 1	PCE		
Number Of Units In Package 1	1		
Package 1 Height	10.63 in (27.0 cm)		
Package 1 Width	10.63 in (27.0 cm)		
Package 1 Length	23.86 in (60.6 cm)		
Package 1 Weight	45.42 lb(US) (20.6 kg)		

## **Contractual warranty**

Warranty

18 months

## Sustainability Screen Premium

**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

### Well-being performance

Mercury Free
Rohs Exemption Information Yes
Pvc Free


## **Certifications & Standards**

Reach Regulation	REACh Declaration					
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)					
China Rohs Regulation	China RoHS declaration					
Environmental Disclosure	Product Environmental Profile					
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.					
Circularity Profile	No need of specific recycling operations					
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov					

### **Dimensions Drawings**

#### Servo Motors Dimensions

#### **Example with Straight Connectors**



a: Power supply for servo motor brake

b: Power supply for servo motor encoder

(1) M4 screw

(2) Shaft end, keyed slot (optional)

(3) For screws M8 x 19 mm/M8 x 0.75 in.

Dimensions in mm

Straight connectors		nnectors Rotatable angled connectors				e (with heales)	
b	b1	b2	b	b1	b2	c (without brake)	c (with brake)
192.5	54	25.5	198.5	60	39.5	383	421

Dimensions in in.


Straig	Straight connectors			s Rotatable angled connectors			
b	b1	b2	b	b1	b2	c (without brake)	c (with brake)
7.57	2.12	1.00	7.81	2.36	1.55	15.07	16.57

### Performance Curves

### 400 V 3-Phase Supply Voltage

#### **Torque/Speed Curves**

Servo motor with LXM32•D72N4 servo drive



 $\boldsymbol{X}$  Speed in rpm

Y Torque in Nm


1 Peak torque

2 Continuous torque

#### 480 V 3-Phase Supply Voltage

#### **Torque/Speed Curves**

Servo motor with LXM32•D72N4 servo drive



X Speed in rpm

Y Torque in Nm

1 Peak torque

2 Continuous torque