Product data sheet

Specification





Control relay, TeSys K, 4 NO, It or eq to 690V, 127VAC coil

CA2KN40FC7

! Discontinued on: Jul 12, 2021

! Discontinued

Main

Range	TeSys	
Product Name	TeSys CAK	
Product Or Component Type	Control relay	
Device Short Name CA2K		
Contactor Application	Control circuit	
Utilisation Category	AC-15 DC-13	
Pole Contact Composition	4 NO	
[Ue] Rated Operational Voltage	e <= 690 V <= 400 Hz	
Control Circuit Type	AC 50/60 Hz	
[Uc] Control Circuit Voltage	127 V AC 50/60 Hz	

Complementary

[Ith] Conventional Free Air Thermal Current	10 A (at 122 °F (50 °C))	
Irms Rated Making Capacity	110 A IEC 60947	
Associated Fuse Rating	10 A gG conforming to IEC 60947 10 A gG conforming to VDE 0660	
[Ui] Rated Insulation Voltage	690 V IEC 60947 750 V VDE 0110 group C 690 V BS 5424 600 V CSA C22.2 No 14	
Mounting Support	Plate Rail	
Connections - Terminals	screw clamp terminals 1 0.000.01 in² (1.54 mm²)solid screw clamp terminals 2 0.000.01 in² (1.54 mm²)solid screw clamp terminals 1 0.000.01 in² (0.754 mm²)flexible with cable end screw clamp terminals 2 0.000.01 in² (0.754 mm²)flexible without cable end screw clamp terminals 1 0.000.00 in² (0.341.5 mm²)flexible with cable end screw clamp terminals 2 0.000.00 in² (0.341.5 mm²)flexible without cable end	
Tightening Torque	11.51 lbf.in (1.3 N.m) screw clamp terminals flat Ø 6 mm 11.51 lbf.in (1.3 N.m) screw clamp terminals Philips No 2 0.24 in (6 mm)	
Control Circuit Voltage Limits	Drop-out: 0.20.75 Uc (at <122 °F (50 °C)) Operational: 0.81.15 Uc (at <122 °F (50 °C))	
Operating Time	ng Time 1020 ms coil de-energisation and NO opening 1020 ms coil energisation and NO closing	
Mechanical Durability	10 Mcycles	
Maximum Operating Rate	10000 cyc/h	

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Immunity To Microbreaks	2 ms
Inrush Power In Va	30 VA (at 68 °F (20 °C))
Hold-In Power Consumption In Va	4.5 VA (at 68 °F (20 °C))
Heat Dissipation	1.3 W
Minimum Switching Voltage	17 V
Minimum Switching Current	5 mA
Non Overlap Distance	0.02 in (0.5 mm)
Insulation Resistance	> 10 MOhm
Height	2.28 in (58 mm)
Width	1.77 in (45 mm)
Depth	2.24 in (57 mm)
Net Weight	0.40 lb(US) (0.18 kg)

Environment

EN/IEC 60947-4-1
GB/T 14048.4
UL 60947-4-1
CSA C22.2 No 60947-4-1
JIS C8201-4-1
CB Scheme
CCC
UL
CSA
EAC
CE
UKCA
IP2X
TC IEC 60068
-13122 °F (-2550 °C)
-58176 °F (-5080 °C)
6561.68 ft (2000 m) without derating
V1 conforming to UL 94
Requirement 2 conforming to NF F 16-101
Requirement 2 conforming to NF F 16-102
Vibrations contactor open2 Gn, 5300 Hz IEC 60068-2-6
Vibrations contactor closed4 Gn, 5300 Hz IEC 60068-2-6
Shocks contactor open10 Gn for 11 ms IEC 60068-2-27
Shocks contactor closed15 Gn for 11 ms IEC 60068-2-27

Ordering and shipping details

Category	22371-RELAYS, CONTROL	
Discount Schedule 112		
Gtin 3389110482973		
Returnability	No	
Country Of Origin	FR	

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1

Package 1 Height	2.56 in (6.5 cm)	
Package 1 Width	2.44 in (6.2 cm)	
Package 1 Length	2.28 in (5.8 cm)	
Package 1 Weight	6.46 oz (183 g)	

Contractual warranty

Warranty 18 months

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

⊘	Reach Free Of Svhc	
⊘	Toxic Heavy Metal Free	
⊘	Mercury Free	
⊘	Rohs Exemption Information	Yes

Certifications & Standards

Compliant
EU RoHS Declaration
China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Product Environmental Profile
The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
End of Life Information
WARNING: This product can expose you to chemicals including: Antimony oxide & Antimony trioxide, which is known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov