

Product data sheet

Specifications

SQUARE D



NEMA Combination Starter, Type S, nonfusible disconnect, Size 0, 18A, 5 HP at 600 VAC polyphase, 120 VAC coil, NEMA 12

8538SBA11S8V02S

To be discontinued

To be discontinued on: Sep 30, 2024

Product availability: Non-Stock - Not normally stocked in distribution facility

Main

Contactor Application	Non-reversing
Device Short Name	S

Complementary

Depth	8.34 in (211.84 mm)
Device Mounting	Surface
Height	24 in (609.60 mm)
Nema Size	0
Number Of Poles	3
Number Of Thermal Units Required	3
Net Weight	40 lb(US) (18.14 kg)
Reset	Without external
Width	9.5 in (241.30 mm)

Environment

Nema Degree Of Protection	NEMA 12
Product Certifications	CSA LR584 class 3211 04 UL listed file E152395 CCN NKJH7

Ordering and shipping details

Category	21212 - 8538,39SB(NOT S*R,S*T,S*W)
Discount Schedule	CP1
Returnability	No
Country Of Origin	MX

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	24.02 in (61.0 cm)
Package 1 Width	9.49 in (24.1 cm)

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Length	8.35 in (21.2 cm)
Package 1 Weight	45.00 lb(US) (20.412 kg)

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Eu Rohs Directive

Under investigation