

# Product data sheet

Specifications



Mini circuit breaker, E-Frame, 30A, 2 pole, 480Y/277 VAC, 65 kA max, bolt on

EGB24030

Product availability: Stock - Normally stocked in distribution facility

Price\*: 776.00 USD

## Main

Range Of Product	125 A Frame EDB-EGB-EJB
Product Or Component Type	Miniature circuit-breaker
Device Short Name	EGB
Module Type	E-Frame
Trip Unit Rating	875 A

## Complementary

Line Rated Current	30 A
Maximum Operating Voltage	480Y/277 V AC
Awg Gauge	AWG 12...AWG 6 aluminium AWG 14...AWG 6 copper
Breaking Capacity	35 kA 277 V AC 65 kA 240 V AC 35 kA 480Y/277 V AC 65 kA 120 V AC 65 kA 120/240 V AC
Circuit Breaker Application	HID rated HACR rated
Electrical Connection	Lugs aluminium
Holding Current	270 A
Local Signalling	Trip indicator
Mounting Mode	Bolt-on
Number Of Poles	2
Number Of Spaces	2
Number Of Spaces Required	2
Product Destination	NF panelboard
Protection Type	Short-circuit Overload
Trip Unit Technology	Thermal-magnetic
Breaking Capacity Code	G
Tightening Torque	30.09 lbf.in (3.4 N.m) 0.00...0.02 in² (2.5...16 mm²) (AWG 14...AWG 6)
Height	5.66 in (143.76 mm)
Width	1.96 in (49.78 mm)

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Depth	4.05 in (102.87 mm)
Net Weight	3 lb(US) (1.36 kg)

## Environment

Product Certifications	cULus
Ambient Air Temperature For Operation	104 °F (40 °C)

## Ordering and shipping details

Category	US10DE200936
Discount Schedule	0DE2
Gtin	785901397694
Returnability	Yes
Country Of Origin	US

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.58 in (9.1 cm)
Package 1 Width	6.10 in (15.5 cm)
Package 1 Length	9.80 in (24.9 cm)
Package 1 Weight	2.65 lb(US) (1.2 kg)

## Contractual warranty

Warranty	18 months
----------	-----------

# Sustainability



**Green Premium™ label** is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)

## Well-being performance

 Mercury Free	
 Rohs Exemption Information	<a href="#">Yes</a>
Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	<a href="#">China RoHS declaration</a> Product out of China RoHS scope. Substance declaration for your information.