

# Product data sheet

Specifications



## COMBO STARTER 600VAC 18A NEMA

8538SBA21V81AFF4T

 To be discontinued on: Sep 30, 2024

 To be discontinued

Product availability: Non-Stock - Not normally stocked in distribution facility

### Main

|                      |                             |
|----------------------|-----------------------------|
| Product              | Combination Starter         |
| Type                 | S                           |
| Control Circuit Type | Control circuit transformer |

### Complementary

|                         |  |
|-------------------------|--|
| Control Circuit Voltage | 120 V AC 60 Hz secondary circuit<br>480 V AC 60 Hz primary circuit                                   |
| Starter Type            | Non reversing  |
| Number Of Poles         | 3P   |
| Horsepower Rating       | 3 hp 200 V AC, 3 phase<br>3 hp 230 V AC, 3 phase<br>5 hp 460 V AC, 3 phase<br>5 hp 575 V AC, 3 phase |
| Maximum Voltage Rating  | 600 V AC   |
| Control Units           | Push-button START)<br>Push-button STOP)  |
| Pilot Light             | No indicator   |
| Auxiliary Contacts      | Without  |
| Control Circuit Fusing  | 2 fuses primary circuit<br>1 fuse secondary circuit  |
| Thermal Overload Type   | Melting alloy 3  |
| Disconnect Type         | Non-fusible disconnect switch  |
| Nema Size               | 0  |

### Environment

|                |   |
|----------------|---|
| Enclosure Type | NEMA 12 painted sheet steel with external reset |
|----------------|---|

### Ordering and shipping details

|                   |                                    |
|-------------------|------------------------------------|
| Category          | 21212 - 8538,39SB(NOT S*R,S*T,S*W) |
| Discount Schedule | CP1                                |
| Gtin              | 785901951780                       |
| Returnability     | No                                 |
| Country Of Origin | MX                                 |

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

## Packing Units

|                              |                          |
|------------------------------|--------------------------|
| Unit Type Of Package 1       | PCE                      |
| Number Of Units In Package 1 | 1                        |
| Package 1 Weight             | 45.00 lb(US) (20.412 kg) |

## Contractual warranty

|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

# Sustainability

**Green Premium™ label** is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)

|                           |   |
|---------------------------|---|
| Eu Rohs Directive         | Not compliant   |
| China Rohs Regulation     | <a href="#">China RoHS declaration</a><br>Product out of China RoHS scope. Substance declaration for your information.  |
| California Proposition 65 | WARNING: This product can expose you to chemicals including: Lead and lead compounds which is known to the State of California to cause Carcinogen & Reproductive harm. For more information go to <a href="http://www.p65warnings.ca.gov">www.p65warnings.ca.gov</a> |