

Product data sheet

Specifications

SQUARE D



COMBO STARTER 600VAC 90A NEMA

8539SEG1V02S

! Discontinued

Main

| | |
|--------------------------|--|
| Contactor Application | Non-reversing |
| Device Short Name | S |
| Disconnecter Device Type | Thermal magnetic circuit breaker 100 A |

Complementary

| | |
|----------------------------------|--|
| Depth | 10.59 in (268.99 mm) |
| Device Mounting | Surface |
| Height | 42 in (1066.80 mm) |
| Maximum Horse Power Rating | 20 hp 200 V AC 25 hp 230 V AC 50 hp 480 V AC |
| Nema Size | 3 |
| Number Of Poles | 3 |
| Number Of Thermal Units Required | 3 |
| Product Destination | Circuit breaker FAL |
| Net Weight | 102 lb(US) (46.27 kg) |
| Width | 15.25 in (387.35 mm) |

Environment

| | |
|---------------------------|----------------------------------|
| Nema Degree Of Protection | NEMA 1 |
| Product Certifications | UL listed file E152395 CCM NKJH7 |

Ordering and shipping details

| | |
|-------------------|----------------------------------|
| Category | 21214-8538,39 SE,SF(NOT S*R,T,W) |
| Discount Schedule | CP1 |
| Returnability | No |

Packing Units

| | |
|------------------------------|---------------------------|
| Unit Type Of Package 1 | PCE |
| Number Of Units In Package 1 | 1 |
| Package 1 Weight | 116.00 lb(US) (52.617 kg) |

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|