

Product data sheet

Specifications

SQUARE D



COMBO STARTER 600VAC 90A NEMA

8539SET42V02S

Discontinued

Main

Contactor Application	Non-reversing
Device Short Name	S

Complementary

Depth	10 in (254.00 mm)
Device Mounting	Surface
Height	31.63 in (803.40 mm)
Maximum Horse Power Rating	15...25 hp 200 V AC 15...30 hp 230 V AC 30...50 hp 460 V AC 40...50 hp 575 V AC
Nema Size	3
Number Of Poles	3
Number Of Thermal Units Required	3
Product Destination	Circuit breaker FAL3610018M
Net Weight	180 lb(US) (81.65 kg)
Width	18.06 in (458.72 mm)

Environment

Nema Degree Of Protection	NEMA 7/9
---------------------------	----------

Ordering and shipping details

Category	21217-8538,39 S*R,S*T,S*W
Discount Schedule	CP1
Returnability	No

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Weight	185.00 lb(US) (83.915 kg)

Contractual warranty

Warranty	18 months
----------	-----------

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

