


Product data sheet

Specifications



auxiliary blown fuse signalling
contact - TeSys GS - 1st C/O - 4
poles - 630 A

GS1AF64

⚠ Discontinued

Main

Range Of Product	TeSys GS 630
Device Short Name	auxiliary blown fuse contact
Product Or Component Type	Auxiliary contact
Product Compatibility	GS 630
Poles Description	4P
[Ie] Rated Operational Current	12 A 24 V DC-13 2 A 48 V DC-13 3 A 400 V AC-15 4 A 230 V AC-15 0.4 A 220 V DC-13 0.6 A 110 V DC-13

Complementary

Fuse Type	NFC DIN
Fuse Size	T3
Contacts Type And Composition	1 NO/NC
Net Weight	0.22 lb(US) (0.1 kg)

Ordering and shipping details

Category	18402-WORLD SERVICE PARTS(CONTROL ACCESS)
Discount Schedule	CP10
Gtin	3389110563405
Returnability	No

Contractual warranty

Warranty	18 months
----------	-----------

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

California Proposition 65

WARNING: This product can expose you to chemicals including: Antimony oxide & Antimony trioxide, which is known to the State of California to cause cancer. Bisphenol A (BPA), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.p65warnings.ca.gov
