# **Product data sheet**

Specifications





Switch disconnector fuse, TeSys GS, 3P, 3NO, 125A, 11W, fuse type NFC, size 22x58mm

GS1KD3

(!) Discontinued

#### Main

Range	TeSys
Product Name	TeSys GS
Device Short Name	GS1 K
Product Or Component Type	Switch-disconnector-fuse
Device Application	Protection
Poles Description	3P
Protected Poles Description	3t
Contacts Type And Composition	3 NO
[Ith] Conventional Free Air Thermal Current	125 A (at 104 °F (40 °C))
[le] Rated Operational Current	100 A 440 V 2 poles in series per phase DC-23A 100 A 440 V 2 poles in series per phase DC-23B 100 A 690 V with terminal cover AC-23A 100 A 690 V with terminal cover AC-23B 125 A 400 V AC-23A 125 A 500 V AC-23A 125 A 500 V AC-23A
Fuse Type	NFC
Fuse Size	22 x 58 mm
Network Type	DC AC
Network Frequency	50/60 Hz

### Complementary

Type Of Operating Handle	Direct right side
Mounting Support	Plate
[Ui] Rated Insulation Voltage	750 V AC 50/60 Hz
[Uimp] Rated Impulse Withstand Voltage	8 kV
Rated Operational Power In W	90 kW 690 V 63 kW 400 V 90 kW 500 V
Breaking Capacity	11 W
Making Capacity	1250 A 400 V AC-23B
Breaking Capacity	1000 A 400 V AC-23B)
Short-Circuit Withstand	20 kA

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Mechanical Durability	10000 cycles
Electrical Durability	1000 cycles AC-23A 1000 cycles AC-23B
Connections - Terminals	Power circuit bars Power circuit lugs-ring terminals 0.050.15 in² (3595 mm²) flexible
[Icm] Rated Short-Circuit Making Capacity	100 kA 400 V with protection by gG fuses
Tightening Torque	Power circuit 106.21 lbf.in (12 N.m) bars Power circuit 106.21 lbf.in (12 N.m) luas-ring terminals

#### **Environment**

Standards	IEC 60947-3	
Product Certifications	CE	
Protective Treatment	тн	
Ip Degree Of Protection	IP20 IEC 60529 with terminal cover)	
Ambient Air Temperature For Operation	-4158 °F (-2070 °C)	
Ambient Air Temperature For Storage	-40176 °F (-4080 °C)	
Fire Resistance	1562 °F (850 °C) fuse cover IEC 60695-2-1 1760 °F (960 °C) body IEC 60695-2-1	
Height	6.38 in (162 mm)	
Width	5.91 in (150 mm)	
Depth	4.57 in (116 mm)	
Net Weight	3.31 lb(US) (1.5 kg)	

### Ordering and shipping details

Category	18402-WORLD SERVICE PARTS(CONTROL ACCESS)	
Discount Schedule	CP10	
Gtin	3389110253948	
Returnability	No	
Country Of Origin	TN	

## **Packing Units**

Unit Type Of Package 1	PCE	
Number Of Units In Package 1	1	
Package 1 Height	7.87 in (20.0 cm)	
Package 1 Width	10.04 in (25.5 cm)	
Package 1 Length	7.87 in (20.0 cm)	
Package 1 Weight	3.81 lb(US) (1.73 kg)	
Unit Type Of Package 2	S06	
Unit Type Of Package 2  Number Of Units In Package 2	S06       27	
Number Of Units In Package 2	27	
Number Of Units In Package 2 Package 2 Height	27 29.53 in (75.0 cm)	

### **Contractual warranty**

Warranty

Apr 23, 2024

18 months

### Sustainability Green Premium

**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

#### Well-being performance

<b>Ø</b>	Reach Free Of Svhc	
<b>Ø</b>	Toxic Heavy Metal Free	
<b>9</b>	Mercury Free	
<b>⊘</b>	Rohs Exemption Information	Yes

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information
California Proposition 65	WARNING: This product can expose you to chemicals including: Styrene, which is known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov