

Product data sheet

Specifications



Contactor, Type S, combination lighting, electrically held, 30A, 3 pole, no fuse, 110/120 VAC 50/60 Hz coil, NEMA 1

8903SMG60V02C

⚠ To be discontinued

⚠ To be discontinued on: Apr 30, 2024

Product availability: Non-Stock - Not normally stocked in distribution facility

Main

| | |
|---------|--|
| Product | Combination electrically held lighting contactor |
| Type | S |

Complementary

| | |
|--------------------------|--|
| Control Circuit Voltage | 120 V AC 60 Hz 110 V AC 50 Hz |
| Current Rating | 30 A |
| Number Of Poles | 3P |
| Control Units | Selector switch 3 positions HAND-OFF-AUTO) |
| Pilot Light | Without pilot light |
| Auxiliary Contacts | Without |
| Other Options | None |
| Disconnecter Device Type | Non-fusible disconnect switch |
| Electrical Connection | Lugs |
| Height | 22.52 in (572 mm) |
| Depth | 8.39 in (213 mm) |
| Width | 9.49 in (241 mm) |

Environment

| | |
|------------------------|---|
| Enclosure Type | NEMA 1 painted sheet steel surface none |
| Product Certifications | UL listed file E16151 CCN NRNT |

Ordering and shipping details

| | |
|-------------------|---------------------------------|
| Category | 21325 - 8903 S (NOT S*C) ELECT. |
| Discount Schedule | CP1 |
| Returnability | No |
| Country Of Origin | MX |

Packing Units

| | |
|------------------------|-----|
| Unit Type Of Package 1 | PCE |
|------------------------|-----|

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

| | |
|------------------------------|-------------------------|
| Number Of Units In Package 1 | 1 |
| Package 1 Height | 22.52 in (57.2 cm) |
| Package 1 Width | 9.49 in (24.1 cm) |
| Package 1 Length | 8.39 in (21.3 cm) |
| Package 1 Weight | 28.18 lb(US) (12.78 kg) |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

| | |
|-----------------------|--|
| Eu Rohs Directive | Under investigation |
| China Rohs Regulation | China RoHS declaration Product out of China RoHS scope. Substance declaration for your information. |