

# Product data sheet

Specifications



## Linergy FT, Comb busbar, 63A, 4 tap-offs, 54mm pitch



GV2G454

Product availability: Stock - Normally stocked in distribution facility

Price\*: 34.20 USD

### Main

|   |   |
|---|---|
| Range                                       | Linergy                                       |
| Product Name                                | FT  |
| Device Short Name                           | GV2G  |
| Product Or Component Type                   | Comb busbar                                   |
| Accessory / Separate Part Category          | Connection accessory                          |
| Poles Description                           | 3P  |
| Range Compatibility                         | TeSys Deca<br>TeSys GV2<br>TeSys K<br>TeSys U |
| Number Of Tap-Offs                          | 4   |
| [Ith] Conventional Free Air Thermal Current | 63 A  |
| Connection Pitch                            | 2.13 in (54 mm)                               |

### Complementary

|                               |                        |
|-------------------------------|------------------------|
| Mounting Location             | On terminal            |
| [Ui] Rated Insulation Voltage | 690 V                  |
| Length                        | 8.11 in (206 mm)       |
| Net Weight                    | 0.19 lb(US) (0.085 kg) |

### Ordering and shipping details

|                   |               |
|-------------------|---------------|
| Category          | US10I1122367  |
| Discount Schedule | 0I11          |
| Gtin              | 3389110555875 |
| Returnability     | Yes           |
| Country Of Origin | FR            |

### Packing Units

|                              |                     |
|------------------------------|---------------------|
| Unit Type Of Package 1       | PCE                 |
| Number Of Units In Package 1 | 1                   |
| Package 1 Height             | 0.75 in (1.900 cm)  |
| Package 1 Width              | 1.46 in (3.700 cm)  |
| Package 1 Length             | 8.50 in (21.600 cm) |

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

|                              |                            |
|------------------------------|----------------------------|
| Package 1 Weight             | 3.10 oz (88.000 g)         |
| Unit Type Of Package 2       | S01                        |
| Number Of Units In Package 2 | 50                         |
| Package 2 Height             | 5.91 in (15.000 cm)        |
| Package 2 Width              | 5.91 in (15.000 cm)        |
| Package 2 Length             | 15.75 in (40.000 cm)       |
| Package 2 Weight             | 10.20 lb(US) (4.628 kg)    |
| Unit Type Of Package 3       | P06                        |
| Number Of Units In Package 3 | 1600                       |
| Package 3 Height             | 29.53 in (75.000 cm)       |
| Package 3 Width              | 23.62 in (60.000 cm)       |
| Package 3 Length             | 31.50 in (80.000 cm)       |
| Package 3 Weight             | 345.02 lb(US) (156.500 kg) |

## Contractual warranty

|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

Sustainability



**Green Premium™ label** is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency   RoHS/REACH

Well-being performance


|   |                            |     |
|---|----------------------------|-----|
| ✓ | Reach Free Of Svhc         |     |
| ✓ | Toxic Heavy Metal Free     |     |
| ✓ | Mercury Free               |     |
| ✓ | Rohs Exemption Information | Yes |

Certifications & Standards

|                          |  |
|--------------------------|--|
| Reach Regulation         | <a href="#">REACH Declaration</a>                |
| Eu Rohs Directive        | Compliant<br><a href="#">EU RoHS Declaration</a> |
| China Rohs Regulation    | <a href="#">China RoHS declaration</a>           |
| Environmental Disclosure | <a href="#">Product Environmental Profile</a>    |
| Circularity Profile      | <a href="#">End of Life Information</a>          |

Dimensions Drawings

Sets of Busbars GV2G445, GV2G454, GV2G472, with Terminal Block GV2G05



|                     | l   | p  |
|---------------------|-----|----|
| GV2G445 (4 x 45 mm) | 179 | 45 |
| GV2G454 (4 x 54 mm) | 206 | 54 |
| GV2G472 (4 x 72 mm) | 260 | 72 |

| Number of tap-offs | a   |     |     |     |
|--------------------|-----|-----|-----|-----|
|                    | 5   | 6   | 7   | 8   |
| GV2G445            | 224 | 269 | 314 | 359 |
| GV2G454            | 260 | 314 | 368 | 422 |
| GV2G472            | 332 | 404 | 476 | 548 |