Product data sheet

Specifications



() Discontinued

Pilot light head, Harmony 9001K, metal, without cap, 30mm, LED yellow, 24-28V

9001KP35LY

Discontinued on: Jun 30, 2023

Product availability: Non-Stock - Not normally stocked in distribution facility

Main

| Range Of Product | Harmony 9001K | |
|---------------------------|----------------------|--|
| Product Or Component Type | Head for pilot light | |
| Device Short Name | 9001K | |

Complementary

| Complementary | |
|--|--|
| Bezel Material | Metal |
| Mounting Diameter | 1.18 in (30 mm) |
| Shape Of Signaling Unit Head | Round |
| Lens Type | Domed plastic |
| Cap/Operator Or Lens Colour | Without cap |
| Light Source | Yellow LED |
| Bulb Base | BA 9s |
| Light Block Supply | Direct 2428 V AC/DC |
| Connections - Terminals | Screw clamp terminals, 1 x 0.222 x 1.5 mm ² IEC 60947-1 |
| Tightening Torque | 7.08 lbf.in (0.8 N.m) IEC 60947-1 |
| Shape Of Screw Head | Cross slotted |
| Operating Position | Any position |
| [Ui] Rated Insulation Voltage | 250 V 2)IEC 60947-1 |
| [Uimp] Rated Impulse Withstand Voltage | 2.5 kV IEC 60947-1 |
| Short-Circuit Protection | 10 A cartridge fuse IEC 60947-5-1 |
| Light Source | LED |
| [Ith] Conventional Free Air Thermal Current | 10 A |
| Cad Overall Width | 2.13 in (54 mm) |
| Cad Overall Height | 2.76 in (70 mm) |
| Cad Overall Depth | 1.65 in (42 mm) |
| Net Weight | 0.30 lb(US) (0.134 kg) |
| [Us] Rated Supply Voltage | 2428 V |
| Light Source Colour | Yellow |
| Size | 30 mm |

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Environment

| Standards | UL 508 EN/IEC 60947-5-1 EN/IEC 60947-5-4 | |
|--|--|--|
| | CSA C22.2 No 14 JIS C 852 | |
| | JIS C 852 JIS C8201-5-1 | |
| | EN/IEC 60947-1 | |
| | JIS C8201-1 | |
| Product Certifications | NEMA | |
| | UL 508 | |
| Protective Treatment | TC | |
| Ambient Air Temperature For Storage | -40158 °F (-4070 °C) | |
| Ambient Air Temperature For Operation | -13158 °F (-2570 °C) | |
| Vibration Resistance | 7 gn 2500 Hz)IEC 60068-2-6 | |
| Shock Resistance | 50 gn IEC 60068-2-27 | |
| Overvoltage Category | Class II IEC 61140 | |
| Ip Degree Of Protection | IP66 IEC 60529 | |
| Nema Degree Of Protection | NEMA 1 | |
| | NEMA 12 | |
| | NEMA 13 | |
| | NEMA 2 | |
| | NEMA 3 | |
| | NEMA 3R | |
| | NEMA 4 | |
| | NEMA 6 | |

Ordering and shipping details

| Category | US10CS121426 | |
|-------------------|--------------|--|
| Discount Schedule | 0CS1 | |
| Gtin | 785901974147 | |
| Returnability | No | |
| Country Of Origin | MX | |

Packing Units

| Unit Type Of Package 1 | PCE |
|------------------------------|------------------|
| Number Of Units In Package 1 | 1 |
| Package 1 Height | 2.24 in (5.7 cm) |
| Package 1 Width | 1.97 in (5 cm) |
| Package 1 Length | 3.74 in (9.5 cm) |
| Package 1 Weight | 5.04 oz (143 g) |

Contractual warranty

Warranty

18 months

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Mercury Free

Rohs Exemption Information Yes

Certifications & Standards

| Reach Regulation | REACh Declaration |
|---------------------------|--|
| Eu Rohs Directive | Pro-active compliance (Product out of EU RoHS legal scope) |
| China Rohs Regulation | China RoHS declaration |
| Environmental Disclosure | Product Environmental Profile |
| Weee | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins. |
| Circularity Profile | No need of specific recycling operations |
| California Proposition 65 | WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov |