





Pilot light, Harmony 9001K, metal, glass, domed, red, 30mm, LED red, 120V

9001KP38LRR6

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 153.00 USD

Main

| Range Of Product | Harmony 9001K |
|---------------------------|---------------|
| Product Or Component Type | Pilot light |
| Device Short Name | 9001K |

Complementary

| J | |
|--|--|
| Bezel Material | Metal |
| Mounting Diameter | 1.18 in (30 mm) |
| Shape Of Signaling Unit Head | Round |
| Lens Type | Domed glass |
| Cap/Operator Or Lens Colour | Red |
| Light Source | Red LED |
| Bulb Base | BA 9s |
| Light Block Supply | Direct 120 V AC/DC |
| Connections - Terminals | Screw clamp terminals, 1 x 0.222 x 1.5 mm² IEC 60947-1 |
| Tightening Torque | 7.08 lbf.in (0.8 N.m) IEC 60947-1 |
| Shape Of Screw Head | Cross slotted |
| Operating Position | Any position |
| [Ui] Rated Insulation Voltage | 250 V 2)IEC 60947-1 |
| [Uimp] Rated Impulse Withstand Voltage | 2.5 kV IEC 60947-1 |
| Short-Circuit Protection | 10 A cartridge fuse IEC 60947-5-1 |
| Light Source | LED |
| [Ith] Conventional Free Air Thermal Current | 10 A |
| Cad Overall Width | 2.13 in (54 mm) |
| Cad Overall Height | 2.76 in (70 mm) |
| Cad Overall Depth | 1.65 in (42 mm) |
| [Us] Rated Supply Voltage | 120 V AC/DC |
| Net Weight | 0.30 lb(US) (0.134 kg) |
| Device Presentation | Complete product |
| Lens Type | Domed |

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

| [Us] Rated Supply Voltage | 120 V |
|---------------------------|-------|
| Light Source Colour | Red |
| Lens Material | Glass |
| Size | 30 mm |

Environment

| LIIVII OIIIIICIIL | |
|---------------------------------------|--|
| Standards | EN/IEC 60947-5-1 JIS C8201-5-1 CSA C22.2 No 14 UL 508 EN/IEC 60947-1 JIS C 852 EN/IEC 60947-5-4 JIS C8201-1 |
| Product Certifications | UL 508 NEMA |
| Protective Treatment | тс |
| Ambient Air Temperature For Storage | -40158 °F (-4070 °C) |
| Ambient Air Temperature For Operation | -13158 °F (-2570 °C) |
| Vibration Resistance | 7 gn 2500 Hz)IEC 60068-2-6 |
| Shock Resistance | 50 gn IEC 60068-2-27 |
| Overvoltage Category | Class II IEC 61140 |
| Ip Degree Of Protection | IP66 IEC 60529 |
| Nema Degree Of Protection | NEMA 1 NEMA 12 NEMA 13 NEMA 2 NEMA 3 NEMA 3 NEMA 3R NEMA 4 NEMA 6 |

Ordering and shipping details

| Category | US10CS121426 |
|-------------------|--------------|
| Discount Schedule | 0CS1 |
| Gtin | 785901126096 |
| Returnability | No |
| Country Of Origin | US |

Packing Units

| Unit Type Of Package 1 | PCE |
|------------------------------|----------------------|
| Number Of Units In Package 1 | 1 |
| Package 1 Height | 5.08 in (12.903 cm) |
| Package 1 Width | 2.00 in (5.08 cm) |
| Package 1 Length | 12.90 in (32.774 cm) |
| Package 1 Weight | 5.12 oz (145.15 g) |

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Mercury Free



Rohs Exemption Information

Yes

Certifications & Standards

| Reach Regulation | REACh Declaration |
|---------------------------|---|
| Eu Rohs Directive | Pro-active compliance (Product out of EU RoHS legal scope) |
| China Rohs Regulation | China RoHS declaration |
| Environmental Disclosure | Product Environmental Profile |
| Weee | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins. |
| Circularity Profile | No need of specific recycling operations |
| California Proposition 65 | WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov |