Product data sheet

Specifications



() Discontinued

Push-to-test pilot light, Harmony 9001K, metal, glass, domed, red, 30mm, 110-120V flashing

9001KTF1R6

() Discontinued on: Jul 6, 2022

Product availability: Non-Stock - Not normally stocked in distribution facility

Main

Range Of Product	Harmony 9001K	
Product Or Component Type	Push-to-test pilot light	
Device Short Name	9001K	

Complementary

Complementary	
Bezel Material	Metal
Mounting Diameter	1.18 in (30 mm)
Shape Of Signaling Unit Head	Round
Lens Type	Domed glass
Cap/Operator Or Lens Colour	Red
Light Source	incandescent flashing
Bulb Base	BA 9s
Light Block Supply	Direct 110120 V AC 50/60 Hz
Connections - Terminals	Screw clamp terminals, 1 x 0.222 x 1.5 mm² IEC 60947-1
Tightening Torque	7.08 lbf.in (0.8 N.m) IEC 60947-1
Shape Of Screw Head	Cross slotted
Operating Position	Any position
[Ui] Rated Insulation Voltage	250 V 2)IEC 60947-1
[Uimp] Rated Impulse Withstand Voltage	2.5 kV IEC 60947-1
Short-Circuit Protection	10 A cartridge fuse IEC 60947-5-1
Light Source	Incandescent bulb
[Ith] Conventional Free Air Thermal Current	10 A
Cad Overall Width	2.13 in (54 mm)
Cad Overall Height	2.76 in (70 mm)
Cad Overall Depth	1.65 in (42 mm)
Operating Mode	Push-to-test
Net Weight	0.46 lb(US) (0.21 kg)
Lens Type	Domed
[Us] Rated Supply Voltage	110120 V

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Light Block Supply	Flashing
Contacts Type And Composition	1 C/O
Supply Frequency	5060 Hz
Lens Material	Glass
Size	30 mm

Environment

Standards	JIS C8201-5-1 EN/IEC 60947-5-4 CSA C22.2 No 14 UL 508 EN/IEC 60947-5-1 JIS C 852 EN/IEC 60947-1 JIS C8201-1	
Product Certifications	NEMA UL 508	
Protective Treatment	TC	
Ambient Air Temperature For Storage	-40158 °F (-4070 °C)	
Ambient Air Temperature For Operation	-13158 °F (-2570 °C)	
Vibration Resistance	7 gn 2500 Hz)IEC 60068-2-6	
Shock Resistance	50 gn IEC 60068-2-27	
Overvoltage Category	Class II IEC 61140	
Ip Degree Of Protection	IP66 IEC 60529	
Nema Degree Of Protection	NEMA 1 NEMA 12 NEMA 13 NEMA 2 NEMA 3 NEMA 3 NEMA 4 NEMA 6	

Ordering and shipping details

Category	US10CS121426	
Discount Schedule	0CS1	
Gtin	785901119449	
Returnability	No	
Country Of Origin	MX	

Contractual warranty

Warranty

18 months

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Mercury Free

Rohs Exemption Information
Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Circularity Profile	No need of specific recycling operations Circularity Profile
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov