Specifications





# TeSys Deca Manual Starter and Protector, thermal magnetic circuit protector, rotary knob, 30 to 40 A, EverLink BTR

GV3P40

Product availability: Stock - Normally stocked in distribution facility

### Price\*: 504.00 USD

### Main

Range	TeSys Deca
Product Name	TeSys GV3 TeSys Deca
Product Or Component Type	Motor circuit breaker
Device Short Name	GV3P
Device Application	Motor protection
Trip Unit Technology	Thermal-magnetic

### Complementary

Complementary	
Poles Description	3P
Network Type	AC
Utilisation Category	AC-3 IEC 60947-4-1
Network Frequency	50/60 Hz IEC 60947-4-1
Fixing Mode	35 mm symmetrical DIN rail clipped
	Panel screwed with 3 x M4 screws)
Motor Power Kw	18.5 kW 400/415 V AC 50/60 Hz
	22 kW 500 V AC 50/60 Hz
	37 kW 690 V AC 50/60 Hz
Breaking Capacity	100 kA lcu 230/240 V AC 50/60 Hz IEC 60947-2
	50 kA lcu 400/415 V AC 50/60 Hz IEC 60947-2
	50 kA lcu 440 V AC 50/60 Hz IEC 60947-2
	12 kA lcu 500 V AC 50/60 Hz IEC 60947-2
	6 kA lcu 690 V AC 50/60 Hz IEC 60947-2
[Ics] Rated Service Short-Circuit	100 % 230/240 V AC 50/60 Hz IEC 60947-2
Breaking Capacity	100 % 400/415 V AC 50/60 Hz IEC 60947-2
	100 % 440 V AC 50/60 Hz IEC 60947-2
	50 % 500 V AC 50/60 Hz IEC 60947-2
	50 % 690 V AC 50/60 Hz IEC 60947-2
Control Type	Rotary handle
Line Rated Current	40 A
Thermal Protection Adjustment Range	3040 A IEC 60947-4-1
Magnetic Tripping Current	560 A
[Ith] Conventional Free Air Thermal Current	40 A IEC 60947-4-1
[Ue] Rated Operational Voltage	690 V AC 50/60 Hz IEC 60947-2

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

[Ui] Rated Insulation Voltage	690 V AC 50/60 Hz IEC 60947-2
[Uimp] Rated Impulse Withstand Voltage	6 kV IEC 60947-2
Phase Failure Sensitivity	Yes IEC 60947-4-1
Suitability For Isolation	Yes IEC 60947-1
Power Dissipation Per Pole	8 W
Mechanical Durability	50000 cycles
Electrical Durability	50000 cycles AC-3 415 V In
Rated Duty	Continuous IEC 60947-4-1
Tightening Torque	44.25 lbf.in (5 N.m) screw clamp terminal
Width	2.17 in (55 mm)
Height	5.20 in (132 mm)
Depth	5.35 in (136 mm)
Net Weight	2.12 lb(US) (0.96 kg)
Color	Dark grey

# Environment

Standards	EN/IEC 60947-2 EN/IEC 60947-4-1 UL 60947-4-1 CSA C22.2 No 60947-4-1
Product Certifications	CCC UL CSA EAC ATEX LROS (Lloyds register of shipping) BV ABS DNV-GL UKCA
Ik Degree Of Protection	IK09 enclosure
Ip Degree Of Protection	IP20 IEC 60529
Climatic Withstand	IACS E10
Ambient Air Temperature For Storage	-40176 °F (-4080 °C)
Fire Resistance	1760 °F (960 °C) IEC 60695-2-11
Ambient Air Temperature For Operation	-4140 °F (-2060 °C)
Mechanical Robustness	Shocks 15 Gn for 11 ms contactor open Shocks 30 Gn for 11 ms contactor closed Vibrations 4 Gn, 5300 Hz
Operating Altitude	9842.52 ft (3000 m)

# Ordering and shipping details

Category	US10I1122366
Discount Schedule	0111
Gtin	3389119405393
Returnability	Yes
Country Of Origin	FR

# **Packing Units**

-	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	6.30 in (16.000 cm)
Package 1 Width	2.56 in (6.500 cm)
Package 1 Length	5.75 in (14.600 cm)
Package 1 Weight	34.67 oz (983.000 g)
Unit Type Of Package 2	P06
Number Of Units In Package 2	120
Package 2 Height	29.53 in (75.000 cm)
Package 2 Width	23.62 in (60.000 cm)
Package 2 Length	31.50 in (80.000 cm)
Package 2 Weight	295.33 lb(US) (133.960 kg)

# **Contractual warranty**

Warranty

18 months

# Sustainability Screen Premium

**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

### Well-being performance

Mercury Free

Rohs Exemption Information Yes


### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Circularity Profile	End of Life Information
California Proposition 65	WARNING: This product can expose you to chemicals including: Antimony oxide & Antimony trioxide, which is known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov

#### Performance Curves

#### **Thermal-Magnetic Tripping Curves**

Average Operating Times at 20 °C Related to Multiples of the Setting Current




- 1a 3 poles from cold state (Ir minimum): GV3P
- 1b 3 poles from cold state (Ir maximum): GV3P
- 2a 3 poles from hot state (Ir minimum): GV3P
- 2b 3 poles from hot state (Ir maximum): GV3P

#### Current Limitation on Short-Circuit (3-Phase 400/415 V)

#### **Dynamic Stress**


I peak = f (prospective Isc) at 1.05 Ue = 435 V



- 1 Maximum peak current
- 2 70-80 A (GV3P80), 62-73 A (GV3P73)
- 3 48-65 A (GV3P65)
- 4 37-50 A (GV3P50)
- 5 30-40 A (GV3P40)
- 6 23-32 A (GV3P32)
- 7 17-25 A (GV3P25)
- 8 12-18 A (GV3P18)
- 9 9-13 A (GV3P13)

#### Maximum Thermal Limit on Short-Circuit

Thermal Limit in kA<sup>2</sup>s in the Magnetic Operating Zone Sum of  $I^2$ dt = f (prospective Isc) at 1.05 Ue = 435 V




- 1 70-80 (GV3P80) 62-73 (GV3P73)
- 2 48-65 A (GV3P65)
- 3 37-50 A (GV3P50)
- 4 30-40 A (GV3P40)
- 5 23-32 A (GV3P32)
- 6 17-25 A (GV3P25)
- 7 12-18 A (GV3P18)
- 8 9-13 A (GV3P13)

#### **Dimensions Drawings**

# GVI3L, GV3P

Dimensions




- (1) Blocks  $\text{GVAN}_{\bullet\bullet}$ ,  $\text{GVAD}_{\bullet\bullet}$  and GVAM11.
- (2) Blocks  $\text{GV3AU}_{\bullet\bullet}$  and  $\text{GV3AS}_{\bullet\bullet}$ .


X1 = Electrical clearance (ISC max) 40 mm for Ue  $\leq$  500 V, 50 mm for Ue  $\leq$  690 V

**NOTE:** Leave a space of 9 mm between 2 circuit breakers: either an empty space or side-mounting add-on contact blocks. Side by side mounting is possible up to 40 °C.


#### Mounting on Rail AM1 DE200 or AM1 ED201



Panel Mounting, using M4 Screws



#### Mounting on Pre-Slotted Plate AM1 PA



Connections and Schema

GV3P••

