





Safety switch, heavy duty, fusible, 1200A, 3 pole, 250hp, 240VAC/250VDC, NEMA 1

H328

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 14,517.00 USD

Main

Product	Single Throw Safety Switch	
Duty Rating	Heavy duty	
Device Application	Heavy application	
Disconnect Type	Fusible disconnect	
Factory Installed Neutral	None	
Phase	3 phase	
Number Of Poles	3	
Current Rating	1200 A	
Voltage Rating	250 V DC 240 V AC	
Enclosure Rating	NEMA 1 steel	
Motor Power Hp	50 hp at 240 V AC 50-60 Hz for 1 phase motors 100 hp at 240 V AC 50-60 Hz for 3 phase motors 250 hp at 240 V AC 50-60 Hz for 3 phase motors 50 hp at 250 V DC	

Complementary

Short-Circuit Current	200 kA maximum for L			
Fuse Type	L			
Mounting Type	Surface			
Electrical Connection	Lugs			
Wiring Configuration	3-wire (3P)			
Wire Size	AWG 3/0750 kcmil copper or aluminium			
Tightening Torque	375 lbf.in (42.37 N.m) 0.130.59 in² (85.01380 mm²) (AWG 3/0750 kcmil)			
Depth	17.75 in (450.85 mm)			
Width	36.62 in (930.15 mm)			
Height	69.13 in (1755.90 mm)			
Net Weight	363.10 lb(US) (164.7 kg)			

Environment

Certifications UL listed file E2875

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Ordering and shipping details

Category	US10DE100053
Discount Schedule	0DE1
Gtin	785901823063
Returnability	No
Country Of Origin	MX

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance


	Mercury Free
	Rohs Exemption Information Yes
②	Pvc Free
⊘	Halogen Free Plastic Parts Product

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

Dimensions Drawings

Approximate Dimensions



	CATALOG		WIRING		3 PHA	SE HOR	SEPOWER	RATIN	GS	D	C HORS	EPOWER	
	NUMBER	VOLTAGE RATINGS	DIAG.	240	WAC	480	WAC	600	WAC	250	VDC	600	VDC
L				STD	MAX.	STD	MAX.	STD	MAX.	STD	MAX.	STD	MAX.
	H328 H328R H328N H328NR H368R H368R H368N H368NR HU368R HU3688	240VAC; 250VDC 240VAC; 250VDC 240VAC; 250VDC 240VAC; 250VDC 600VAC; 600VDC 600VAC; 600VDC 600VAC; 600VDC 600VAC; 600VDC 600VAC; 600VDC 600VAC; 600VDC	A A B B A A B B C C	100 100 100 100 100 100 100 100 100 100	250 250 250 250 250 250 250 250 250 100 100	- - 200 200 200 200 200	500 500 500 500 500 500	250 250 250 250 250	500 500 500 500 500 500 500	50 50 50 50 - - -	50 50 50 50 - - -	500000 550000 550000	50 50 50 50 50

Connections and Schema

Wiring Diagrams

WIRING DIAGRAMS						
FUSIBLE	NOT FUSIBLE					
A \$ \$ \$ \$ \$ \$ \$ \$ \$	c / / /					

	TERMINAL LUGS							
I	AMPERES MAX. WIRE MIN. WIRE TYPE							
	1200	(4)750	KCMIL	(4)#3/0 AWG	75°C	AL	OR	CU

FUSE PROVISIONS								
AMPERES	TYPE							
1200	CLASS "L"	800	CLASS "L"					