Product data sheet

Specifications



Safety switch, heavy duty, fusible, 200A, 3 poles, 150hp, 600VAC/ 600 NDC, NEMA 4, 4X, 5, 316 steel,

H364SS

() Discontinued on: Jul 3, 2023

Product availability: Non-Stock - Not normally stocked in distribution facility

Main

Product	Single Throw Safety Switch			
Duty Rating	Heavy duty			
Device Application	Heavy application			
Disconnect Type	Fusible disconnect			
Factory Installed Neutral	None			
Phase	3 phase			
Number Of Poles	3			
Current Rating	200 A			
Voltage Rating	600 V AC/DC			
Enclosure Rating	NEMA 4/4X/5 stainless steel 316			
Motor Power Hp50 hp at 480 V AC 50-60 Hz for 3 phase motors 125 hp at 480 V AC 50-60 Hz for 3 phase motors 60 hp at 600 V AC 50-60 Hz for 3 phase motors 150 hp at 600 V AC 50-60 Hz for 3 phase motors 50 hp at 600 V DC				

Complementary

• •				
Short-Circuit Current	10 kA for H or K			
	200 kA for R or J			
Fuse Type	H or K			
	R or J			
Mounting Type	Surface			
Electrical Connection	Lugs			
Wiring Configuration	3-wire			
Wire Size	AWG 6250 kcmil copper or aluminium			
Tightening Torque	275 lbf.in (31.07 N.m) 0.020.20 in ² (13.3127 mm ²) (AWG 6250 kcmil)			
Depth	8.88 in (225.55 mm)			
Width	19.25 in (488.95 mm)			
Height	29 in (736.60 mm)			
Net Weight	56.99 lb(US) (25.85 kg)			

Environment

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

UL listed file E2875

Ordering and shipping details

Category	US10DE100010
Discount Schedule	0DE1
Gtin	785901675792
Returnability	Yes
Country Of Origin	US

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	30.00 in (76.2 cm)
Package 1 Width	8.31 in (21.112 cm)
Package 1 Length	19.25 in (48.895 cm)
Package 1 Weight	57.00 lb(US) (25.855 kg)

Contractual warranty

Warranty

18 months

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Reach Free Of Svhc
Toxic Heavy Metal Free
Mercury Free
Rohs Exemption Information Yes
Pvc Free

Certifications & Standards


REACh Declaration		
Compliant		
EU RoHS Declaration		
China RoHS declaration		
Pro-active China RoHS declaration (out of China RoHS legal scope)		
Product Environmental Profile		
No need of specific recycling operations		
WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov		

Product data sheet

H364SS

Dimensions Drawings

Approximate Dimensions



Connections and Schema

Connections and Wiring Diagrams

WIRING DIAGRAMS				
H364SS	HU364SS			
FUSIBLE	NOT FUSIBLE			

TERMINAL LUG DATA ‡				
AMPERES	MAX WIRE	MIN WIRE	TYPE	
200	250 KCMIL	#6 AWG	CU/AL	

‡ LUGS SUITABLE FOR 75°C CONDUCTORS.