


Product data sheet

Specifications



Appliance, EcoStruxure IT Data Center Expert, enterprise, up to 4025 devices, up to 250 surveillance cameras, remote monitoring, management

AP9475

Overview

Presentation	StruxureWare Data Center Expert Enterprise scales up to 4025 devices and 250 surveillance cameras.
Lead Time	Usually Ships within 2 Weeks

Main

Number Of Rack Unit	2U
Number Of Cables	2
Communication Port Protocol	DNS HTTP HTTPS SMTP SMS SNMP SSL TCP/IP
Provided Equipment	1 Node Surveillance License Key 25-Node license key CD with software Server appliance User Manual Installation guide

General

Operating System	Windows 7 Windows 8 Windows Vista Windows XP Windows XP Professional SP1 Windows XP Professional SP2
Memory Capacity	4GB/5 x 300GB RAID-5 available for data storage

Physical

Color	Silver
Height	3.50 in (8.9 cm)
Width	19.02 in (48.3 cm)
Depth	19.02 in (48.3 cm)
Net Weight	55.12 lb(US) (25 kg)
Mounting Location	Front
Mounting Preference	No preference
Mounting Mode	Rack-mounted

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Environmental

Ambient Air Temperature For Operation	50...95 °F (10...35 °C)
Operating Altitude	0...10000 ft
Relative Humidity	5...90 %
Ambient Air Temperature For Storage	-40...158 °F (-40...70 °C)
Storage Altitude	0...30000 ft (0.00...9144.00 m)
Storage Relative Humidity	5...95 %

Communications & Management

Communication Network Type	RJ-45 10/100 Base-T USB
----------------------------	----------------------------

Ordering and shipping details

Gtin	731304246039
------	--------------

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	15.00 in (38.1 cm)
Package 1 Width	35.98 in (91.4 cm)
Package 1 Length	24.76 in (62.9 cm)
Package 1 Weight	87.19 lb(US) (39.55 kg)

Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency

Eu Rohs Directive

Not applicable, out of EU RoHS legal scope

Environmental Disclosure

[Product Environmental Profile](#)