





(!) Discontinued

Safety switch, heavy duty, non fusible, 200A, 3 pole, 150HP, 600VAC/600VDC, NEMA 4, 4X, 5, 316 stainless steel

HU364SS

(!) Discontinued on: Nov 22, 2023

Product availability: Non-Stock - Not normally stocked in distribution facility

Main

Product	Single Throw Safety Switch	
Duty Rating	Heavy duty	
Device Application	Heavy application	
Disconnect Type	Non-fusible disconnect	
Factory Installed Neutral	None	
Phase	3 phase	
Number Of Poles	3	
Current Rating	200 A	
Voltage Rating	600 V AC/DC	
Enclosure Rating	NEMA 4/4X/5 stainless steel 316	
Motor Power Hp	125 hp at 480 V AC 50-60 Hz for 3 phase motors 150 hp at 600 V AC 50-60 Hz for 3 phase motors 50 hp at 600 V DC	

Complementary

Mounting Type	Surface	
Electrical Connection	Lugs	
Wiring Configuration	3-wire	
Wire Size	AWG 6250 kcmil copper or aluminium	
Tightening Torque	275 lbf.in (31.07 N.m) 0.020.20 in² (13.3127 mm²) (AWG 6250 kcmil)	
Depth	8.88 in (225.55 mm)	
Width	19.25 in (488.95 mm)	
Height	29 in (736.60 mm)	
Net Weight	54.90 lb(US) (24.9 kg)	

Environment

Certifications UL listed file E2875

Ordering and shipping details

Category US10DE100010

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Discount Schedule	0DE1
Gtin	785901413134
Returnability	Yes
Country Of Origin	US

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	8.20 in (20.828 cm)
Package 1 Width	19.30 in (49.022 cm)
Package 1 Length	30.70 in (77.978 cm)
Package 1 Weight	57.02 lb(US) (25.864 kg)

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance


⊘	Reach Free Of Svhc
⊘	Toxic Heavy Metal Free
⊘	Mercury Free
⊘	Rohs Exemption Information Yes
⊘	Pvc Free

Certifications & Standards

Reach Regulation	REACh Declaration		
Eu Rohs Directive	Compliant EU RoHS Declaration		
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)		
Environmental Disclosure	Product Environmental Profile		
Circularity Profile	No need of specific recycling operations		
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov		

Dimensions Drawings

Approximate Dimensions



May 27, 2024

HU364SS

Connections and Schema

Connections and Wiring Diagrams

WIRING DIAGRAMS			
H364SS	HU364SS		
FUSIBLE	NOT FUSIBLE		
F P P P	15 /-/-		

TERMINAL LUG DATA ‡			
AMPERES	MAX WIRE	MIN WIRE	TYPE
200	250 KCMIL	#6 AWG	CU/AL

[‡] LUGS SUITABLE FOR 75°C CONDUCTORS.

May 27, 2024