

# Product data sheet

Specifications



## enclosed variable speed drive ATV31 - 1.1kW - 240V - IP55

ATV31CU11M2

 **Discontinued on:** Feb 17, 2021

 **Discontinued**

### Main

Range Of Product	Altivar 31
Product Or Component Type	Variable speed drive
Product Destination	Asynchronous motors
Product Specific Application	Simple machine
Assembly Style	Enclosed
Component Name	ATV31
Emc Filter	Integrated
Power Supply Voltage	200...240 V - 15...10 %
Power Supply Frequency	50...60 Hz - 5...5 %
Phase	Single phase
Motor Power Kw	1.1 kW
Maximum Horse Power Rating	1.5 hp
Line Current	10.2 A 240 V 1 kA 12.1 A 200 V 1 kA
Apparent Power	2.4 kVA
Maximum Prospective Line Isc	1 kA
Nominal Output Current	6.9 A 4 kHz
Maximum Transient Current	10.4 A 60 s
Power Dissipation In W	74 W at nominal load
Speed Range	1...50
Transient Overtorque	150...170 % of nominal motor torque
Asynchronous Motor Control Profile	Factory set : constant torque Sensorless flux vector control with PWM type motor control signal
Analogue Input Number	3
Ip Degree Of Protection	IP55

### Complementary

Power Supply Voltage Limit	170...264 V
Power Supply Frequency Limits	47.5...63 Hz
Speed Drive Output Frequency	0.5...500 Hz
Nominal Switching Frequency	4 kHz

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Switching Frequency	2...16 kHz adjustable
Braking Torque	<= 150 % 60 s with braking resistor 100 % with braking resistor continuously 50 % without braking resistor
Regulation Loop	Frequency PI regulator
Motor Slip Compensation	Automatic whatever the load Adjustable Suppressable
Output Voltage	<= power supply voltage
Electrical Connection	AI1, AI2, AI3, AOV, AOC, R1A, R1B, R1C, R2A, R2B, LI1...LI6 terminal 0.00 in <sup>2</sup> (2.5 mm <sup>2</sup> ) AWG 14 L1, L2, L3, U, V, W, PA, PB, PA/+, PC/- terminal 0.00 in <sup>2</sup> (2.5 mm <sup>2</sup> ) AWG 14
Tightening Torque	AI1, AI2, AI3, AOV, AOC, R1A, R1B, R1C, R2A, R2B, LI1...LI6 5.31 lbf.in (0.6 N.m) L1, L2, L3, U, V, W, PA, PB, PA/+, PC/- 7.08 lbf.in (0.8 N.m)
Insulation	Electrical between power and control
Supply	Internal supply for logic inputs 19...30 V, <100 mA overload protection Internal supply for logic inputs 19...30 V, <100 mA short-circuit protection Internal supply for reference potentiometer 10...10.8 V, <10 mA overload protection Internal supply for reference potentiometer 10...10.8 V, <10 mA short-circuit protection
Analogue Input Type	AI3 configurable current 0...20 mA 250 Ohm AI1 configurable voltage 0...10 V 30 V max 30000 Ohm AI2 configurable voltage +/- 10 V 30 V max 30000 Ohm
Input Sampling Time	LI1...LI6 4 ms discrete AI1, AI2, AI3 8 ms analog
Output Response Time	AOV, AOC 8 ms analog R1A, R1B, R1C, R2A, R2B 8 ms discrete
Linearity Error	+/- 0.2 % output
Analogue Output Number	2
Analogue Output Type	AOC configurable current 0...20 mA 800 Ohm 8 bits AOV configurable voltage 0...10 V 470 Ohm 8 bits
Discrete Input Logic	Positive logic (source) LI1...LI6), < 5 V, > 11 V Logic input not wired LI1...LI4), < 13 V Negative logic (source) LI1...LI6), > 19 V
Discrete Output Number	2
Discrete Output Type	Configurable relay logic R1A, R1B, R1C) 1 NO + 1 NC - 100000 cycles Configurable relay logic R2A, R2B) NC - 100000 cycles
Minimum Switching Current	10 mA 5 V DC R1-R2
Maximum Switching Current	2 A 250 V AC inductive - cos phi = 0.4 - L/R = 7 ms R1-R2) 2 A 30 V DC inductive - cos phi = 0.4 - L/R = 7 ms R1-R2) 5 A 250 V AC resistive - cos phi = 1 - L/R = 0 ms R1-R2) 5 A 30 V DC resistive - cos phi = 1 - L/R = 0 ms R1-R2)
Discrete Input Number	6
Discrete Input Type	LI1...LI6) programmable 24 V, 0...100 mA PLC 3500 Ohm
Acceleration And Deceleration Ramps	Linear adjustable separately from 0.1 to 999.9 s S, U or customized
Braking To Standstill	By DC injection
Protection Type	Input phase breaks drive Line supply overvoltage and undervoltage safety circuits drive Line supply phase loss safety function, for three phases supply drive Motor phase breaks drive Overcurrent between output phases and earth (on power up only) drive Overheating protection drive Short-circuit between motor phases drive Thermal protection motor

Insulation Resistance	>= 500 mOhm 500 V DC for 1 minute
Local Signalling	for drive voltage 1 LED (red) for CANopen bus status four 7-segment display units
Time Constant	5 ms for reference change
Frequency Resolution	Display unit 0.1 Hz Analog input 0.1...100 Hz
Communication Port Protocol	CANopen Modbus
Connector Type	1 RJ45 CANopen via VW3 CANTAP2 adaptor 1 RJ45 Modbus
Physical Interface	RS485 multidrop serial link Modbus
Transmission Frame	RTU Modbus
Transmission Rate	10, 20, 50, 125, 250, 500 kbps or 1 Mbps CANopen via VW3 CANTAP2 adaptor 4800, 9600 or 19200 bps Modbus
Number Of Addresses	1...127 CANopen via VW3 CANTAP2 adaptor 1...247 Modbus
Number Of Drive	127 CANopen via VW3 CANTAP2 adaptor 31 Modbus
Marking	CE
Operating Position	Vertical +/- 10 degree
Net Weight	19.40 lb(US) (8.8 kg)

## Environment

Dielectric Strength	2040 V DC between earth and power terminals 2880 V AC between control and power terminals
Electromagnetic Compatibility	1.2/50 µs - 8/20 µs surge immunity test level 3 IEC 61000-4-5 Electrical fast transient/burst immunity test level 4 IEC 61000-4-4 Electrostatic discharge immunity test level 3 IEC 61000-4-2 Radiated radio-frequency electromagnetic field immunity test level 3 IEC 61000-4-3
Standards	EN 50178
Product Certifications	CSA N998 C-tick UL
Pollution Degree	2
Protective Treatment	TC
Vibration Resistance	1 gn 13...150 Hz)EN/IEC 60068-2-6 1.5 mm 3...13 Hz)EN/IEC 60068-2-6
Shock Resistance	15 gn 11 ms EN/IEC 60068-2-27
Relative Humidity	5...95 % without condensation IEC 60068-2-3 5...95 % without dripping water IEC 60068-2-3
Ambient Air Temperature For Storage	-13...158 °F (-25...70 °C)
Ambient Air Temperature For Operation	14...122 °F (-10...50 °C) without derating with protective cover on top of the drive) 14...140 °F (-10...60 °C) with derating factor without protective cover on top of the drive)
Operating Altitude	<= 3280.84 ft (1000 m) without derating >= 3280.84 ft (1000 m) with current derating 1 % per 100 m

## Ordering and shipping details

Category	22152-ATV320/ATV312/ATV32 (.25 THRU 7.5HP)
----------	--

Discount Schedule	CP4B
Gtin	3389110587579
Returnability	No
Country Of Origin	ID

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	11.02 in (28 cm)
Package 1 Width	10.04 in (25.5 cm)
Package 1 Length	14.17 in (36 cm)
Package 1 Weight	15.36 lb(US) (6.968 kg)

## Contractual warranty

Warranty	18 months
----------	-----------

## Sustainability




**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

## Well-being performance

 Reach Free Of Svhc	
 Mercury Free	
 Rohs Exemption Information	<a href="#">Yes</a>
<b>Eu Rohs Directive</b>	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
<b>China Rohs Regulation</b>	<a href="#">China RoHS declaration</a>
<b>Weee</b>	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
<b>California Proposition 65</b>	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>