Product data sheet

Specification





servo motor BCH, Lexium 28, 40mm, 100W, with oil seal, smooth, leads connection

BCH2MB0132CA5C

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 875.80 USD

Main

Range Compatibility	Lexium 28
Product Or Component Type	Servo motor
Device Short Name	BCH2

Complementary

Maximum Mechanical Speed	5000 rpm	
[Us] Rated Supply Voltage	220 V 110 V	
Phase	Single phase Three phase	
Continuous Stall Current	0.81 A	
Continuous Stall Torque	2.83 lbf.in (0.32 N.m) LXM28 0.9 A, 220 V, single phase 2.83 lbf.in (0.32 N.m) LXM28 0.9 A, 220 V, three phase 2.83 lbf.in (0.32 N.m) LXM28 1.8 A, 110 V, single phase	
Continuous Power	100 W	
Peak Stall Torque	8.50 lbf.in (0.96 N.m) LXM28 0.9 A, 220 V, single phase 8.50 lbf.in (0.96 N.m) LXM28 0.9 A, 220 V, three phase 8.50 lbf.in (0.96 N.m) LXM28 1.8 A, 110 V, single phase	
Nominal Output Power	100 W LXM28 0.9 A, 220 V, single phase 100 W LXM28 0.9 A, 220 V, three phase 100 W LXM28 1.8 A, 110 V, single phase	
Nominal Torque	2.83 lbf.in (0.32 N.m) LXM28 0.9 A, 220 V, single phase 2.83 lbf.in (0.32 N.m) LXM28 0.9 A, 220 V, three phase 2.83 lbf.in (0.32 N.m) LXM28 1.8 A, 110 V, single phase	
Nominal Speed	3000 rpm LXM28 0.9 A, 220 V, single phase 3000 rpm LXM28 0.9 A, 220 V, three phase 3000 rpm LXM28 1.8 A, 110 V, single phase	
Maximum Current Irms	2.65 A LXM28 0.1 kW, 220 V 2.65 A LXM28 0.1 kW, 110 V	
Maximum Permanent Current	0.89 A	
Product Compatibility	LXM28 servo drive 0.1 kW, 220 V, single phase LXM28 servo drive 0.1 kW, 220 V, three phase LXM28 servo drive 0.1 kW, 110 V, single phase	
Shaft End	Smooth shaft	
Shaft Diameter	0.31 in (8 mm)	
Shaft Length	0.98 in (25 mm)	
Feedback Type	20 bits single turn absolute encoder	

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Holding Brake	Without	
Mounting Support	Asian standard flange	
Motor Flange Size	1.57 in (40 mm)	
Electrical Connection	Free lead	
Torque Constant	0.4 N.m/A 68 °F (20 °C)	
Back Emf Constant	24 V/krpm 68 °F (20 °C)	
Rotor Inertia	0.075 kg.cm²	
Stator Resistance	23.4 Ohm 68 °F (20 °C)	
Stator Inductance	20.6 mH 68 °F (20 °C)	
Stator Electrical Time Constant	0.88 ms 68 °F (20 °C)	
Maximum Radial Force Fr	85 N 3000 rpm	
Maximum Axial Force Fa	40 N	
Brake Pull-In Power	4.35 W	
Type Of Cooling	Natural convection	
Length	3.94 in (100 mm)	
Number Of Motor Stacks	2	
Centring Collar Diameter	1.18 in (30 mm)	
Centring Collar Depth	0.12 in (3 mm)	
Number Of Mounting Holes	4	
Mounting Holes Diameter	0.18 in (4.5 mm)	
Circle Diameter Of The Mounting Holes	1.81 in (46 mm)	
Distance Shaft Shoulder-Flange	0.12 in (3 mm)	
Net Weight	1.23 lb(US) (0.56 kg)	

Environment

Ip Degree Of Protection	IP50 IM V3 IP65 IM B5, IM V1	
Ambient Air Temperature For Operation	-4104 °F (-2040 °C)	

Ordering and shipping details

Category	US1PC5318281	
Discount Schedule	PC53	
Gtin	3606480733444	
Returnability	No	
Country Of Origin	CN	

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.15 in (8.0 cm)
Package 1 Width	5.12 in (13.0 cm)
Package 1 Length	9.45 in (24.0 cm)

Package 1 Weight	27.57 oz (781.5 g)	
Unit Type Of Package 2	S02	
Number Of Units In Package 2	3	
Package 2 Height	5.91 in (15.0 cm)	
Package 2 Width	11.81 in (30.0 cm)	
Package 2 Length	15.75 in (40.0 cm)	
Package 2 Weight	5.97 lb(US) (2.706 kg)	



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

	Reach Free Of Svhc	
9	Mercury Free	
⊘	Rohs Exemption Information	Yes
⊘	Pvc Free	


Certifications & Standards

Reach Regulation	REACh Declaration		
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)		
China Rohs Regulation	China RoHS declaration		
Environmental Disclosure	Product Environmental Profile		
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.		
Circularity Profile	End of Life Information		
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov		

Dimensions Drawings

Dimensions

Dimensions of Motor




	mm	in.
L (without holding brake)	100	3.94
L (with holding brake)	130	5.12
Z	61.5	2.42

Performance Curves

Torque/Speed Curves with 230 V Single/Three Phase Supply Voltage


Servo Motor without shaft sealing ring and LXM28AU01●●● Servo Drive M [Nm]



- 1: Peak torque
- 2: Continuous torque

Torque/Speed Curves with 230 V Single/Three Phase Supply Voltage

Servo Motor with shaft sealing ring and LXM28AU01●●● Servo Drive M [Nm]



- 1: Peak torque
- 2: Continuous torque